

TS 35X7.5 2M/ST/ZN**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Product image

Similar to illustration

Building installation wiring

For building installations, we offer a complete system that revolves around the 10×3 copper rail and comprises perfectly coordinated components: from installation terminal blocks, neutral conductor terminal blocks and distribution terminal blocks to comprehensive accessories such as busbars and busbar holders.

General ordering data

Version	Rail, TS 35, TS 35 x 7.5, without slot, Steel, galvanic zinc plated and passivated
Order No.	0383400000
Type	TS 35X7.5 2M/ST/ZN
GTIN (EAN)	4008 190088026
Qty.	2 m

Creation date March 20, 2021 10:28:31 PM CET

Catalogue status 12.03.2021 / We reserve the right to make technical changes.

TS 35X7.5 2M/ST/ZN

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	7.5 mm	Depth (inches)	0.295 inch
Height	35 mm	Height (inches)	1.378 inch
Net weight	325 g	Width	2,000 mm
Width (inches)	78.74 inch		

Mounting rail

Installation advice	Direct mounting		
Length of the terminal rail	max.	2,000 mm	
	nominal	2,000 mm	
	min.	0 mm	
Material	Steel		
Pre-punched mounting rail	No		
Short circuit strength corresponds to E-Cu wire	16 mm ²		
Short-time withstand current according to IEC 60947-7-2	1.92 kA/1s		
Slit gap			
Slit length			
Slit width			
Standards	DIN EN 60715		
Surface finish	galvanic zinc plated and passivated		
Thickness	1 mm		

Classifications

ETIM 6.0	EC001285	ETIM 7.0	EC001285
ECLASS 9.0	27-40-06-02	ECLASS 9.1	27-40-06-02
ECLASS 10.0	27-40-06-02	ECLASS 11.0	27-40-06-02

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	STEP
Engineering Data	EPLAN, WSCAD, Zuken E3.S
User Documentation	StorageConditionsTerminalBlocks