



## NC4FX-B

4 pole female cable connector with black metal housing and gold contacts.

The "industry standard" XLR cable connector, easy to assemble with only 4 parts and no screws. Compact design with sturdy diecast shell, fibreglass reinforced hard plastic insert and chuck type strain relief for secure clamping of all cables.

### Features & Benefits

- Rugged zinc diecast shell, long lasting and durable
- Chuck type strain relief system for secure clamping of cables
- Boot with rubber gland gives high protection against bending stresses
- Coloured rings and boots available for coding and marking
- UL recognized components

**Technical Information**

| Product                |         |
|------------------------|---------|
| <b>Title</b>           | NC4FX-B |
| <b>Connection Type</b> | XLR     |
| <b>Gender</b>          | female  |

| Electrical                          |                             |
|-------------------------------------|-----------------------------|
| <b>Capacitance between contacts</b> | $\leq 7$ pF                 |
| <b>Contact resistance</b>           | $\leq 3$ m $\Omega$         |
| <b>Dielectric strength</b>          | 1,5 kVdc                    |
| <b>Insulation resistance</b>        | $> 10$ G $\Omega$ (initial) |
| <b>Rated current per contact</b>    | 10 A                        |
| <b>Rated voltage</b>                | $< 50$ V                    |

| Mechanical              |                          |
|-------------------------|--------------------------|
| <b>Cable O.D.</b>       | 3.5 - 8.0 mm             |
| <b>Insertion force</b>  | $\leq 20$ N              |
| <b>Withdrawal force</b> | $\leq 20$ N              |
| <b>Lifetime</b>         | $> 1000$ mating cycles   |
| <b>Wiresize</b>         | max. 1.5 mm <sup>2</sup> |
| <b>Wiresize</b>         | max. 16 AWG              |
| <b>Wiring</b>           | Solder contacts          |
| <b>Locking device</b>   | Latch lock               |

| <b>Material</b>        |                                   |
|------------------------|-----------------------------------|
| <b>Boot</b>            | Polyurethan                       |
| <b>Contact plating</b> | 0.2 µm Au hard alloy over 2 µm Ni |
| <b>Contacts</b>        | Brass (CuZn39Pb3)                 |
| <b>Insert</b>          | Polyamide (PA66)                  |
| <b>Locking element</b> | St3K32 (latch) / Ck 67 (spring)   |
| <b>Shell</b>           | Zinc diecast (ZnAl4Cu1)           |
| <b>Shell plating</b>   | Black chromium                    |
| <b>Strain relief</b>   | Polyacetal (POM)                  |

| <b>Environmental</b>       |                           |
|----------------------------|---------------------------|
| <b>Approvals</b>           | UL                        |
| <b>Flammability</b>        | UL 94 V-0                 |
| <b>Standard compliance</b> | IEC 61076-2-103           |
| <b>Protection class</b>    | IP 40                     |
| <b>Solderability</b>       | Complies with IEC 68-2-20 |
| <b>Temperature range</b>   | -30 °C to +80 °C          |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Neutrik:](#)

[NC4FX-B](#)