



NE8FDV-Y110

Panel mount receptacle with IDC 110 punch down terminals, D-shape metal flange with latch lock, max. panel thickness 4 mm, mounting screws included

The etherCON Series is a ruggedized and lockable RJ45 connector system, optimized for pro audio, video and lightning network applications. The chassis connectors are shaped to fit into standardized panels out of the entertainment industry. The D-Series offers the most rugged design of the etherCON series and is perfectly suitable for panel mount and the installer market.

Attention! Does not intermate with CAT6 cable connector NE8MC6-MO and NKE6S* cables.

Features & Benefits

- Accommodates NE8MC* or any standard RJ45 plug
- Mountable from the front or rear of the panel
- Selectable ground - panel connection
- Approved latch lock system
- Complies with Cat 5e according to TIA / EIA 568B and ISO / IEC 11801 standard
- Easy and quick mounting using 110 type punch down terminals

Technical Information

Product	
Title	NE8FDV-Y110
Gender	female

Electrical	
Contact resistance	< 10 mΩ
Dielectric strength	1 kVdc
Frequencyrange	1 - 100 MHz
Insulation resistance	> 0.5 GΩ
Rated current per contact	1,5 A
Rated voltage	< 50 V
Transmission performance	CAT 5e
Standard compliance	TIA/EIA 586B, IEC11801

Mechanical	
Insertion force	≤ 20 N
Withdrawal force	≤ 20 N
Lifetime	> 1000 mating cycles
Panel thickness	max. 4 mm 0.16"
Wiresize	0.14 - 0.5 mm ²
Wiresize	26 - 20 AWG
Wiring	IDC 110 punch down terminals
Locking device	Latch lock
Chassis shape	D

Material	
Contact plating	0.2 µm Au over Ni plating
Contacts	Bronze (CuSn8)
Insert	PBTP 15 % GR
Shell	Zinc diecast (ZnAl4Cu1)
Shell plating	Nickel
Strain relief	CuZn35Pb2, Tin plated

Environmental	
Flammability	UL 94 V-0
Temperature range	-30 °C to +80 °C

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Neutrik:](#)

[NE8FDV-Y110](#)