

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0430300005**
Status: **Active**
Overview: Micro-Fit Connector System
Description: Micro-Fit 3.0 Crimp Terminal, Female, with Select Gold (Au) Plated Phosphor Bronze Contact, 26-30 AWG, Reel

Documents:

Drawing (PDF)	Test Summary TS-43045-001-001 (PDF)
Product Specification PS-43045-001 (PDF)	Test Summary TS-43045-002-001 (PDF)
Packaging Specification PK-43030-001-001 (PDF)	Datasheet (PDF)
Test Summary 430450005-TS-000 (PDF)	RoHS Certificate of Compliance (PDF)
Test Summary 430450006-TS-000 (PDF)	

General

Product Family	Crimp Terminals
Series	43030
Application	Power, Wire-to-Board, Wire-to-Wire
Crimp Quality Equipment	Yes
Overview	<u>Micro-Fit Connector System</u>
Packaging Alternative	430300011 (Loose)
Product Name	Micro-Fit 3.0
UPC	800754369206

Physical

Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Net Weight	0.057/g
Packaging Type	Reel
Plating min - Mating	0.381µm
Plating min - Termination	2.540µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.27mm max.
Wire Size AWG	26, 28, 30
Wire Size mm ²	N/A

Electrical

Current - Maximum per Contact	8.5A
-------------------------------	------


Solder Process Data

Lead-free Process Capability	N/A
------------------------------	-----

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-43030-001-001
Product Specification	PS-43045-001
Sales Drawing	SD-43030-XXXX-001
Test Summary	430450005-TS-000, 430450006-TS-000, TS-43045-001-001, TS-43045-002-001



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Contained Per -
D(2020)4578-DC (25
June 2020)
6-methoxy-m-toluidine
C,C'-
azodi(formamide)
di-n-pentyl phthalate
(DPP)
tricosafuorododecanoic
acid
perfluorooctanoic acid
heptacosafuorotetradecanoic
acid
dodecamethylcyclohexasiloxane
octamethylcyclotetrasiloxane
disodium 3,3'-[[1,1'-
biphenyl]-4,4'-
diylbis(azo)
diisopentylphthalate
methoxyacetic acid
1,2-diethoxyethane
dibutyltin dichloride
2-methylimidazole
4,4'-methylenedi-o-
toluidine
1-vinylimidazole
1,3-propanesultone
chromium trioxide
disodium 4-
amino-3-[[4'-[(2,4-
diaminophenyl)azo]
henicosafuoroundecanoic
acid
ammoniumpentadecafluorooctanoate
sodium
peroxometaborate
1,3,5-tris-[(2S
and 2R)-2,3-
epoxypropyl]-1,3,5-t

China RoHS

benzo[a]pyrene
4-aminoazobenzene
diethyl sulphate
propylene oxide
dimethyl sulphate
N-methylacetamide
p-(1,1-dimethylpropyl)phenol
dihexyl phthalate
(DnHP)
phenanthrene
dinoseb (ISO)
butyl 4-hydroxybenzoate
o-toluidine
4-methyl-m-phenylenediamine
ethylene thiourea
4-o-tolylazo-o-toluidine
4-tert-butylphenol
nitrobenzene
1-bromopropane
ethylenediamine
furan
2-methoxyethyl acetate
Trixylyl phosphate
4-(1,1,3,3-tetramethylbutyl)phenol, ethoxylated
4-Nonylphenol, branched and linear, ethoxylated
4-Heptylphenol, branched and linear
Nonadecafluorodecanoic acid (PFDA) and its sodium
2,3,3,3-tetrafluoro-2-(heptafluoropropoxy)propio
Tris(4-nonylphenyl, branched and linear) phosphite
Fluoranthene
Pyrene
Chrysene
Dodecachloropentacyclo[12.2.1.16,9.02,13.05,10]octane
Reaction products of 1,3,4-thiadiazolidine-2,5-dione
Perfluorononan-1-oic acid
(2,2,3,3,4,4,5,5,6,6,7,7,7,7-tetrafluoro-4-(1,1,3,3-tetramethylbutyl)phenol, ethoxylated
hexahydro-2-benzofuran-1,3-dione
Methylhexahydrophthalic anhydride
Sodium perborate; perboric acid, sodium salt
Cadmium sulphate

reaction mass of
2-ethylhexyl 10-
ethyl-4,4-dioct
1,2-
benzenedicarboxylic
acid, di-C6-10-alkyl
est
5-sec-butyl-2-(2,4-
dimethylcyclohex-3-
en-1-yl)-5
Perfluorohexane-1-
sulphonic acid and its
salts
1,7,7-trimethyl-3-
(phenylmethylene)bicyclo[2.2.1
2-ethylhexyl 10-
ethyl-4,4-dioctyl-7-
oxo-8-oxa-3,
dibutylbis(pentane-2,4-
dionato-O,O')tin
2-(2H-benzotriazol-2-
yl)-4-(tert-butyl)-6-
(sec-b
1,2-
Benzenedicarboxylic
acid, dihexyl ester,
bra
diisohexyl phthalate
pentacosafuorotridecanoic
acid
1,2-
benzenedicarboxylic
acid, dipentylester,
bra
2-methyl-1-(4-
methylthiophenyl)-2-
morpholinoprop
4,4-
isobutylethylidenediphenol
2-benzyl-2-
dimethylamino-4-
morpholinobutyropheno
3-ethyl-2-methyl-2-
(3-methylbutyl)-1,3-
oxazolidi
n-pentyl-
isopentylphthalate
1,3-BENZENEDIOL,
TRINITRO-, LEAD
SALT
Hydrazine
Disodium tetraborate
Boric acid
4,4'-Oxydianiline and
its salts
Aluminosilicate
Refractory Ceramic
Fibres
Zirconia
Aluminosilicate
Refractory Ceramic
Fibr
Acids generated from
chromium trioxide and
their

4-Nonylphenol,
branched and linear
[substances w
cobalt carbonate
cobalt di(acetate)
cobalt dinitrate
cobalt sulphate
2-ethoxyethyl acetate
strontium chromate
1,2-
benzenedicarboxylic
acid; di-C7-11-
branched
N-methyl-2-
pyrrolidone
1,2,3-trichloropropane
1,2-
benzenedicarboxylic
acid; di-C6-8-
branched a
calcium arsenate
bis(2-methoxyethyl)
ether
potassium
hydroxyoctaoxidizincatedichromate(1-)
lead dipicrate
N,N-
dimethylacetamide
arsenic acid
2-methoxyaniline
trilead diarsenate
1,2-dichloroethane
pentazinc chromate
octahydroxide
Formaldehyde,
polymer with
benzenamine
bis(2-methoxyethyl)
phthalate
triethyl arsenate
4,4'-
diaminodiphenylmethane
lead hydrogen
arsenate
2,4-dinitrotoluene
Anthracene oil;
Anthracene oil
Anthracene oil,
anthracene paste;
Anthracene Oil
Anthracene oil,
anthracene paste,
anthracene fra
Anthracene oil,
anthracene paste,
distn. lights;
Anthracene oil,
anthracene-low;
Anthracene Oil F
diisobutyl phthalate
(DIBP)
lead chromate
Lead chromate
molybdate sulfate red

Lead sulfochromate
yellow
Pitch, coal tar, high-
temp.; Pitch
tris(2-chloroethyl)
phosphate
ammonium
dichromate
potassium chromate
potassium dichromate
sodium chromate
tetraboron disodium
heptaoxide, hydrate
trichloroethylene
2-ethoxyethanol
 α,α -Bis[4-
(dimethylamino)phenyl]-4
(phenylamino)
cadmium
cadmium fluoride
pyrochlore, antimony
lead yellow
lead dinitrate
cadmium chloride
Silicic acid, lead salt
lead oxide sulfate
lead titanium trioxide
pentalead tetraoxide
sulphate
trilead dioxide
phosphonate
tetralead trioxide
sulphate
dioxobis(stearato)trilead
Lead titanium
zirconium oxide
lead
bis(tetrafluoroborate)
lead cyanamidate
Acetic acid, lead salt,
basic
Sulfurous acid, lead
salt, dibasic
Silicic acid (H₂Si₂O₅),
barium salt (1:1),
lead-
[phthalato(2-)]dioxotrilead
Fatty acids, C16-18,
lead salts
lead(II)
methanesulphonate
lead diazide
phenolphthalein
dichromium
tris(chromate)
2,2'-dichloro-4,4'-
methylenedianiline
formamide
tetraethyllead
4,4'-
bis(dimethylamino)benzophenone
N,N,N',N'-
tetramethyl-4,4'-
methylenedianiline
1,2-dimethoxyethane

1.12-1.27mm, 26-30
AWG Wire
FineAdjust Applicator 639046600
for Micro-Fit 3.0
Crimp Terminals,
26-30 AWG
T2 Terminator 639104400
for Insulation OD
1.12-1.27mm, 26-30
AWG

Japan

Description	Product #
--------------------	------------------

Applicator for M211A Bench Press, 20-30	<u>572983000</u>
--	------------------

AWG Wire

S-1 Applicator for Micro-Fit 3.0 Plug	<u>572983710</u>
--	------------------

and Receptacle
Crimp Terminals,

26-30 AWG

This document was generated on 10/13/2020

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION