

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0444281001](#)
Status: **Active**
Overview: [Micro-Fit Connector System](#)
Description: Micro-Fit BMI Header, Surface Mount Compatible, Dual Row, Right-Angle, with Snap-in Plastic Peg PCB Lock, 10 Circuits, Tin (Sn) Plating

Documents:

Drawing (PDF)	Test Summary 444280001-TS-000 (PDF)
3D Model	Symbol Footprint Data SYM-44428-1001 (PDF)
3D Model (PDF)	Symbol Footprint Data SYM-44428-10013 (PDF)
Product Specification PS-44300-001-001 (PDF)	RoHS Certificate of Compliance (PDF)
Packaging Specification PK-44428-001-001 (PDF)	Product Literature (PDF)

Agency Certification


CSA	LR19980
UL	E29179

General

Product Family	PCB Headers
Series	44428
Application	Board-to-Board, Power, Wire-to-Board
Comments	High Temperature Square Pin Solder Type Polarized to Mating Part
Overview	Micro-Fit Connector System
Product Name	Micro-Fit BMI
UPC	800756081663

Physical

Breakaway	No
Circuits (Loaded)	10
Circuits (maximum)	10
Color - Resin	Black
Durability (mating cycles max)	30
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	2.399/g
Number of Rows	2
Orientation	Right Angle
PC Tail Length	3.50mm
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Packaging Type	Tray
Pitch - Mating Interface	3.00mm
Plating min - Mating	5.080µm
Plating min - Termination	5.080µm
Polarized to PCB	Yes
Shrouded	Fully
Stackable	No



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Contained Per -
D(2020)4578-DC (25
June 2020)
decamethylcyclopentasiloxane
benzene-1,2,4-
tricarboxylic acid 1,2-
anhydride
decamethylcyclopentasiloxane
dodecamethylcyclohexasiloxane
benzene-1,2,4-
tricarboxylic acid 1,2-
anhydride
octamethylcyclotetrasiloxane
disodium 3,3'-[[1,1'-
biphenyl]-4,4'-
diylbis(azo)
dodecamethylcyclohexasiloxane
heptacosafuorotetradecanoic
acid
tricosafuorododecanoic
acid
di-n-pentyl phthalate
(DPP)
6-methoxy-m-toluidine
diisopentylphthalate
methoxyacetic acid
dibutyltin dichloride
4,4'-methylenedi-o-
toluidine
1-vinylimidazole
1,3-propanesultone
chromium trioxide
disodium 4-
amino-3-[[4'-[(2,4-
diaminophenyl)azo]
henicosafuoroundecanoic
acid

China RoHS

Surface Mount Compatible (SMC) Yes
Temperature Range - Operating -40° to +105°C
Termination Interface: Style Through Hole

Electrical

Current - Maximum per Contact 8.5A
Voltage - Maximum 600V

Solder Process Data

Duration at Max. Process Temperature (seconds) 005
Lead-free Process Capability WAVE
Max. Cycles at Max. Process Temperature 001
Process Temperature max. C 260

Material Info

Reference - Drawing Numbers

Packaging Specification PK-44428-001-001
Product Specification PS-44300-001-001
Sales Drawing SD-44428-001
Symbol/Footprint Data SYM-44428-1001, SYM-44428-1001_3
Test Summary 444280001-TS-000

Silicic acid (H₂Si₂O₅),
barium salt (1:1),
lead-
[phthalato(2-)]dioxotrilead
Fatty acids, C16-18,
lead salts
4-aminoazobenzene
diethyl sulphate
dimethyl sulphate
N-methylacetamide
dicyclohexyl phthalate
dihexyl phthalate
(DnHP)
dinoseb (ISO)
butyl 4-
hydroxybenzoate
o-toluidine
4-methyl-m-
phenylenediamine
ethylene thiourea
4-o-tolylazo-o-
toluidine
nitrobenzene
1-bromopropane
furan
Zirconia
Aluminosilicate
Refractory Ceramic
Fibr
Trixylyl phosphate
4-(1,1,3,3-
tetramethylbutyl)phenol,
ethoxylated
2,3,3,3-tetrafluoro-2-
(heptafluoropropoxy)propio
Tris(4-nonylphenyl,
branched and linear)
phosphi
Pyrene
Cadmium nitrate
Chrysene
Dodecachloropentacyclo[12.2.1.16,9.02,13.05,10]o
Reaction
products of 1,3,4-
thiadiazolidine-2,5-d
Perfluorononan-1-
oic acid
(2,2,3,3,4,4,5,5,6,6,7
4-(1,1,3,3-
tetramethylbutyl)phenol,
ethoxylated
hexahydro-2-
benzofuran-1,3-dione
Sodium perborate;
perboric acid, sodium
salt
Cadmium sulphate
1,2-
benzenedicarboxylic
acid, di-C6-10-alkyl
est
5-sec-butyl-2-(2,4-
dimethylcyclohex-3-
en-1-yl)-5

Perfluorohexane-1-sulphonic acid and its salts
ammoniumpentadecafluorooctanoate
sodium
peroxometaborate
disodium octaborate
2-ethylhexyl 10-ethyl-4,4-dioctyl-7-oxo-8-oxa-3,
dibutylbis(pentane-2,4-dionato-O,O')tin
2-(2H-benzotriazol-2-yl)-4,6-ditertpentylphenol
2-(2H-benzotriazol-2-yl)-4-(tert-butyl)-6-(sec-b
Terphenyl,
hydrogenated
1,2-Benzenedicarboxylic acid, dihexyl ester,
bra
pentacosafuorotridecanoic acid
1,2-benzenedicarboxylic acid, dipentylester,
bra
3-ethyl-2-methyl-2-(3-methylbutyl)-1,3-oxazolidi
n-pentyl-
isopentylphthalate
1,3-BENZENEDIOL, TRINITRO-, LEAD SALT
Hydrazine
Disodium tetraborate
Boric acid
Aluminosilicate
Refractory Ceramic Fibres
tetraboron disodium heptaoxide, hydrate
cobalt carbonate
cobalt di(acetate)
cobalt sulphate
2-ethoxyethyl acetate
1,2-benzenedicarboxylic acid; di-C7-11-branched
N-methyl-2-pyrrolidone
1,2-benzenedicarboxylic acid; di-C6-8-branched a
calcium arsenate
bis(2-methoxyethyl) ether
potassium
hydroxyoctaoxodizincatedichromate(1-)

lead dipicrate
N,N-
dimethylacetamide
arsenic acid
2-methoxyaniline
trilead diarsenate
1,2-dichloroethane
pentazinc chromate
octahydroxide
triethyl arsenate
4,4'-
diaminodiphenylmethane
dibutyl phthalate
(DBP)
bis(2-ethylhexyl)
phthalate (DEHP)
lead hydrogen
arsenate
Butylbenzylphthalate
(BBP)
Anthracene oil,
anthracene paste;
Anthracene Oil
Anthracene oil,
anthracene paste,
anthracene fra
Anthracene oil,
anthracene paste,
distn. lights;
Anthracene oil,
anthracene-low;
Anthracene Oil F
lead chromate
Lead chromate
molybdate sulfate red
Lead sulfochromate
yellow
tris(2-chloroethyl)
phosphate
ammonium
dichromate
potassium chromate
potassium dichromate
sodium chromate
[4-[[4-anilino-1-
naphthyl]]4-
(dimethylamino)phen
 α,α -Bis[4-
(dimethylamino)phenyl]-4
(phenylamino)
lead
cadmium
cadmium fluoride
pyrochlore, antimony
lead yellow
lead dinitrate
cadmium chloride
Silicic acid, lead salt
lead oxide sulfate
pentalead tetraoxide
sulphate
trilead dioxide
phosphonate
tetralead trioxide
sulphate

dioxobis(stearato)trilead
Lead titanium
zirconium oxide
cadmium hydroxide
Acetic acid, lead salt,
basic
Sulfurous acid, lead
salt, dibasic
Formaldehyde,
polymer with
benzenamine
bis(2-methoxyethyl)
phthalate
lead diazide
phenolphthalein
dichromium
tris(chromate)
4,4'-
bis(dimethylamino)benzophenone
1,2-dimethoxyethane
cadmium carbonate
[4-[4,4'-
bis(dimethylamino)
benzhydrylidene]cycl
4,4'-
bis(dimethylamino)-4"-
(methylamino)trityl
bis(pentabromophenyl)
ether
diboron trioxide
cadmium oxide (non-
pyrophoric)
cadmium sulphide
orange lead
trilead bis(carbonate)
dihydroxide
Lead oxide
1,3,5-
tris(oxiranylmethyl)-1,3,5-
triazine-2,4,6(

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[44428](#) Series

Mates With

[44133](#) Micro-Fit BMI Panel Mount
Receptacle Housing, [44764](#) Micro-Fit BMI
Receptacle Header, [44769](#) Micro-Fit BMI
Receptacle Header

This document was generated on 10/14/2020

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION