

Bridge - LB 10-6 GY - 0202358

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Bridge, pitch: 6 mm, color: gray

Key Commercial Data

| | |
|--------------------------------------|---------------------|
| Packing unit | 1 pc |
| Minimum order quantity | 10 pc |
| GTIN | 4 017918 098575 |
| GTIN | 4017918098575 |
| Weight per Piece (excluding packing) | 19.800 g |
| Custom tariff number | 85369095 |
| Country of origin | Poland |

Technical data

Technical data

| | |
|---------------------|--------|
| Color | gray |
| Material | Copper |
| Number of positions | 10 |
| Pitch | 6 mm |

Ambient conditions

| | |
|--|---|
| Operating temperature | -60 °C ... 105 °C (max. short-term operating temperature RTI Elec.) |
| Ambient temperature (storage/transport) | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C) |
| Permissible humidity (storage/transport) | 30 % ... 70 % |
| Ambient temperature (assembly) | -5 °C ... 70 °C |

Bridge - LB 10-6 GY - 0202358

Technical data

Ambient conditions

| | |
|---------------------------------|-----------------|
| Ambient temperature (actuation) | -5 °C ... 70 °C |
|---------------------------------|-----------------|

Environmental Product Compliance

| | |
|------------|---|
| China RoHS | Environmentally Friendly Use Period = 50 years |
| | For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration" |

Classifications

eCl@ss

| | |
|---------------|----------|
| eCl@ss 10.0.1 | 27141140 |
| eCl@ss 11.0 | 27141140 |
| eCl@ss 4.0 | 27141100 |
| eCl@ss 4.1 | 27141100 |
| eCl@ss 5.0 | 27141100 |
| eCl@ss 5.1 | 27141100 |
| eCl@ss 6.0 | 27141100 |
| eCl@ss 7.0 | 27141140 |
| eCl@ss 9.0 | 27141140 |

ETIM

| | |
|----------|----------|
| ETIM 2.0 | EC000489 |
| ETIM 3.0 | EC000489 |
| ETIM 4.0 | EC000489 |
| ETIM 6.0 | EC000489 |
| ETIM 7.0 | EC000489 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 30211829 |
| UNSPSC 7.0901 | 39121426 |
| UNSPSC 11 | 39121426 |
| UNSPSC 12.01 | 39121426 |
| UNSPSC 13.2 | 39121426 |
| UNSPSC 18.0 | 39121426 |
| UNSPSC 19.0 | 39121426 |
| UNSPSC 20.0 | 39121426 |
| UNSPSC 21.0 | 39121426 |

