### **Littelfuse** Expertise Applied | Answers Delivered

### **Axial Lead & Cartridge Fuses**

5×20 mm > Fast-Acting > 216 Series

# 216 Series, 5×20 mm, Fast-Acting Fuse Rolls 🕫 🕼 🐨 🐨 🐨 🛆 🛆



#### **Agency Approvals**

Agency	Agency File Number	Ampere Range			
	Cartridge: 1-5A NBK 080205-E10480A 6.3A-10A NBK 250702-E10480E 12.5A NBK 240108-JP1021C 16A NBK 240108-JP1021E Leaded: 1-5A NBK 080205-E10480B 6.3A-10A NBK 250702-E10480F 12.5A NBK 240108-JP1021D 16A NBK 240108-JP1021F	1A – 16A			
(	2003010207079960	0.05A – 6.3A			
<u>S</u>	SU05001-2013	1A – 10A			
c <b>FL</b> °us	E10480	0.05A – 16A			
SP.	29862	0.05A - 16A			
$(\mathbb{Z})$	1402843	0.05A - 10A, 16A			
	40013834	0.05A – 6.3A *8A, *10A			
VDE	40016442	*12.5A			
$\overleftarrow{\nabla}$	KM41462	1A – 6.3A			
$\Delta$	J50248090	8A – 16A			
Œ	N/A	0.05A – 16A			

\*Approval for Cartridge versions only

#### Description

5×20mm fast-acting ceramic body cartridge fuse designed to IEC specification.

#### Features

- Designed to International (IEC) Standards for use globally
- Meets the IEC 60127-2, sheet 1 specification for fast-acting fuses
- Available in cartridge and axial lead form
- RoHS compliant and lead-free

#### Applications

Used as supplementary protection in appliance or utilization equipment to provide individual protection for components or internal circuits.

#### **Electrical Characteristics for Series**

% of Ampere Rating	Ampere Rating	<b>Opening Time</b>					
	0.05A – 4A	60 minutes, Minimum					
150%	5A – 6.3A	60 minutes, Minimum					
	8A – 16A	30 minutes, Minimum					
	0.05A – 4A	30 minutes, Maximum					
210%	5A – 6.3A	30 minutes, Maximum					
	8A – 16A	30 minutes, Maximum					
	0.05A – 4A	0.01 sec, Min.; 2 sec. Max.					
275%	5A – 6.3A	0.01 sec, Min.; 3 sec. Max.					
	8A – 16A	0.04 sec., Min.; 20 sec. Max.					
	0.05A – 4A	.003 sec., Min.; 0.3 sec. Max.					
400%	5A – 6.3A	.003 sec., Min.; 0.3 sec. Max.					
	8A – 16A	.01 sec, Min.; 1.0 sec. Max.					
	0.05A – 4A	.02 seconds, Maximum					
1000%	5A – 6.3A	.02 seconds, Maximum					
	8A – 16A	.03 sec.onds, Maximum					

#### **Additional Information**







For recommended fuse accessories for this product series, see '<u>Recommended Accessories</u>' section.



## **Axial Lead & Cartridge Fuses**

5×20 mm > Fast-Acting > 216 Series

				Maximum Maximum	Agency Approvals													
Amp Code	Amp Rating (A)	Voltage Rating (V)	Interrupting Rating	Nominal Cold Resistance (Ohms)	Nominal Melting I²t (A² sec)	Melting Drop at Dissapation	Dissapation at 1.5In	Ŷ	K	۲	c <b>W</b> us	SP:	$\bigcirc$	CE	DE	VDE	4	<b>₽</b> ₽ ₩
.050	0.05	250		15.9000	0.00019	10000	1.6			х	х	х	х	х	х			
.063	0.063	250		10.4500	0.00079	8800	1.6			х	x	х	х	х	х			
.080	0.08	250		7.8850	0.00084	7600	1.6			Х	х	х	х	х	X			
.100	0.1	250		5.7925	0.00450	7000	1.6			х	x	х	х	х	х			
.125	0.125	250	1	3.6750	0.00546	5000	1.6			х	х	х	x	Х	X			
.160	0.16	250	1	5.3490	0.00326	4300	1.6			х	X	х	x	Х	x			
.200	0.2	250	1	3.3500	0.00439	3500	1.6			х	X	Х	x	Х	x			
.250	0.25	250	1	2.3500	0.01350	2800	2.5			х	х	х	x	Х	x			
.315	0.315	250	1500A@	1.8500	0.02320	2500	2.5			х	х	Х	x	Х	x			
.500	0.5	250		0.8660	0.16500	1800	2.5			х	X	х	х	х	х			
.630	0.63	250		0.4650	0.05940	1500	2.5			Х	X	Х	X	Х	X			
.800	0.8	250		0.2950	0.14600	1200	2.5			Х	X	Х	X	х	X			
001.	1	250	250Vac	0.2370	0.18000	1000	2.5	Х	х	Х	X	Х	X	Х	X			Х
1.25	1.25	250		0.1530	0.48000	800	4	Х	х	Х	X	Х	X	х	X			х
01.6	1.6	250		0.1112	1.00500	600	4	Х	Х	Х	х	Х	х	Х	X			Х
002.	2	250		0.0764	1.87000	500	4	Х	Х	Х	х	Х	х	Х	X			Х
02.5	2.5	250		0.0584	3.67200	400	4	Х	Х	Х	х	Х	х	Х	X			Х
3.15	3.15	250		0.0368	6.70000	350	4	х	х	х	х	х	х	х	х			х
004.	4	250		0.0247	14.99500	300	4	х	х	х	x	Х	х	х	х			х
005.	5	250		0.0183	27.46000	250	4	х	х	х	х	х	х	х	х			х
06.3	6.3	250		0.0137	56.43000	200	4	х	х	Х	X	Х	х	х	х			х
008.	8	250		0.0123	64.31500	200	4		X		х	х	х	х	X*		Х	х
010.	10	250		0.0079	154.34000	200	4		х		X	Х	х	х	X*		Х	х
12.5	12.5	250		0.0057	175.00000	200	N/A**				х	х		х		×*	Х	х
016.	16	250	750A@ 250Vac	0.0040	462.50000	200	N/A**				x***	x	x	x			x***	x

\* Approval for cartidge versions only.


N/A\*\* - Please contact Littelfuse for details on these parameters

I<sup>2</sup>t test at 10x rated current \*\*\*1500A@250Vac for 16A

**Temperature Re-rating Curve** 140 1 120 i PERCENT OF RATING 100 Т 80 i 1 60 1 25°C 40 ī 1 20 20°C 40°C 60°C 80°C 100°C 120°C 68°F 104°F 140°F 176°F 212°F 248°F -60°C -40°C -76°F -40°F -20°C -4°F 0°C 32°F AMBIENT TEMPERATURE

Note: Rerating depicted in this curve is in addition to the standard derating of 25% for continuous operation.

### Average Time Current Curves




<sup>© 2019</sup> Littelfuse, Inc. Specifications are subject to change without notice. Revised: 07/30/19



### **Axial Lead & Cartridge Fuses**

5×20 mm > Fast-Acting > 216 Series

#### **Soldering Parameters - Wave Soldering**



#### **Recommended Process Parameters:**

Wave Parameter	Lead-Free Recommendation
Preheat: (Depends on Flux Activation Temperature)	(Typical Industry Recommendation)
Temperature Minimum:	100°C
Temperature Maximum:	150°C
Preheat Time:	60-180 seconds
Solder Pot Temperature:	260°C Maximum
Solder Dwell Time:	2-5 seconds

#### **Recommended Hand-Solder Parameters:**

Solder Iron Temperature: 350°C +/- 5°C Heating Time: 5 seconds max.

Note: These devices are not recommended for IR or Convection Reflow process.

#### **Product Characteristics**

Material	Body: Ceramic Cap: Nickel-plated brass Leads: Tin-plated Copper Filler (160mA-16A): Sand
Terminal Strength	MIL-STD-202, Method 211, Test Condition A
Solderability	MIL-STD-202 Method 208
Product Marking	Cap 1: Brand logo, current and voLage rating Cap 2: Agency approval markings
Packaging	Available in Bulk (M=1000 pcs/pkg) or on Tape/Reel (MRET1=1000 pcs/reel)

Operating Temperature	–55°C to +125°C
Thermal Shock	MIL-STD-202, Method 107, Test Condition B: (5 cycles –65°C to +125°C)
Vibration	MIL-STD-202, Method 201
Humidity	MIL-STD-202, Method 103, Test Condition A. high RH (95%) and elevated temperature (40°C) for 240 hours.
Salt Spray	MIL-STD-202, Method 101, Test Condition B



### **Axial Lead & Cartridge Fuses**

Part Numbering System

Series

Amp Code

Quantity Code

M = 1000

X = Filler

**Option Codes** 

E

Lead-free

**Packaging Code** 

Refer to Amp Code column of


**Electrical Characteristics Table** 

Blank : Cartidge Type Fuse

: Axial Leaded Fuse

0216 xxxx M X E P

5×20 mm > Fast-Acting > 216 Series



All dimensions in mm

Notes:

Ratings above 6.3 A have 0.8 ± 0.05 diameter lead.

#### Packaging

Packaging Option	Packaging Specification	Quantity	Quantity & Packaging Code	Taping Width	
		216 Series			
Bulk	N/A	1000	MX	N/A	
Bulk	N/A	1000	MXE	N/A	
Reel and Tape	EIA 296-E	1000	MRET1	T1=53mm (2.087")	
Bulk	N/A	1000	MXG	N/A	
Bulk	N/A	1000	MXB	N/A	
Bulk	N/A	100	HX	N/A	

#### **Recommended Accessories**

Accessory Type	Series	Description	Max Application Voltage	Max Application Amperage
	<u>345_ISF</u>	Panel Mount Shock-Safe Fuseholder		10
Holder	<u>345</u>	Shock-Safe Fuseholder with PC Mount, Solder Mount and Panel Mount options		20A
830   520   Block 646	<u>830</u>	PC Mount Shock-Safe Miniature Fuseholder		16
	<u>520</u>	Metric OMNI-BLOK® Fuse Block		10
	PC Mount Miniature Fuse Block	250	6.3	
-	<u>658</u>	Surface Mount Miniature Fuse Block		10
	<u>520_W</u>	PC Mount Miniature Fuse Clip		6.3
Clip	<u>111</u>	PC Board Mount Fuse Clip		10
	445	PC Board Mount Fuse Clip		10

Notes: Do not use in applications above rating.

2. Please refer to fuseholder data sheet for specific re-rating information.

3. Please contact Littelfuse for applications greater than the max voltage and amperage shown.

Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at: www.littelfuse.com/disclaimer-electronics.