




REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	C9	HOUSING COLOR ADDED	03OCT2019	RK	PS
	C10	PART OBSOLETE	02AUG2021	GMN	PS




282925-3 AS SHOWN



9	SEE DETAIL F	60.96	12	2-282925-3
9	SEE DETAIL E	76.20	15	2-282925-2
12/10/9	SEE DETAIL D	106.68	21	2-282925-1
12/10/9	SEE DETAIL C	76.20	15	1-282925-5
12/9	SEE DETAIL B	60.96	12	1-282925-2
8/7	OBSOLETE	828.04	163	1-282925-0
	OBSOLETE	15.24	3	282925-3
	OBSOLETE	10.16	2	282925-2
	DIM.A		NO OF POS.	PART NUMBER


RECOMMENDED PC BOARD LAYOUT



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm	
0 PLC	±
1 PLC	±0.3
2 PLC	±0.25
3 PLC	±
4 PLC	±
ANGLES	±2°
MATERIAL	FINISH
SEE NOTES	SEE NOTES

DWN	09NOV2001
E. ZANOLINI	
CHK	09NOV2001
D. BIEVENOUR	
APVD	09NOV2001
D. BIEVENOUR	
PRODUCT SPEC	-
APPLICATION SPEC	-
WEIGHT	-
CUSTOMER DRAWING	



NAME			
TERMINAL BLOCK, PCB MOUNT			
3RD LEVEL, STACKING W/INTERLOCK,			
5.08mm PITCH			
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-282925	-
SCALE		SHEET	REV
2:1		1 OF 4	C10

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

DETAIL D
SCALE 2:1

DETAIL C
SCALE 2:1

DETAIL B
SCALE 2:1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC	±	0.3
1 PLC	±	0.3
2 PLC	±	0.25
3 PLC	±	
4 PLC	±	
ANGLES	±	2°

MATERIAL
SEE NOTES

FINISH
SEE NOTES

DWN 09NOV2001

E. ZANOLINI

CHK 09NOV2001

D. BIEVENOUR

APVD 09NOV2001

D. BIEVENOUR

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

-

CUSTOMER DRAWING

TE Connectivity

NAME
TERMINAL BLOCK, PCB MOUNT
3RD LEVEL, STACKING W/INTERLOCK,
5.08mm PITCH

SIZE CAGE CODE DRAWING NO

A300779 C-282925

RESTRICTED TO

-

SCALE 2:1

SHEET 2 OF 4

REV C10

1470-19 (3/13)

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION


20

© COPYRIGHT 20 BY -


ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



DETAIL E
SCALE 2:1



DETAIL F
SCALE 2:1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm	

TOLERANCES UNLESS OTHERWISE SPECIFIED:	
0 PLC	±
1 PLC	±0.3
2 PLC	±0.25
3 PLC	±
4 PLC	±
ANGLES	±2°
FINISH	SEE NOTES

MATERIAL
SEE NOTES

DWN	09NOV2001
E. ZANOLINI	
CHK	09NOV2001
D. BIEVENOUR	
APVD	09NOV2001
D. BIEVENOUR	
PRODUCT SPEC	-
APPLICATION SPEC	-
WEIGHT	-

		TE Connectivity	
NAME TERMINAL BLOCK, PCB MOUNT 3RD LEVEL, STACKING W/INTERLOCK, 5.08mm PITCH			
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A300779	C	282925	-

CUSTOMER DRAWING SCALE 2:1 SHEET 3 OF 4 REV C10

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
-		SEE SHEET 1	-	-	-

- 1. MATERIALS AND FINISH
HOUSING: PA 66, UL 94-V0, COLOR: GREEN.
CLAMP: BRASS, NICKEL PLATED.
TERMINAL: BRASS, TIN PLATED.
CLAMPING SCREW: M3, BRASS, NICKEL PLATED.
- 2. MECHANICAL:
RECOMENDED TIGHTENING TORQUE : 0.5Nm
WIRE STRIPPING LENGTH : 6.5-7.0mm
MIN. PC BOARD HOLES DIAMETER : 1.4mm
MAX. PC BOARD THICKNESS : 2.4mm
- 3. ELECTRICAL
WIRE RANGE : 16-30 AWG
MAX. VOLTAGE : 300 V
MAX CURRENT : 24 A
CONTACT RESISTANCE : < 15 m Ohm
INSULATION RESISTANCE : > 1000 M Ohm (500V DC)

- 4. OPERATING TEMPERATURE RANGE: -40C TO +105C.
- 5. RECOGNIZED UNDER THE COMPONENT PROGRAM OF UNDERWRITERS LABORATORIES INC., FILE NO E60677

- 6. NOT CUMULATIVE TOLERANCE.
- 7. P/N 1-282925-0 IS A KIT PACKAGE COMPRISED OF THE FOLLOWING:(3) OF 25 POS. GLUED ASSEMBLIES AND (4) OF 22 POS. GLUED ASSEMBLIES. EACH GLUED ASSEMBLY IS PACKAGED SEPERATLY IN A UNIT BOX.
- 8. INK MARKING, BLACK COLOR. NUMERICAL SEQUENCE: FROM LEFT TO RIGHT FOR EACH GLUED ASSEMBLY.
- 9. INK MARKING, BLACK COLOR. SEE DETAIL FOR MARKING.
- 10. PARTS TO BE SHIPPED WITH CAGES IN THE CLOSED POSITION WITH SCREW TORQUE TO 3 IN-16s MIN.
- 11. DELETED
- 12. SECTION GLUED USING CYANOLIT 241F OR TE ENGINEERING APPROVED EQUIVALENT.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN E. ZANOLINI 09NOV2001	STE TE Connectivity	
DIMENSIONS: mm		CHK D. BIEVENOUR 09NOV2001		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD D. BIEVENOUR 09NOV2001	NAME TERMINAL BLOCK, PCB MOUNT 3RD LEVEL, STACKING W/INTERLOCK, 5.08mm PITCH	
		PRODUCT SPEC -	RESTRICTED TO -	
MATERIAL SEE NOTES		FINISH SEE NOTES	APPLICATION SPEC -	SIZE A300779
		WEIGHT -	DRAWING NO C-282925	SCALE 2:1
		CUSTOMER DRAWING	SHEET 4 OF 4	REV C10

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-282925-2](#)