

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0475901001**
Status: **Active**
Overview: USB Products and Solutions
Description: Micro-USB AB Receptacle, Right-Angle, Top Mount, Surface Mount, Lead-Free

Documents:

[3D Model](#) [Product Specification PS-47589-001-001 \(PDF\)](#)
[3D Model \(PDF\)](#) [Packaging Specification PK-47589-001-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E107635

General


Product Family I/O Connectors
Series [47590](#)
Application Wire-to-Board
Comments Signal contacts 1.0A, Power contacts 1.8A
Component Type Receptacle
Electrical Model Yes
Overview [USB Products and Solutions](#)
Product Name USB 2.0
Type Micro-AB
UPC 884982783737

Physical

Boot Color N/A
Circuits (Loaded) 5
Circuits (maximum) 5
Color - Resin Gray
Durability (mating cycles max) 10000
Flammability 94V-0
Gender Female
Keying to Mating Part Yes
Lock to Mating Part No
Material - Metal Copper Alloy
Material - Plating Mating Gold
Material - Plating Termination Gold
Material - Resin High Temperature Thermoplastic
Net Weight 0.263/g
Number of Rows 1
Orientation Right Angle
PCB Retention None
Packaging Type Embossed Tape on Reel
Panel Mount No
Pitch - Mating Interface 0.65mm
Pitch - Termination Interface 0.65mm
Polarized to Mating Part Yes
Ports 1
Surface Mount Compatible (SMC) Yes
Temperature Range - Operating -30° to +85°C
Termination Interface: Style Surface Mount
Waterproof / Dustproof No

Electrical

Current - Maximum per Contact 1.8A, 1.0A
Grounding to Panel Yes



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)4578-DC (25
June 2020)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[47590 Series](#)

Shield Type	Full Shield
Shielded	Yes
Voltage - Maximum	30V AC (RMS)

Solder Process Data

Duration at Max. Process Temperature (seconds)	010
Lead-freeProcess Capability	REFLOW
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	245

Material Info**Reference - Drawing Numbers**

Electrical Model Document	EE-47590-001
Packaging Specification	PK-47589-001-001
Product Specification	PS-47589-001-001
S-Parameter Model	SP-47590-001
Sales Drawing	SD-47590-101

This document was generated on 08/07/2020

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION