

FLK 20/EZ-DR/ 200KONFEK - Cable



2296485

<https://www.phoenixcontact.com/us/products/2296485>

Please be informed that the data shown in this PDF document is generated from our Online Catalog. Please find the complete data in the user documentation. Our General Terms of Use for Downloads are valid.



Round cable set; connection 1: IDC/FLK socket strip (1x 20-position); connection 2: IDC/FLK socket strip (1x 20-position); cable length: 2 m

Your advantages

- Unshielded

Commercial Data

Item number	2296485
Packing unit	1 pc
Minimum order quantity	1 pc
Sales Key	C421
Product Key	CK2131
Catalog Page	Page 566 (C-5-2019)
GTIN	4017918570002
Weight per Piece (including packing)	170.4 g
Weight per Piece (excluding packing)	160 g
Customs tariff number	85444290
Country of origin	DE

Technical Data

Product properties

Product type	System cable
Insulation characteristics	
Insulation	Functional insulation
Insulation characteristics: Air clearances and creepage distances	
Insulation	Functional insulation
Overvoltage category	II
Pollution degree	2

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP00
Degree of protection (Installation location)	≥ IP54 (Installation location)
Ambient temperature (operation)	-40 °C ... 70 °C (fixed installation) -10 °C ... 70 °C (flexible installation)
Ambient temperature (storage/transport)	-40 °C ... 80 °C
Altitude	≤ 2000 m

Electrical properties

Max. permissible operating voltage	25 V AC
	60 V DC
Nominal operating mode	100% operating factor
Max. current carrying capacity per path	1 A (50 °C)
	0.6 A (70 °C)

Air clearances and creepage distances

Rated insulation voltage	63 V
Rated surge voltage	0.6 kV

Cable/line

Cable length	2 m
--------------	-----

20X0.14 [PVC]

UL AWM Style	2464/1061
Number of positions	20
Shielded	no
Cable type	20X0.14 [PVC]
Conductor type	Round cable set
Conductor structure signal line	7x 0.16 mm
AWG signal line	26
Conductor cross section	20x 0.14 mm ²

FLK 20/EZ-DR/ 200KONFEK - Cable



2296485

<https://www.phoenixcontact.com/us/products/2296485>

Wire diameter incl. insulation	1 mm ±0.03 mm
External cable diameter	7.6 mm ±0.4 mm
Outer sheath, material	Semi-rigid PVC
External sheath, color	gray
Conductor material	Tin-plated Cu litz wires
Cable resistance	≤ 145 Ω/km (20 °C)
Insulation resistance	≥ 20 MΩ*km (20 °C)
Smallest bending radius, fixed installation	64 mm
Smallest bending radius, movable installation	120 mm
Max. bending cycles	5000 (at a radius of ≥ 15x outside diameter)
Halogen-free	no
Flame resistance	IEC 60332-1-2 (raw cable)
	VDE 0842, Part 332-1-2 (raw cable)
	IEC 60332-3-22 (raw cable)
	UL VW-1
	CSA FT-1
Resistance to oil	can withstand occasional splashes (raw cable)
Type	Cable for one module
Cable, preassembly	Insulation displacement, IEC 60352-4/DIN EN 60352-4

color code

IDC/FLK20 (1)	IDC/FLK20 (1) = black
IDC/FLK20 (2)	IDC/FLK20 (2) = brown
IDC/FLK20 (3)	IDC/FLK20 (3) = red
IDC/FLK20 (4)	IDC/FLK20 (4) = orange
IDC/FLK20 (5)	IDC/FLK20 (5) = yellow
IDC/FLK20 (6)	IDC/FLK20 (6) = green
IDC/FLK20 (7)	IDC/FLK20 (7) = blue
IDC/FLK20 (8)	IDC/FLK20 (8) = violet
IDC/FLK20 (9)	IDC/FLK20 (9) = gray
IDC/FLK20 (10)	IDC/FLK20 (10) = white
IDC/FLK20 (11)	IDC/FLK20 (11) = white-black
IDC/FLK20 (12)	IDC/FLK20 (12) = white-brown
IDC/FLK20 (13)	IDC/FLK20 (13) = white-red
IDC/FLK20 (14)	IDC/FLK20 (14) = white-orange
IDC/FLK20 (15)	IDC/FLK20 (15) = white-yellow
IDC/FLK20 (16)	IDC/FLK20 (16) = white-green
IDC/FLK20 (17)	IDC/FLK20 (17) = white-blue
IDC/FLK20 (18)	IDC/FLK20 (18) = white-violet
IDC/FLK20 (19)	IDC/FLK20 (19) = white-gray
IDC/FLK20 (20)	IDC/FLK20 (20) = brown-black

Connection data

Field level

FLK 20/EZ-DR/ 200KONFEK - Cable



2296485

<https://www.phoenixcontact.com/us/products/2296485>

Connection in acc. with standard	IEC 60603-13
Connection method	IDC/FLK socket strip
Number of connections	1
Number of positions	20
Insertion/withdrawal cycles	> 50
Pitch	2.54 mm

Controller level

Connection in acc. with standard	IEC 60603-13
Connection method	IDC/FLK socket strip
Number of connections	1
Number of positions	20
Insertion/withdrawal cycles	> 50
Pitch	2.54 mm


Standards and regulations

Air clearances and creepage distances

Standards/regulations	DIN EN 50178
-----------------------	--------------

Drawings

Diagram



Maximum permissible current per path in uncoiled state

FLK 20/EZ-DR/ 200KONFEK - Cable



2296485

<https://www.phoenixcontact.com/us/products/2296485>

Approvals



EAC

Approval ID: RU*-DE.HB*35.B00385



UL Listed

Approval ID: FILE E 238705

	Nominal Voltage U_N	Nominal Current I_N	Cross Section AWG	Cross Section mm^2
	125 V	1 A	-	-



cUL Listed

Approval ID: FILE E 238705

	Nominal Voltage U_N	Nominal Current I_N	Cross Section AWG	Cross Section mm^2
	125 V	1 A	-	-

cULus Listed

FLK 20/EZ-DR/ 200KONFEK - Cable



2296485

<https://www.phoenixcontact.com/us/products/2296485>

Classifications

ECLASS

ECLASS-9.0	27242220
ECLASS-10.0.1	27242220
ECLASS-11.0	27242220
ECLASS-12.0	27242220
ECLASS-13.0	27242220

ETIM

ETIM 8.0	EC000237
----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

FLK 20/EZ-DR/ 200KONFEK - Cable



2296485

<https://www.phoenixcontact.com/us/products/2296485>

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

FLK 20/EZ-DR/ 200KONFEK - Cable

2296485

<https://www.phoenixcontact.com/us/products/2296485>



Accessories

KME - Cable marker carrier

0807083

<https://www.phoenixcontact.com/us/products/0807083>



Cable marker carrier, white, unlabeled, mounting type: Assembly with cable ties, cable diameter: > 5 mm, lettering field size: 20 x 8 mm

Phoenix Contact 2023 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road

Middletown, PA 17057, United States

(+717) 944-1300

info@phoenixcon.com