



Search by part # or keyword

Products

Industries & Solutions

Resources

TE Store

Sign In



Relays, Contactors & Switches > Relays > Mil-Aero Relays > Mid-Range

5-1617806-1

FC-325-SY8= RELAY, 3PST



CII | CII FC-325

TE Internal #: **5-1617806-1**

TE Internal Description: **FC-325-SY8= RELAY, 3PST**

Alias #: **FC-325-SY8**

Contact Arrangement : **3 Form X, 3PST-NO-DM**

Coil Suppression Diode : **Without**

Auxiliary Contacts : **Without**

Contact Current Rating (A): **25**

Coil Voltage Rating (VAC): **115**

[Compatible Parts & Tooling](#)

Purchase items directly from TE.com

Free Shipping to select countries. Exclusions apply. See complete details at [TE Store FAQs](#)

QTY:

Extended Price:

We are here to help!

Get in touch with our product experts.



[CHAT WITH US](#)



[EMAIL US](#)



[CALL US](#)

Documents

Features

Product Compliance

Product Drawings

FC-325-SY8= RELAY, 3PST

[FC-325-SY8= RELAY, 3PST](#) English

CAD Files

3D PDF

[3D_CVM_CVM_5-1617806-1_A.pdf](#) 3D

Customer View Model

[ENG_CVM_CVM_5-1617806-1_A.2d_dxf.zip](#)

English

[ENG_CVM_CVM_5-1617806-1_A.3d_igs.zip](#)

English

[ENG_CVM_CVM_5-1617806-1_A.3d_stp.zip](#)

English

Datasheets & Catalog Pages

CII FC-325 Series Relay

[ENG_DS_1-1773871-3_fc325_0417.pdf](#) English

Please review product documents or [contact us](#) for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.

Product Type Features

Terminal Configuration : **Screw**

Electrical
Characteristics

Coil Suppression Diode : **Without**
Coil Voltage Rating (VAC): **115**
Coil Current (A): **.55**
Contact Switching (Max) : **115/200Vac (50-400Hz)**
Back EMF Suppression : **Without**

Contact Features

Contact Arrangement : **3 Form X, 3PST-NO-DM**
Auxiliary Contacts : **Without**
Contact Current Rating (A): **25**
Contact Base Material :
Silver Cadmium Oxide with Gold Plating

Mechanical
Attachment

Mounting Type : **Raised Vertical Flange Mount**

Usage Conditions

Operating Temperature Range : **-70 – 125 °C [-94 – 257 °F]**

