

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0348050111](#)
Status: **Active**
Overview: [CTX Crimp Terminals](#)
Description: CTX150 Female Terminal, Tin (Sn), 22 AWG D-Wind, Left Payoff, Grip Code S

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Application Specification AS-34805-001 \(PDF\)](#)

General

Product Family Crimp Terminals
 Series [34805](#)
 Application Power
 Crimp Quality Equipment Yes
 Overview [CTX Crimp Terminals](#)
 Product Name CTX150
 UPC 884982651166

Physical

Durability (mating cycles max) 10
 Gender Female
 Material - Metal Copper Alloy
 Material - Plating Mating Tin
 Material - Plating Termination Nickel
 Net Weight 0.224/g
 Packaging Type Reel
 Termination Interface: Style Crimp or Compression
 Wire Insulation Diameter 2.80mm
 Wire Size AWG 22
 Wire Size mm² 0.35-0.50

Electrical

Current - Maximum per Contact 15.0A
 Voltage - Maximum 250V


Solder Process Data

Lead-freeProcess Capability N/A

Material Info

Reference - Drawing Numbers

Application Specification AS-34805-001
 Sales Drawing SD-34805-001



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 ED/21/2016 (20 June
 2016)

Halogen-Free

Status

Not Relevant

**Need more information on product
 environmental compliance?**

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any
 non-product compliance questions.

China ROHS

ELV

China RoHS

Not Relevant

Compliant

Search Parts in this Series

[34805 Series](#)

Application Tooling | [FAQ](#)

*Tooling specifications and manuals are
 found by selecting the products below.
 Crimp Height Specifications are then
 contained in the Application Tooling
 Specification document.*

Global

Description	Product #
Hand Crimp Tool for CTX 1.50mm Receptacle Terminal, 0.30, 0.35, and 0.50mm ² Wires	0638193900
FineAdjust™ Applicator for CTX150 Receptacle Terminals, 0.30mm ² , 0.35mm ² , & 0.50mm ²	0639010400

This document was generated on 09/21/2016

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION