




KEB-1025 is a crimping tool for endsleeves according to DIN 46228, 10 mm² - 25 mm²/AWG 6-4, side feeded, Trapez-Crimp.

- High strength, through hardened alloy steel construction
- Unique mechanism significantly reduces hand force requirement over competing crimping tools
- Versatile and easy to customize for right hand or left hand users.
- Non-slip pad holds tool in place when leveraging on a work surface
- Full cycle crimp mechanism to ensure consistent, reliable crimp
- Ratchet release mechanism to clear miscrimps and obstructions
- Precision eccentric adjustment for consistent performance and ability to calibrate
- · Hole in handle allows attachment of safety strap
- Each tool has a unique serial number for traceability

Tool shown is an example only, for correct die profile please look at the illustration to the right.





Crimp profile

TECHNICAL DATA

Length: 256 mm/10.08" Width: 22 mm/0.87" Height: 80 mm/3.15" Weight: 570 gr/1.26 lb Wire size: 10-25 mm² / AWG 6-AWG 4 Crimp dimensions mm/mm²: 10 mm²/16 mm²/25 mm² Crimp dimensions inch/AWG: (AWG 5)/AWG 6/AWG 4 Connector: Endsleeves Description: For endsleve connectors, both uninsulated and insulated. Life span, cycles: 50,000

Pressmaster AB P.O. Box 3, Industrivägen SE-796 21 Älvdalen, Sweden Tel: +46 (0)251-451 00 info@pressmaster.se www.pressmaster.com