


## BTA24, BTB24, T25

### Datasheet

## 800 V and 600 V, 25 A standard and Snubberless Triacs



### **Features**

- High current 25 A RMS current Triac
- Low thermal resistance
- High commutation (4 quadrants) or very high commutation (3 quadrants) capability
- BTA series UL1557 recognized components (file ref: 81734)
- RoHS (2002/95/EC) compliant packages
- UL-94, V0 flammability package resin compliance

### **Applications**

- On/off function in static relays, heating regulation, induction motor starting circuits
- Phase control operations in light dimmers and motor speed controllers

### **Description**

Available either in through-hole or surface-mount packages, the BTA24, BTB24 and T25 are suitable for general purpose AC switching.



Product status link				
BTA24	TO-220AB insulated package			
BTB24	TO-220AB uninsulated package			
T25	D <sup>2</sup> PAK package			

Product summary					
	BTA24	BTB24	T25		
I <sub>T(RMS)</sub>	25 A				
V <sub>DRM</sub> /V <sub>RRM</sub>	600 V and 800 V				
l <sub>GT</sub> Snubberless	35 / 50 mA 35 r		35 mA		
I <sub>GT</sub> standard		50 mA			

### 1 Characteristics

Symbol	Parameters	Parameters							
I <sub>T(RMS)</sub>	RMS on-state current (full sine wave)	D <sup>2</sup> PAK / TO-220AB T <sub>c</sub> = 100 °C		25	А				
		TO-220AB Ins.	T <sub>c</sub> = 75 °C						
I <sub>TSM</sub>	Non repetitive surge peak on-state current (full cycle,	f = 60 Hz	t <sub>p</sub> = 16,7 ms	260	Α				
ISM	T <sub>j</sub> initial = 25 °C)	f = 50 Hz	t <sub>p</sub> = 20 ms	250	A				
l <sup>2</sup> t	I <sup>2</sup> t value for fusing	340	A <sup>2</sup> s						
dl/dt	Critical rate of rise of on-state current $I_G = 2 \times I_{GT}$ , $t_r \le 100 \text{ ns}$	f = 120 Hz	T <sub>j</sub> = 125 °C	50	A/µs				
$V_{DSM}, V_{RSM}$	Non repetitive surge peak off-state voltage	t <sub>p</sub> = 10 ms	T <sub>j</sub> = 25 °C	V <sub>DRM</sub> , V <sub>RRM</sub> + 100	V				
$V_{DRM}, V_{RRM}$	Repetitive peak off-state voltage		T <sub>j</sub> = 25 °C	600 or 800	V				
I <sub>GM</sub>	Peak gate current	t <sub>p</sub> = 20 μs	T <sub>j</sub> = 125 °C	4	Α				
P <sub>G(AV)</sub>	Average gate power dissipation		T <sub>j</sub> = 125 °C	1	W				
T <sub>stg</sub>	Storage junction temperature range		-40 to +150	°C					
Тj	Operating junction temperature range	-40 to +125	°C						
TL	Maximum lead temperature for soldering during 10 s		260	°C					
V <sub>INS</sub>	Insulation RMS voltage, 1 minute			2.5	kV				

#### Table 1. Absolute maximum ratings

# Table 2. Electrical characteristics (Tj = 25 °C, unless otherwise specified) - Snubberless (3 quadrants) T25,BTA24-XXXXW, BTB24-XXXXW

Symbol	Parameters	Quadrant		T25	BTA/BTB		Unit
Symbol	Farameters	Quadrant		T2535	cw	BW	Unit
I <sub>GT</sub> <sup>(1)</sup>	$V_{D} = 12 V, R_{I} = 33 \Omega$	1 - 11 - 111	Max.	35	35	50	mA
V <sub>GT</sub>	vD - 12 v, KL - 33 12	1 - 11 - 111	Max.	1.3		V	
V <sub>GD</sub>	$V_D = V_{DRM}, R_L = 3.3 \text{ k}\Omega, T_j = 125 \text{ °C}$ I - II - III			0.2			V
I <sub>H</sub> <sup>(2)</sup>	I <sub>T</sub> = 500 mA	Max.	50	50	75	mA	
IL.	I <sub>G</sub> = 1.2 I <sub>GT</sub>	1 - 111	Max.	70	70	80	mA
ч <u></u>		II	Max.	80	80	100	IIIA
dV/dt <sup>(2)</sup>	$V_D$ = 67 % $V_{DRM}$ gate open, $T_j$ = 125 °C			500	500	1000	V/µs
(dl/dt)c <sup>(2)</sup>	Without snubber		Min.	13	13	22	A/ms

1. Minimum  $I_{GT}$  is guaranteed at 5 % of  $I_{GT}$  max.

2. For both polarities of A2 referenced to A1

Symbol	Parameters	Quadrant		Value	Unit
I <sub>GT</sub> <sup>(1)</sup>		1 - 11 - 111	Max.	50	
'GT` ′	$V_D$ = 12 V, $R_L$ = 33 $\Omega$	IV	IVIAX.	100	mA
V <sub>GT</sub>		All	Max.	1.3	V
V <sub>GD</sub>	$V_D = V_{DRM}$ , $R_L = 3.3 \text{ k}\Omega$ , $T_j = 125 \text{ °C}$	All	Min.	0.2	V
I <sub>H</sub> <sup>(2)</sup>	I <sub>T</sub> = 500 mA		Max.	80	mA
IL.	$I_{G} = 1.2 I_{GT}$	I - III - IV	Max. 70		
ιL.	IG = 1.2 IGT	II	Max.	160	mA
dV/dt <sup>(2)</sup>	$V_D$ = 67 % $V_{DRM}$ gate open, $T_j$ = 125 °C		Min.	500	V/µs
(dV/dt)c <sup>(2)</sup>	(dl/dt)c = 13.3 A/ms, T <sub>j</sub> = 125 °C	Min.	10	V/µs	

# Table 3. Electrical characteristics (Tj = 25 °C, unless otherwise specified) - standard (4 quadrants)BTB24-800B, BTB24-600B

1. Minimum  $I_{GT}$  is guaranteed at 5 % of  $I_{GT}$  max.

2. For both polarities of A2 referenced to A1

#### Table 4. Static electrical characteristics

Symbol	Test conditions	Τj		Value	Unit
V <sub>TM</sub> <sup>(1)</sup>	I <sub>TM</sub> = 35 A, t <sub>p</sub> = 380 μs	25 °C	Max.	1.55	V
V <sub>TO</sub> <sup>(1)</sup>	threshold on-state voltage	125 °C	Max.	0.85	V
R <sub>D</sub> <sup>(1)</sup>	Dynamic resistance	125 °C	Max.	16	mΩ
I <sub>DRM</sub> /I <sub>RRM</sub>	$V_T = V_{DRM}, V_T = V_{RRM}$	25 °C	Max.	5	μA
	I UKM; I KKM	125 °C	ividX.	3	mA


1. For both polarities of A2 referenced to A1

#### Table 5. Thermal resistance

Symbol	Pa	Value	Unit		
P	lupation to appa (AC)	D <sup>2</sup> PAK / TO-220AB	Max.	0.8	
R <sub>th(j-c)</sub>	Junction to case (AC)	TO-220AB insulated	iviax.	1.7	°C/W
Du a v	Junction to ambient, $S^{(1)} = 2.5 \text{ cm}^2$	D <sup>2</sup> PAK	Tun	45	C/vv
R <sub>th(j-a)</sub>	Junction to ambient	TO-220AB / TO-220AB insulated	Тур.	60	

1. S = Copper surface under tab.

### 1.1 Characteristics (curves)







Figure 4. Relative variation of thermal impedance versus pulse duration









Figure 6. Surge peak on-state current versus number of cycles









57/






Figure 10. Relative variation of critical rate of decrease of main current versus junction temperature (typical values)








### 2 Package information

In order to meet environmental requirements, ST offers these devices in different grades of ECOPACK packages, depending on their level of environmental compliance. ECOPACK specifications, grade definitions and product status are available at: www.st.com. ECOPACK is an ST trademark.

### 2.1 TO-220AB package information

- Molding compound resin is halogen free and meets UL94 flammability standard, level V0
- Lead-free plating package leads
- Recommended torque: 0.4 to 0.6 N·m





(1)Resin gate position accepted in one of the two positions or in the symmetrical opposites.

	Dimensions							
Ref.		Millimeters		Inches <sup>(1)</sup>				
	Min.	Тур.	Max.	Min.	Тур.	Max.		
А	15.20		15.90	0.5984		0.6260		
a1		3.75			0.1476			
a2	13.00		14.00	0.5118		0.5512		
В	10.00		10.40	0.3937		0.4094		
b1	0.61		0.88	0.0240		0.0346		
b2	1.23		1.32	0.0484		0.0520		
С	4.40		4.60	0.1732		0.1811		
c1	0.49		0.70	0.0193		0.0276		
c2	2.40		2.72	0.0945		0.1071		
е	2.40		2.70	0.0945		0.1063		
F	6.20		6.60	0.2441		0.2598		
I	3.73		3.88	0.1469		0.1528		
L	2.65		2.95	0.1043		0.1161		
12	1.14		1.70	0.0449		0.0669		
13	1.14		1.70	0.0449		0.0669		
14	15.80	16.40	16.80	0.6220	0.6457	0.6614		
М		2.6			0.1024			

### Table 6. TO-220AB package mechanical data


1. Inch dimensions are for reference only.

### 2.2 D<sup>2</sup>PAK package information

•

57

- ECOPACK2 compliant
- Lead-free package leads finishing
- Molding compound resin is halogen-free and meets UL94 flammability standard level V0



### Figure 13. D<sup>2</sup>PAK package outline

(1) Resin gate is accepted in each of position shown on the drawing, or their symmetrical.

				Dimensions		
Ref.		Millimeters			Inches <sup>(1)</sup>	
	Min.	Тур.	Max.	Min.	Тур.	Max.
А	4.30		4.60	0.1693		0.1811
A1	2.49		2.69	0.0980		0.1059
A2	0.03		0.23	0.0012		0.0091
A3		0.25			0.0098	
b	0.70		0.93	0.0276		0.0366
b2	1.25		1.7	0.0492		0.0669
с	0.45		0.60	0.0177		0.0236
c2	1.21		1.36	0.0476		0.0535
D	8.95		9.35	0.3524		0.3681
D1	7.50		8.00	0.2953		0.3150
D2	1.30		1.70	0.0512		0.0669
е	2.54			0.10000		
E	10.00		10.28	0.3937		0.4047
E1	8.30		8.70	0.3268		0.3425
E2	6.85		7.25	0.2697		0.2854
G	4.88		5.28	0.1921		0.2079
Н	15		15.85	0.5906		0.6240
L	1.78		2.28	0.0701		0.0898
L2	1.19		1.40	0.0468		0.0551
L3	1.40		1.75	0.0551		0.0689
R		0.40			0.0157	
V2 <sup>(2)</sup>	0°		8°	0°		8°

### Table 7. D<sup>2</sup>PAK package mechanical data

1. Dimensions in inches are given for reference only

2. Degrees





Figure 14. D<sup>2</sup>PAK recommended footprint (dimensions are in mm)







### **3** Ordering information

51

#### Figure 16. Ordering information scheme (BTA24 and BTB24 series)



#### Figure 17. Ordering information scheme (T25 series)



(blank) = Tube -TR = Tape and reel

Order code	Order code Marking Package		Weig ht	Base qty.	Delivery mode
BTA24-600BWRG	BTA24 600BW				
BTA24-600CWRG	BTA24 600CW	TO-220AB insulated			
BTA24-800BWRG	BTA24 800BW	TO-220AB Insulated			
BTA24-800CWRG	BTA24 800CW				
BTB24-600BRG	BTB24 600B		22 ~	50	Tube
BTB24-600BWRG	BTB24 600BW		2.3 g	50	Tube
BTB24-600CWRG	BTB24 600CW				
BTB24-800BRG	BTB24 800B	TO-220AB			
BTB24-800BWRG	BTB24 800BW				
BTB24-800CWRG	BTB24 800CW				
T2535-600G	T2535 600G			50	Tube
T2535-600G-TR	T2535 600G	D²PAK	15 0	2500	Tape and reel
T2535-800G	T2535 800G	DTAN	1.5 g	50	Tube
T2535-800G-TR	T2535 800G			2500	Tape and reel

### **Revision history**

Date	Revision	Changes
Oct-2002	6A	Previous update.
13-Feb-2006	7	TO-220AB delivery mode changed from bulk to tube. ECOPACK statement added.
31-May-2006	8	Reformatted to current standard. Tc in figure 3 changed to Tamb
31-Jul-2006	9	Typing error corrected on page 1 (BTB124 instead of BTB24)
05-Jul-2007	10	Added BTB26-600BRG. Restructured cover page and section 2: Ordering information scheme on page 6 to simplify product selection. Thermal resistance values updated in Table 6 and Figure 2. Graphic for I2t updated in Figure 7.
28-Jul-2021	11	Removed RD91, TOP3 insulated and TOP3 package information. Put in separate specification. Minor text changes.
29-Sep-2021	12	Updated Table 2.

### Table 9. Document revision history

#### IMPORTANT NOTICE - PLEASE READ CAREFULLY

STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgement.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of Purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. For additional information about ST trademarks, please refer to www.st.com/trademarks. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2021 STMicroelectronics - All rights reserved