


Time-Delay Fuses

Class G – 600 Volt, ½ - 20 Amps

480 Volt, 25 - 60 Amps



Dimensional Data



Catalog Symbol: SC
 Current-Limiting
 Ampere Rating: ½ to 6 Amperes (fast-acting),
 7 to 60 Amperes (time-delay)
 Voltage Ratings:
 SC ½ to 20 600VAC, 170VDC
 SC 25 to 60 480VAC, 300VDC
 Interrupting Rating: 100,000A RMS Sym. AC, 10,000A DC
 Agency Approvals:
 U.L. Listed, Std. 248-5, Class G, Guide JDDZ, File E4273
 CSA Certified, C22.2 No. 248.5, Class 1422-01, File 53787

Fuse (Amps)	A (±0.03) (Length) x .41" (±0.006) (Diameter)
SC-½ to -15	1.31"
SC-20	1.41"
SC-25 to -30	1.63"
SC-35 to -60	2.25"

Catalog Numbers

SC-½	SC-6	SC-25
SC-1	SC-7	SC-30
SC-1½	SC-8	SC-35
SC-2	SC-9	SC-40
SC-2½	SC-10	SC-45
SC-3	SC-12	SC-50
SC-4	SC-15	SC-60
SC-5	SC-20	—

Carton Quantity and Weight

Catalog Number	Carton Qty.	Weight†	
		Lbs.	Kg.
½-15	4	0.060	0.0272
20	4	0.064	0.029
25-30	2	0.040	0.018
35-60	2	0.075	0.0340

†Weight per carton.

General Information:


- Compact branch-circuit units with high interrupting rating and current-limitation.
- With 600 volt rating, they can be used in 120/208, 120/240 and 277/480 volt circuits.
- Length variations relative to case size make the "rejection" type fuses.
- In general, SC fuses are about ½ the size of the 600 volt NEC fuse type.
- SC fuses with ampere ratings above 6 amps have a degree of overload time-delay which permits them to pass temporary overloads. At 200% load, they have a minimum opening time of 12 seconds.
- Block and fuseholder information on page 2.

CE CE logo denotes compliance with European Union Low Voltage Directive (50-1000 Vac, 75-1500 Vdc). Refer to BIF document #8002 or contact Bussmann Application Engineering at 636-527-1270 for more information.

Time-Delay Fuses

Class G - 600 Volt, 1/2 - 20 Amps
480 Volt, 25 - 60 Amps

Peak Let-Through Curves



Standard SC Fuseblocks Catalog Data

Amps	Poles	Terminal Type			
		Screw With Quick Connect	Pressure Plate w/Quick Connect	Box Lug	Box Lug w/Retaining Clip
1/2	1	BG3011SQ	BG3011PQ	BG3011B	—
	2	BG3012SQ	BG3012PQ	BG3012B	—
15	3	BG3013SQ	BG3013PQ	BG3013B	—
	1	BG3021SQ	BG3021PQ	BG3021B	—
20	2	BG3022SQ	BG3022PQ	BG3022B	—
	3	BG3023SQ	BG3023PQ	BG3023B	—
25	1	BG3031S	BG3031P	BG3031B	—
	2	BG3032S	BG3032P	BG3032B	—
30	3	BG3033S	BG3033P	BG3033B	—
35	1	—	—	G30060-1C	G30060-1CR
	2	—	—	G30060-2C	G30060-2CR
60	3	—	—	G30060-3C	G30060-3CR


Panel-mount Fuseholders for SC Fuses

Catalog Number	Description	
	Fuse Size	Terminal Type
HPF-EE	1-15A	Solder (w/o leads)
HPF-FEE	1-15A	Leads; 10" #18 copper insul. wire
HPF-JJ	20A	Solder (w/o leads)
HPF-FF	25-30A	Solder (w/o leads)

Time-Delay Fuses

Class G - 600 Volt, 1/2 - 20 Amps
480 Volt, 25 - 60 Amps

Time-Current Characteristic Curves-Average Melt



The only controlled copy of this BIF document is the electronic read-only version located on the Bussmann Network Drive. All other copies of this document are by definition uncontrolled. This bulletin is intended to clearly present comprehensive product data and provide technical information that will help the end user with design applications. Bussmann reserves the right, without notice, to change design or construction of any products and to discontinue or limit distribution of any products. Bussmann also reserves the right to change or update, without notice, any technical information contained in this bulletin. Once a product has been selected, it should be tested by the user in all possible applications.