


NOTE

MATERIAL : NYLON 6/6 UL94 V-0  
 COLOUR : BLACK

APPROVED - UNCONTROLLED

UNLESS OTHERWISE STATED

ALL DIMENSIONS IN mm		DO NOT SCALE	
LINEAR TOLERANCE		THIRD ANGLE PROJECTION	
SIZE	(0) (0.0) (0.00)	 ANGULAR TOLERANCE ±0.5 DEGREES UNSPECIFIED RADII 0.25mm DRAFT ANGLE 0.5 DEGREES DIMENSIONS IN BRACKETS [ ] ARE IN INCHES FOR REFERENCE ONLY	
0-10mm	±0.5 ±0.15 ±0.10		
>10-30	±0.5 ±0.20 ±0.15		
>30-50	±0.5 ±0.30 ±0.20		
>50-100	±0.8 ±0.50 ±0.25		
>100-200	±1.5 ±0.80 ±0.40		
>200-300	±2.0 ±1.20 ±0.80		
>300-500	±3.0 ±2.00 ±1.00	ORG. SCALE: 1:1	
>500	±5.0 ±3.00 ±1.50	CREATE DATE: 05/04/2019	

MATERIAL: SEE NOTES

Part ID: 1128934 Project: P110480-1

TITLE: 16 WAY FIBRE CLIP

DWG. No. EFA04-06-ASS

SHEET 1 of 1  
 ISSUE 1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Essentra:](#)

[EFA04-06-ASS](#)