



**Part Number: 9463**

Blue Hose®, 1 Pr #20 Str TC, PO Ins Blu,Wht, OS+TC Brd, PVC Jkt, CM

[Request Sample](#)

**Product Description**

Blue Hose® for Data Highway Plus, 1 Pair 20AWG (7x28) Tinned Copper, PO Insulation Blu,Wht Color Code, Overall Beldfoil®+Tinned Copper Braid(55%) Shield, Blue PVC Outer Jacket, CM

**Technical Specifications**

**Physical Characteristics (Overall)**

**Conductor**

AWG	Stranding	Material	Nominal Diameter	No. of Pairs
20	7x28	TC - Tinned Copper	0.038 in	1

Conductor Count:	2
Conductor Size:	20 AWG

**Insulation**

Material	Nominal Diameter
PE - Polyethylene	0.078 in

**Color Chart**

Number	Color
1	Clear & Blue

**Outer Shield Material**

Type	Layer	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Tape	1	Aluminum/Polyester	Beldfoil®	100 %	TC - Tinned Copper	20	7x28H mm
Braid	2	TC - Tinned Copper		55 %			

**Outer Jacket Material**

Material	Nominal Diameter
PVC - Polyvinyl Chloride	0.238 in

**Construction and Dimensions**

**Stranding**

Twists	Diameter
2.75 twist/ft	0.154 mm

**Electrical Characteristics**

**Conductor DCR**

Nominal Conductor DCR	Nominal Outer Shield DCR
9.5 Ohm/1000ft	4.1 Ohm/1000ft

**Capacitance**

Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Other Conductor to Shield
19.7 pF/ft	36 pF/ft

**Inductance**

Nominal Inductance
0.12 µH/ft

#### Impedance

Nominal Characteristic Impedance
78 Ohm

#### High Frequency (Nominal/Typical)

Frequency [MHz]	Nom. Insertion Loss
1 MHz	0.6 dB/100m
10 MHz	2.1 dB/100m
50 MHz	5 dB/100m
100 MHz	7.5 dB/100m
200 MHz	11 dB/100m
400 MHz	16 dB/100m

#### Delay

Nominal Delay	Nominal Velocity of Propagation (VP) [%]
1.54 ns/ft	66 %

#### Voltage

UL Voltage Rating
300 V RMS (UL AWM Style 2464)
300 (NEC Type CM) V RMS
300 V RMS (NEC Type CL2)

Electrical Characteristics Notes: DC Resistance Unbalanced: .77 Ohms/1000 ft Max

#### Temperature Range

Installation Temp Range:	-40°C To +80°C
UL Temp Rating:	80°C (UL AWM Style 2464)
Storage Temp Range:	-40°C To +80°C
Operating Temp Range:	-40°C To +80°C

#### Mechanical Characteristics

Bulk Cable Weight:	36 lbs/1000ft
Max Recommended Pulling Tension:	48 lbs
Min Bend Radius/Minor Axis:	2.4 in

#### Standards

Customer Part Number Reference Spec:	Allen Bradley P/N 1770-CD
NEC/(UL) Specification:	CL2, CM
CEC/C(UL) Specification:	CM
UL AWM Style:	UL Style 2464 (300 V 80°C)
CPR Euroclass:	Eca
PMSHA Specification:	P-7K-SC-182141

#### Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2005-01-01
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

#### Suitability

Suitability - Sunlight Resistance:	Yes
------------------------------------	-----

## Flammability, LSOH, Toxicity Testing

UL Flammability:	UL1685 UL Loading
UL voltage rating:	300 V RMS (UL AWM Style 2464)

## Plenum/Non-Plenum

Plenum Number:	89463
----------------	-------

## Part Number

### Variants

Item #	Color	Footnote
9463.001829	Blue	
9463.00305	Blue	
9463.00U152	Blue	
9463.00U305	Blue	
9463.01152	Blue	
9463 J22100	Blue, Strong	
9463 J221000	Blue, Strong	C
9463 J2212000	Blue, Strong	C Y
9463 J22500	Blue, Strong	
9463 J226000	Blue, Strong	C Z
9463 J22U1000	Blue, Strong	
9463 J22U500	Blue, Strong	
9463.02305	Brown	
9463 0011000	Brown	
9463 00110000	Brown	C Z
9463 00112000	Brown	C Y
9463 0016000	Brown	C Z
9463.031829	Orange	
9463.03305	Orange	
9463 0031000	Orange	C
9463 00310000	Orange	C Z
9463 00312000	Orange	C Y
9463 0036000	Orange	C Z
9463.041829	Violet	
9463.04305	Violet	
9463 0071000	Violet	C
9463 0076000	Violet	C Z

Footnote:	C - CRATE REEL PUT-UP.
Footnote:	Z - FINAL PUT-UP MAY VARY (= OR -) 10% FOR SPOOLS OR REELS AND (+ OR -) 5% FOR UNREEL CARTONS FROM LENGTH SHOWN.
Footnote:	Y - FINAL PUT-UP LENGTH MAY VAR -10% TO +20% FROM LENGTH SHOWN. MAY CONTAIN 2 PIECES. MINIMUM LENGTH OF ANY ONE PIECE IS 1500'.

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.