

MC3303 MC3403 - MC3503

LOW POWER QUAD BIPOLAR OPERATIONAL AMPLIFIERS

- SHORT-CIRCUIT PROTECTED OUTPUTS
- CLASS AB OUTPUT STAGE FOR MINIMAL CROSSOVER DISTORTION
- SINGLE SUPPLY OPERATION: +3V TO +36V
- DUAL SUPPLIES: ±15V TO ±18V
- LOW INPUT BIAS CURRENT: 500nA MAX
- INTERNALLY COMPENSATED
- SIMILAR PERFORMANCE TO POPULAR UA741


DESCRIPTION

The MC3403 is a low-cost, guad operational amplifier with true differential inputs. The device has electrical characteristics similar to the popular UA741. However the MC3403, has several distinct advantages over standard operational amplifiers types in single supply applications. The quad amplifier can operate at supply voltage as low as 3 Volts or as high as 36 volts with quiescent currents about one third of those associated with the UA741 (on a per amplifier basis). The common-mode input range includes the negative supply, thereby eliminating the necessity for external biasing components in many applications.


ORDER CODE

Part	Temperature	Package		e		
Number	Range	Ν	D	Р		
MC3303	-40°C, +105°C	•	•	•		
MC3403	0°C, +70°C	•	•	•		
MC3503	-55°C, +125°C	•	•	•		
Example : MC3403N						


N = Dual in Line Package (DIP) D = Small Outline Package (SO) - also available in Tape & Reel (DT) P = Thin Shrink Small Outline Package (TSSOP) - only available in Tape & Reel (PT)



PIN CONNECTIONS (top view)



SCHEMATIC DIAGRAM (each amplifier)



DUAL SUPPLIES

v_{cc}+¢

V_{CC}

-0

-0

-0

≟ 1.5V to 18V

₀ ┌┛

≟ 1.5V to 18V

5

0

0-

0-

0-


0-

0-

0

0

SCHEMATIC DIAGRAM



ABSOLUTE MAXIMUM RATINGS

Symbol	Parameter	MC3503	MC3403	MC3303	Unit
V _{CC}	Supply voltage		V		
Vi	Input Voltage ¹⁾		V		
V _{id}	Differential Input Voltage	±36			V
	Output Short-circuit Duration ²⁾	Infinite			
P _{tot}	Power Dissipation	500			mW
T _{oper}	Operating Free-air Temperature Range-55 to +1250 to +70-40 to +105		°C		
T _{stg}	Storage Temperature Range	-65 to +150			°C

1. For supply voltage less than $\pm 15V$, the absolute maximum input voltage is equal to the supply voltage.

2. Any of the amplifier outputs can be shorted to ground indefinitly; however more than one should not be simultaneously shorted as the maximum junction will be exceeded.

ELECTRICAL CHARACTERISTICS

$V_{CC} = \pm 15V, T_{amb}$, = 25°C (unless	otherwise	specified)
-----------------------------	------------------	-----------	------------

Symbol	Parameter	Min.	Тур.	Max.	Unit
	Input Offset Voltage ($R_s \le 10k\Omega$)		ł		
V _{io}	$T_{amb} = 25^{\circ}C$		1	5	mV
	$T_{min} \le T_{amb} \le T_{max}$			6	
	Input Offset Current				
l _{io}	$T_{amb} = 25 \degree C$		5	50	nA
	$T_{min} \le T_{amb} \le T_{max}$			200	
	Input Bias Current				
l _{ib}	$T_{amb} = 25^{\circ}C$		40	500 800	nA
	$T_{min} \le T_{amb} \le T_{max}$			000	
٨	Large Signal Voltage Gain ($V_0 = \pm 10V$, $R_L = 2k\Omega$)	=0			
A _{vd}	$T_{amb} = 25^{\circ}C$	50 25	200		V/mV
	$T_{min} \le T_{amb} \le T_{max}$	20			
	Supply Voltage Rejection Ratio ($R_s \le 10k\Omega$)	77	00		-10
SVR	T _{amb} = 25°C T _{min} ≤ T _{amb} ≤ T _{max}	77 77	90		dB
	Supply Current, all Amp, no load				
	$T_{amb} = 25^{\circ}C$		2.8	7	
I _{cc}	MC3503		2.0	4	mA
	$T_{min} \le T_{amb} \le T_{max}$			8	
	MC3503			5	
.,	Input Common Mode Voltage Range				
V_{icm}	T _{amb} = 25°C T _{min} ≤ T _{amb} ≤ T _{max}	-15 -15		+13 +13	V
		-15		+15	
CMR	Common Mode Rejection Ratio ($R_s \le 10k\Omega$)	70	00		чD
CIVIK	T _{amb} = 25°C T _{min} ≤ T _{amb} ≤ T _{max}	70 70	90		dB
1			20	45	
I _{os}	Output Short-circuit Current	10	30	45	mA
	$\begin{array}{l} \text{Output Voltage Swing} \\ T_{amb} = 25^{\circ}\text{C} \\ \end{array} \qquad \qquad$	10	10 5		
$\pm V_{opp}$	$R_{\rm I} \leq 2k\Omega$	12 10	13.5 13		V
=•opp	$T_{min} \le T_{amb} \le T_{max}$ $R_L \le 10k\Omega$	12	10		v
	$R_{\rm L} \le 2k\Omega$	10			
0.0	Slew Rate (V _I = ±10V, R _L = 2k Ω , C _L = 100pF, T _{amb} = 25°C,				
SR	unity gain)	0.35	0.5		V/µs
+ +	Rsie Time ($V_0 = \pm 20$ mV, $R_L = 2k\Omega$, $C_L = 100$ pF, $T_{amb} = 25$ °C,				
t _{r,} t _f	unity gain)		0.18		μs
K _{OV}	Overshoot (V _I = ± 20 mV, R _L = $2k\Omega$, C _L = 100 pF, T _{amb} = 25° C,				%
	unity gain)		10		/0
ZI	Input Impedance	0.3	1		MΩ
Zo	Output Impedance		75		Ω
Bom	Power Bandwidth ($R_L = 2k\Omega$, $C_L = 100pF$, $A_V = 1$, $T_{amb} = 25^{\circ}C$,		T		k11-7
Pom	$V_{O} = 2V_{pp}, THD \le 5\%)$		9		kHz
В	Unity Gain Bandwidth $V_0 = 10mV$, $R_L = 2k\Omega$, $C_L = 100pF$, $T_{amb} =$		1		MHz
D	25°C, unity gain)				101112

MC3303 - MC3403 - MC3503

Symbol	Parameter	Min.	Тур.	Max.	Unit
GBP	Gain Bandwith Product (V _O = 10 mV, R _L = $2k\Omega$, C _L = 100pF f =100kHz, T _{amb} = 25° C)	0.7	1		MHz
THD	Total Harmonic Distortion (f = 1kHz, A_v = 20dB, R_L = 2k Ω C_L = 100pF, V_o = 2V _{pp} , T_{amb} = 25°C)		0.02		%
e _n	Equivalent Input Noise Voltage (f = 1kHz, $R_s = 100\Omega$		43		$\frac{nV}{\sqrt{Hz}}$
φm	Phase Margin		60		Degrees
DV _{io}	Input Offset Voltage Drift T _{min} ≤ T _{amb} ≤ T _{max}		10		µV/°C
DI _{io}	Input Offset Current Drift T _{min} ≤ T _{amb} ≤ T _{max}		50		pA/°C
V _{o1} /V _{o2}	Channel Separation		120		dB

ELECTRICAL CHARACTERISTICS

 $V_{CC}^{+} = 5V$, $V_{CC}^{-} = Ground$, $T_{amb} = 25^{\circ}C$ (unless otherwise specified)

Symbol	Parameter	Min.	Тур.	Max.	Unit
V _{io}	Input Offset Voltage ($R_s \le 10k\Omega$) $T_{amb} = 25^{\circ}C$ $T_{min} \le T_{amb} \le T_{max}$		1	5 6	mV
l _{io}	Input Offset Current $T_{amb} = 25^{\circ}C$ $T_{min} \le T_{amb} \le T_{max}$		5	50 200	nA
l _{ib}	Input Bias Current $T_{amb} = 25^{\circ}C$ $T_{min} \le T_{max}$		40	500 800	nA
A _{vd}	Large Signal Voltage Gain (V _o = 1.4Vto 2.4V, R _L = 2k Ω) $T_{amb} = 25^{\circ}C$ $T_{min} \leq T_{amb} \leq T_{max}$	10 5	200		V/mV
SVR	Supply Voltage Rejection Ratio ($R_s \le 10k\Omega$) $T_{amb} = 25^{\circ}C$ $T_{min} \le T_{amb} \le T_{max}$	77 77	90		dB
I _{cc}	Supply Current, all Amp, no load MC3503		2.8	7 4	mA
V _{opp}	Output Voltage Range (R _L = 10k Ω) V _{CC} = +5V +5 < V _{CC} ≤ +30V	3.3 V _{CC} ⁺ -2V	3.5 V _{CC} ⁺ -1.7V		V

CIRCUIT DESCRIPTION


The MC3403 is made using four internally compensated, two-stage operational amplifiers. The first stage of each consists of differential input devices Q24 and Q22 with input buffer transistors Q25 and Q21 and the differential to single ended converter Q3 and Q4. The first stage performs not only the first stage gain function but also performs the level shifting and transonductance reduction functions. By reducing the transconductance a smaller compensation capacitor (only 8pF) can be employed, thus saving chip area.


The transconductance reduction is accomplished by splitting the collectors of Q24 and Q22. Another feature of this input stage is that the input common-mode range can include the negative supply fo ground, in single supply operation, without saturation either the input devices or the differential to single-ended converter.

The second stage consists of a standard current source load amplifier stage. The output stage is unique because it allows the output to swing to ground in single supply operation and yet does not exhibit any crossover distortion in split supply operations. This is possible because class AB operation is utilized.

Each amplifier is biased from an internal voltage regulator which has a low temperature coefficient thus giving each amplifier good temperature characteristics as well as excellent power supply rejection.


TYPICAL PERFORMANCE CURVES






APPLICATION INFORMATION

VOLTAGE REFERENCE




WIEN BRIDGE OSCILLATOR




57


HIGH IMPEDANCE DIFFERENTIAL AMPLIFIER




COMPARATOR WITH HYSTERESIS




BI-QUAD FILTER




FUNCTION GENERATOR





MULTIPLE FEEDBACK BANDPASS FILTER



TYPICAL PERFORMANCE CURVES








PACKAGE MECHANICAL DATA


14 PINS - PLASTIC PACKAGE



Dimension	Millimeters			Inches		
Dimensions	Min.	Тур.	Max.	Min.	Тур.	Max.
a1	0.51			0.020		
В	1.39		1.65	0.055		0.065
b		0.5			0.020	
b1		0.25			0.010	
D			20			0.787
E		8.5			0.335	
е		2.54			0.100	
e3		15.24			0.600	
F			7.1			0.280
i			5.1			0.201
L		3.3			0.130	
Z	1.27		2.54	0.050		0.100

PACKAGE MECHANICAL DATA

14 PINS - PLASTIC MICROPACKAGE (SO)




Dimensions		Millimeters			Inches	
Dimensions	Min.	Тур.	Max.	Min.	Тур.	Max.
A			1.75			0.069
a1	0.1		0.2	0.004		0.008
a2			1.6			0.063
b	0.35		0.46	0.014		0.018
b1	0.19		0.25	0.007		0.010
С		0.5			0.020	
c1			45°	(typ.)	·	•
D (1)	8.55		8.75	0.336		0.344
E	5.8		6.2	0.228		0.244
е		1.27			0.050	
e3		7.62			0.300	
F (1)	3.8		4.0	0.150		0.157
G	4.6		5.3	0.181		0.208
L	0.5		1.27	0.020		0.050
М			0.68			0.027
S			8° (max.)		

Note : (1) D and F do not include mold flash or protrusions - Mold flash or protrusions shall not exceed 0.15mm (.066 inc) ONLY FOR DATA BOOK.

PACKAGE MECHANICAL DATA

14 PINS - THIN SHRINK SMALL OUTLINE PACKAGE



D:		Millimeters			Inches		
Dimensions	Min.	Тур.	Max.	Min.	Тур.	Max.	
А			1.20			0.05	
A1	0.05		0.15	0.01		0.006	
A2	0.80	1.00	1.05	0.031	0.039	0.041	
b	0.19		0.30	0.007		0.15	
С	0.09		0.20	0.003		0.012	
D	4.90	5.00	5.10	0.192	0.196	0.20	
E		6.40			0.252		
E1	4.30	4.40	4.50	0.169	0.173	0.177	
е		0.65			0.025		
k	0°		8°	0°		8°	
L	0.450	0.600	0.750	0.018	0.024	0.030	
L1		1.00			0.039		
aaa			0.100			0.004	

Information furnished is believed to be accurate and reliable. However, STMicroelectronics assumes no responsibility for the consequences of use of such information nor for any infringement of patents or other rights of third parties which may result from its use. No license is granted by implication or otherwise under any patent or patent rights of STMicroelectronics. Specifications mentioned in this publication are subject to change without notice. This publication supersedes and replaces all information previously supplied. STMicroelectronics products are not authorized for use as critical components in life support devices or systems without express written approval of STMicroelectronics.

© The ST logo is a registered trademark of STMicroelectronics

© 2001 STMicroelectronics - Printed in Italy - All Rights Reserved

STMicroelectronics GROUP OF COMPANIES

Australia - Brazil - Canada - China - Finland - France - Germany - Hong Kong - India - Israel - Italy - Japan - Malaysia

Malta - Morocco - Singapore - Spain - Sweden - Switzerland - United Kingdom - United States

لرجا

© http://www.st.com

10/10