

LMV82x, LMV82xA

Low power, high accuracy, general-purpose operational amplifier

Datasheet — production data

Features

Low power consumption: 400 µA max at 5 V

• Low power shutdown mode: 50 nA max

• Low offset voltage: 0.8 mV max at 25°C

· Tiny packages

Extended temperature range: -40°C to +125°C

Low supply voltage: 2.5 V - 5.5 V
Gain bandwidth product: 5.5 MHz

Automotive qualification

Benefits

- Longer lifetime in battery-powered applications
- · Higher accuracy without calibration
- Smaller form factor than equivalent competitor devices
- Application performances guaranteed over wide temperature range

Related products

 See TSV85x series for lower power consumption (180 μA max at 5 V)

Applications


- · Battery-powered applications
- · Portable devices
- · Automotive signal conditioning

This is information on a product in full production.

- Active filtering
- Medical instrumentation

Description

The LMV82x and LMV82xA series of single, dual, and quad operational amplifiers offer low voltage operation with rail-to-rail output swing. They outperform the industry standard LMV321, especially with regard to the gain bandwidth



product (5.5 MHz). The LMV821, LMV822 and LMV824 are offered with standard pinouts.

The LMV820, LMV823, and LMV825 include a power-saving shutdown feature that reduces the supply current to a maximum of 50 nA at 25 °C.

The wide temperature range, high ESD tolerance, and automotive grade qualification make them particularly suitable for use in harsh automotive applications.

Table 1. Device summary

	Without	shutdown	With sh	nutdown
	Standard Vio	Enhanced Vio	Standard Vio	Enhanced Vio
Single	LMV821	LMV821A	LMV820	LMV820A
Dual	LMV822	LMV822A	LMV823	LMV823A
Quad	LMV824	LMV824A	LMV825	LMV825A

www.st.com

April 2017 DocID022467 Rev 4 1/32

Contents LMV82x, LMV82xA

Contents

1	Pack	age pin connections 3
2	Abso	olute maximum ratings and operating conditions4
3	Elect	rical characteristics 6
4	Appl	ication information16
	4.1	Operating voltages
	4.2	Input common mode range
	4.3	Rail-to-rail output
	4.4	Input offset voltage drift over temperature
	4.5	PCB layouts
	4.6	Macromodel
	4.7	Shutdown function
5	Pack	age information
	5.1	SC70-5 (or SOT323-5) package information
	5.2	SOT23-5 package information
	5.3	SOT23-6 package information
	5.4	DFN8 2 x 2 mm package information
	5.5	MiniSO-8 package information
	5.6	MiniSO-10 package information
	5.7	TSSOP14 package information
	5.8	TSSOP16 package information
	5.9	SO-8 package information
	5.10	SO-14 package information
6	Orde	ring information
7	Revi	sion history



1 Package pin connections




Figure 1. Pin connections for each package (top view)

1. The exposed pad of DFN8 2x2 can be connected to VCC- or left floating.

577

2 Absolute maximum ratings and operating conditions

Table 2. Absolute maximum ratings (AMR)

Symbol	Parameter	Value	Unit
V _{cc}	Supply voltage ⁽¹⁾	6	
V _{id}	Differential input voltage ⁽²⁾	±V _{cc}	V
V _{in}	Input pins (IN+ and IN- pins) voltage ⁽³⁾	V_{cc-} - 0.3 to V_{cc+} + 0.3	
I _{in}	Input current ⁽⁴⁾	10	mA
SHDN	Shutdown voltage ⁽⁵⁾	V_{cc-} - 0.2 to V_{cc+} + 0.2	V
T _{stg}	Storage temperature	-65 to +150	°C
	Thermal resistance junction to ambient ⁽⁶⁾⁽⁷⁾		
	- SC70-5	205	
	- SOT23-5	250	
	- DFN8 2x2	57	
	- MiniSO8	190	
R _{thja}	- SO8	bitage ⁽²⁾ # V _{cc} - 0.3 to V _{cc+} + 0.3 10 m 10 m 5) V _{cc-} - 0.2 to V _{cc+} + 0.2 re -65 to +150 205 250 57 190 125 100 **Canonical description of the properties of the prope	°C/W
	- TSSOP14	100	
	- SO14	105	
	- SOT23-6	240	
	- MiniSO10	113	
	- TSSOP16	95	
T _j	Maximum junction temperature	150	°C
	HBM: human body model (except shutdown pin) ⁽⁸⁾	4	147
	HBM: human body model (shutdown pin) ⁽⁸⁾	3.5	KV
ESD	MM: machine model ⁽⁹⁾	250	V
	CDM: charged device model ⁽¹⁰⁾	1.3	147
	CDM: charged device model LMV825 ⁽¹⁰⁾	1	kV
	Latch-up immunity	200	mA

- 1. All voltage values, except the differential voltage are with respect to the network ground terminal.
- 2. Differential voltages are the non-inverting input terminal with respect to the inverting input terminal.
- 3. V_{cc} - V_{in} must not exceed 6 V, V_{in} must not exceed 6 V.
- 4. The input current must be limited by a resistor in series with the inputs.
- 5. V_{cc} - V_{shdn} must not exceed 6 V, V_{in} must not exceed 6 V.
- 6. Short-circuits can cause excessive heating and destructive dissipation.
- 7. R_{th} are typical values.
- 8. Human body model: a 100 pF capacitor is discharged through a 1.5 k Ω resistor between two pins of the device. This is done for all couples of pin combinations while other pins are floating.
- 9. Machine model: a 200 pF capacitor is charged to the specified voltage, then discharged directly between two pins of the device with no external series resistor (internal resistor < 5 Ω). This is done for all couples of pin combinations while other pins are floating.
- Charged device model: all pins and package are charged together to the specified voltage and then discharged directly to ground.

-

Table 3. Operating conditions

Symbol	Parameter	Value	Unit
V _{cc}	Supply voltage	2.5 to 5.5	V
V _{icm}	Common mode input voltage range	V _{cc-} - 0.2 to V _{cc+} - 1	V
T _{oper}	Operating free air temperature range	-40 to +125	°C



Electrical characteristics LMV82x, LMV82xA

3 Electrical characteristics

Table 4. Electrical characteristics at V_{cc+} = 2.5 V with V_{cc-} = 0 V, V_{icm} = $V_{cc}/2$, T_{amb} = 25° C, and R_L connected to $V_{cc}/2$ (unless otherwise specified)

Symbol	Parameter	Conditions	Min.	Тур.	Max.	Unit
	DC performance					
		LMV82xA			0.8	
\ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \	Input offset voltage	LMV82x			3.5	
V _{io}	Input offset voltage	LMV82xA, -40 °C < T< 125 °C			2	
		LMV82x, -40 °C < T< 125 °C			4	
		$R_L = 600 \Omega$			220	
\ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \	High level output voltage	R _L = 600 Ω, -40 °C < T< 125 °C			320	mV
V _{CC} -V _{OH}		$R_L = 2 k\Omega$			120	
		R _L = 2 kΩ, -40 °C < T< 125 °C			220	
		$R_L = 600 \Omega$			220	
\ \/	Low lovel output voltage	R _L = 600 Ω, -40 °C < T< 125 °C			320	
V _{OL}	Low level output voltage	$R_L = 2 k\Omega$			120	
		R _L = 2 kΩ, -40 °C < T< 125 °C			200	
	I _{sink} (V _{out} = V _{cc})		5			
	V _{id} = -1 V	-40 °C < T< 125 °C	5			mA
l _{out}	I _{source} (V _{out} = 0 V)		5			
	V _{id} = 1 V	-40 °C < T< 125 °C	5			

Table 5. Shutdown characteristics $V_{CC} = 2.5 \text{ V}$

Symbol	Parameter	Conditions	Min.	Тур.	Max.	Unit				
DC perfor	DC performance									
	Supply current in shutdown	T = 25 °C		2.5	50	nA				
I _{CC}	mode (all operators)	-40°C < T< 85 °C			200	IIA				
	SHDN = V _{CC} -	-40°C < T< 125 °C			1.5	μΑ				
t _{on}	Amplifier turn-on time ⁽¹⁾	$R_L = 2 k\Omega,$ $V_{out} = V_{CC} \text{ to } V_{CC} + 0.2 \text{ V}$		300		ns				
t _{off}	Amplifier turn-off time ⁽¹⁾	$R_L = 2 k\Omega$, Vout = V_{CC+} - 1 V to V_{CC+} - 1.2 V		20		115				
V _{IH}	SHDN logic high		V _{cc} -0.5			V				
V _{IL}	SHDN logic low				0.5	V				
I _{IH}	SHDN current high	SHDN = V _{CC+}		10						
I _{IL}	SHDN current low	SHDN = V _{CC} -		10		pА				
1.	Output leakage in shutdown	SHDN = V _{CC} -		50						
^I OLeak	mode	-40°C < T< 125°C		1		nA				

^{1.} See Section 4.7: Shutdown function on page 17.

Electrical characteristics LMV82x, LMV82xA

Table 6. Electrical characteristics at V_{cc+} = 2.7 V with V_{cc-} = 0 V, V_{icm} = $V_{cc}/2$, T_{amb} = 25° C, and R_L connected to $V_{cc}/2$ (unless otherwise specified)

Symbol	Parameter	Conditions	Min.	Тур.	Max.	Unit
	DC performance		•	•		
		LMV82xA			0.8	
	land offertualte as	LMV82x			3.5	
V _{io}	Input offset voltage	LMV82xA, -40 °C < T< 125 °C			2	mV
		LMV82x, -40 °C < T< 125 °C			4	
ΔV _{io} /ΔΤ	Input offset voltage drift ⁽¹⁾	-40 °C < T< 125 °C		1		μV/°C
	Input offset current			0.5	30	
l _{io}	$(V_{out} = V_{cc}/2)$	-40 °C < T< 125 °C		1	50	nA
	Input bigg ourrent ()/ \/ (2)			60	120	ΠA
l _{ib}	Input bias current ($V_{out} = V_{cc}/2$)	-40 °C < T< 125 °C			180	
	Common mode rejection ratio		70	75		
CMR	20 log ($\Delta V_{icm}/\Delta V_{io}$) Vic = 0 V to V_{cc} -1V, $V_{out} = V_{cc}/2$	-40 °C < T< 125 °C	68			
	Large signal voltage gain $V_{out} = 0.5V$ to $(V_{cc}-0.5V)$	$R_L = 600 \Omega$	90	100		dB
^		R _L = 600 Ω, -40 °C < T< 125 °C	85			ub
A _{vd}		$R_L = 2 k\Omega$	95	100		
		R _L = 2 kΩ, -40 °C < T< 125 °C	90			
		$R_L = 600 \Omega$			200	
V V	Lligh lovel output voltage	R _L = 600 Ω, -40 °C < T< 125 °C			300	
vCC-vOH	High level output voltage	$R_L = 2 k\Omega$			100	
		R _L = 2 kΩ, -40 °C < T< 125 °C			200	\ /
		$R_L = 600 \Omega$			200	mV
	Low lovel output voltage	R _L = 600 Ω, -40 °C < T< 125 °C			300	
V _{OL}	Low level output voltage	$R_L = 2 k\Omega$			120	
		R _L = 2 kΩ, -40 °C < T< 125 °C			200	
	$I_{\text{sink}}(V_{\text{out}} = V_{\text{cc}})$		15	26		
	$I_{sink} (V_{out} = V_{cc})$ $V_{id} = -1 V$	-40 °C < T< 125 °C	12			m ^
l _{out}	I _{source} (V _{out} = 0 V)		15	21		mA
	$V_{id} = 1 V$	-40 °C < T< 125 °C	12			
	Supply current (per channel)			220	300	^
I _{CC}	No load, $V_{out} = V_{cc}/2$	-40 °C < T< 125 °C			500	μΑ

LMV82x, LMV82xA Electrical characteristics

Table 6. Electrical characteristics at V_{cc+} = 2.7 V with V_{cc-} = 0 V, V_{icm} = $V_{cc}/2$, T_{amb} = 25° C, and R_L connected to $V_{cc}/2$ (unless otherwise specified) (continued)

Symbol	Parameter	Conditions	Min.	Тур.	Max.	Unit			
	AC performance								
GBP	Gain bandwidth product			5.5		MHz			
F _u	Unity gain frequency	$R_1 > 1 M\Omega$, $C_1 = 22 pF$		4.5		IVII IZ			
Φ_{m}	Phase margin	N[> 1 Wisz, O[= 22 pr		60		degrees			
G _m	Gain margin			10		dB			
SR	Slew rate	$R_L > 1 M\Omega$, $C_L = 22 pF$, $V_{out} = 0.5 V \text{ to } V_{CC} - 0.5 V$	1.2	1.7		V/µs			
e _n	Equivalent input noise voltage	f = 1 kHz f = 10 kHz		18 15		$\frac{\text{nV}}{\sqrt{\text{Hz}}}$			
i _n	Equivalent input noise current	f = 1 kHz		0.30		<u>pA</u> √Hz			
THD+N	Total harmonic distortion + noise	$\begin{aligned} f_{in} &= 1 \text{ kHz}, \text{ A}_{CL} = 1, \text{ R}_{L} = 100 \text{ k}\Omega \\ \text{Vicm} &= \text{Vcc/2}, \text{ BW} = 22 \text{ kHz}, \\ \text{Vout} &= 3 \text{ Vpp} \end{aligned}$		0.001		%			

Table 7. Shutdown characteristics $V_{CC} = 2.7 \text{ V}$

Symbol	Parameter	Conditions	Min.	Тур.	Max.	Unit				
DC perfo	DC performance									
	Supply current in shutdown mode (all operators)	SHDN = V _{CC} -		2.5	50	nΛ				
I _{CC}		-40°C < T< 85°C			200	nA				
		-40°C < T< 125°C			1.5	μΑ				
t _{on}	Amplifier turn-on time ⁽¹⁾	$R_{L} = 2 k\Omega,$ $V_{out} = V_{CC} to V_{CC} + 0.2 V$		300		no				
t _{off}	Amplifier turn-off time ⁽¹⁾	$R_L = 2 k\Omega$, Vout = V_{CC+} - 1 V to V_{CC+} - 1.2 V		20		ns				
V _{IH}	SHDN logic high		V _{cc} - 0.5			V				
V _{IL}	SHDN logic low				0.5					
I _{IH}	SHDN current high	SHDN = V _{CC+}		10						
I _{IL}	SHDN current low	SHDN = V _{CC} -		10		рА				
la	Output leakage in shutdown	SHDN = V _{CC} -		50						
l _{OLeak}	mode	-40°C < T< 125°C		1		nA				

^{1.} See Section 4.7: Shutdown function on page 17.



Electrical characteristics LMV82x, LMV82xA

Table 8. Electrical characteristics at V_{cc+} = 5 V with V_{cc-} = 0 V, V_{icm} = $V_{cc}/2$, V_{amb} = 25° C, and $V_{cc}/2$ (unless otherwise specified)

Symbol	Parameter	Conditions	Min.	Тур.	Max.	Unit
	DC performance				•	
		LMV82xA			0.8	
\ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \		LMV82x			3.5	\/
V _{io}	Input offset voltage	LMV82xA, -40 °C < T< 125 °C			2	mV
		LMV82x, -40 °C < T< 125 °C			4	
$\Delta V_{io}/\Delta T$	Input offset voltage drift ⁽¹⁾	-40 °C < T< 125 °C		1		μV/°C
1	Input offset current (\\ -\\ /2\)			0.5	30	
l _{io}	Input offset current ($V_{out} = V_{cc}/2$)	-40 °C < T< 125 °C		1	50	n ^
1	Input bigg current (\(\lambda \) / /2\			60	120	nA
l _{ib}	Input bias current (V _{out} = V _{cc} /2)	-40 °C < T< 125 °C			180	
	Common mode rejection ratio 20		72	90		
CMR	$ \log (\Delta V_{icm}/\Delta V_{io}) $ $V_{ic} = 0 \text{ V to } V_{cc}\text{-1V}, V_{out} = V_{cc}/$	-40 °C < T< 125 °C	70			
	Supply voltage rejection ratio 20 log (ΔV _{cc} /ΔV _{io})	$V_{cc} = 2.5 \text{ to } 5 \text{ V}$				
SVR			70	75		
		-40 °C < T< 125 °C	65			dB
	Large signal voltage gain $V_{out} = 0.5V$ to $(V_{cc}-0.5V)$	$R_L = 600 \Omega$	95	100		
۸		R _L = 600 Ω, -40 °C < T< 125 °C	90			
A _{vd}		$R_L = 2 k\Omega$	95	100		
		R _L = 2 kΩ, -40 °C < T< 125 °C	90			
		$R_L = 600 \Omega$			250	
W. W.	High level output voltage	R _L = 600 Ω, -40 °C < T< 125 °C			400	
V _{CC} -V _{OH}	I light level output voltage	$R_L = 2 k\Omega$			150	
		R _L = 2 kΩ, -40 °C < T< 125 °C			200	mV
		$R_L = 600 \Omega$			250	IIIV
V	Low level output voltage	R _L = 600 Ω, -40 °C < T< 125 °C			300	
V _{OL}	Low level output voltage	$R_L = 2 k\Omega$			150	
		R _L = 2 kΩ, -40 °C < T< 125 °C			200	
	I _{sink} (V _{out} = V _{cc)}		35	43		
1 .	V _{id} = -1 V	-40 °C < T< 125 °C	25			mA
l _{out}	I _{source} (V _{out} = 0 V)		60	70		111/4
	V _{id} = 1 V	-40 °C < T< 125 °C	50			
loc	Supply current (per channel)			300	400	пΔ
I _{CC}	No load, $V_{out} = V_{cc}/2$	-40°C < T< 125°C			600	μA



Table 8. Electrical characteristics at V_{cc+} = 5 V with V_{cc-} = 0 V, V_{icm} = $V_{cc}/2$, T_{amb} = 25° C, and R_L connected to $V_{cc}/2$ (unless otherwise specified) (continued)

Symbol	Parameter	Conditions	Min.	Тур.	Max.	Unit				
	AC performance									
GBP	Gain bandwidth product			5.5		MHz				
F _u	Unity gain frequency			4.5		IVITZ				
Φ_{m}	Phase margin	$R_L > 1 M\Omega$, $C_L = 22 pF$		60		degree s				
G _m	Gain margin			10		dB				
SR	Slew rate	$R_L > 1 M\Omega$, $C_L = 22 pF$, $V_{out} = 0.5 V to V_{CC} - 0.5 V$	1.4	1.9		V/µs				
e _n	Equivalent input noise voltage	f = 1 kHz f = 10 kHz		16 13		<u>nV</u> √Hz				
i _n	Equivalent input noise current	f = 1 kHz		0.30		<u>pA</u> √Hz				
THD+N	Total harmonic distortion + noise	$ f_{in} = 1 \text{ kHz}, \ A_{CL} = 1, \\ R_L = 100 \text{ k}\Omega, \\ \text{Vicm} = \text{Vcc/2}, \ \text{BW} = 22 \text{ kHz}, \\ \text{Vout} = 3 \text{ Vpp} $		0.001		%				

^{1.} See Section 4.4: Input offset voltage drift over temperature.

Table 9. Shutdown characteristics $V_{CC} = 5 V$

Symbol	Parameter	Conditions	Min.	Тур.	Max.	Unit				
DC perfo	DC performance									
	Supply current in shutdown	T= 25°C		2.5	50	nA				
I _{CC}	mode (all operators)	-40°C < T< 85°C			200	IIA				
	SHDN = V _{CC} -	-40°C < T< 125°C			1.5	μA				
t _{on}	Amplifier turn-on time ⁽¹⁾	$R_L = 2 k\Omega,$ $V_{out} = V_{CC} \text{ to } V_{CC} + 0.2 \text{ V}$		300		ne				
t _{off}	Amplifier turn-off time ⁽¹⁾	$R_L = 2 \text{ k}\Omega$, Vout = V_{CC+} - 1 V to V_{CC+} - 1.2 V		20		ns				
V _{IH}	SHDN logic high		V _{cc} - 0.5			V				
V _{IL}	SHDN logic low				0.5					
I _{IH}	SHDN current high	SHDN = V _{CC+}		10						
I _{IL}	SHDN current low	SHDN = V _{CC} -		10		pA				
1	Output leakage in shutdown	SHDN = V _{CC} -		50						
^I OLeak	mode	-40°C < T< 125°C		1		nA				

^{1.} See Section 4.7: Shutdown function on page 17.

Electrical characteristics LMV82x, LMV82xA

Figure 2. Supply current vs. supply voltage at $Vicm = V_{CC}/2$

0.35 0.30 **Supply Current (mA)**0.20
0.15
0.10 0.20 T=25°C T=125°C 0.15 T=-40°C 0.10 0.05

Vicm=2.5V

4.0

Supply Voltage (V)

4.5

5.0

5.5

Figure 3. Supply current vs. Vicm at $V_{CC} = 5 V$





Figure 4. Vio distribution at $V_{CC} = 5 \text{ V}$

0.00 L 2.5

3.0

Figure 5. Input offset voltage vs. input common mode voltage at V_{CC} = 5 V







Figure 6. Output current vs. output voltage at $V_{CC} = 2.7 V$

Figure 7. Output current vs. output voltage at $V_{CC} = 5 V$






Figure 8. Output current vs. supply voltage at $V_{CC}/2$

Figure 9. Voltage gain and phase with $C_L = 40 \text{ pF}$





Figure 10. Voltage gain and phase with $C_L = 100 \text{ pF}$

Figure 11. Voltage gain and phase with $C_L = 200 \text{ pF}$








Figure 12. Phase margin vs. output current at $V_{CC} = 5 \text{ V}$

Figure 13. Stability in follower configuration






577

Electrical characteristics LMV82x, LMV82xA

Figure 14. Positive and negative slew rate vs. supply voltage

Figure 15. Positive slew rate at V_{CC} = 5 V with C_L = 100 pF







Figure 16. Negative slew rate at V_{CC} = 5 V with C_L = 100 pF

Figure 17. Noise vs. frequency at $V_{CC} = 5 \text{ V}$








Figure 18. 0.1 Hz to 10 Hz noise at $V_{CC} = 5 \text{ V}$

Figure 19. Distortion + noise vs. frequency





DocID022467 Rev 4

14/32

LMV82x, LMV82xA Electrical characteristics

10⁻¹
10⁻¹
RI=100kΩ
RI=10kΩ
RI=10kΩ
10⁻¹
10 Output Voltage (Vpp)

Figure 20. Distortion + noise vs. output voltage



4 Application information

4.1 Operating voltages

The LMV82x and LMV82xA can operate from 2.5 to 5.5 V. The devices' parameters are fully specified for 2.5, 2.7, and 5 V power supplies. Additionally, the main specifications are guaranteed at extended temperature ranges from -40° C to +125° C.

4.2 Input common mode range

The LMV82xA devices have an input common mode range that includes ground. The input common mode range is extended from V_{cc-} - 0.2 V to V_{cc+} - 1 V, with no output phase reversal.

4.3 Rail-to-rail output

The operational amplifiers' output levels can go close to the rails: 150 mV maximum above and below the rail when connected to a 2 k Ω resistive load to $V_{cc}/2$.

4.4 Input offset voltage drift over temperature

The maximum input voltage drift over temperature variation is defined in Equation 1.

Equation 1

$$\frac{\Delta Vio}{\Delta T} = max \left| \frac{Vio(T) - Vio(25^{\circ}C)}{T - 25^{\circ}C} \right|$$

for Tmin < T < Tmax.

4.5 PCB layouts

For correct operation, it is advised to add 10 nF decoupling capacitors as close as possible to the power supply pins.

4.6 Macromodel

Accurate macromodels of the LMV82x and LMV82xA are available on STMicroelectronics' web site at www.st.com. These models are a trade-off between accuracy and complexity (that is, time simulation) of the LMV82x and LMV82xA operational amplifiers. They emulate the nominal performances of a typical device within the specified operating conditions mentioned in the datasheet. They also help to validate a design approach and to select the right operational amplifier, but they do not replace on-board measurements.

57/

4.7 Shutdown function

The operational amplifier is enabled when the SHDN pin is pulled high. To disable the amplifier, the SHDN pin must be pulled down to V_{CC}. When in shutdown mode, the amplifier output is in a high impedance state. The SHDN pin must never be left floating but tied to V_{CC+} or V_{CC-}.

The turn-on and turn-off times are calculated for an output variation of ±200 mV. Figure 21 and Figure 22 show the test configurations. Figure 23 and Figure 24 show the respective results with these test configurations.

Figure 21. Test configuration for turn-on time (Vout pulled down)

Figure 22. Test configuration for turn-off time (Vout pulled down)





Figure 23. Turn-on time, $V_{CC} = 5 \text{ V}$, Vout pulled down, T = 25 °C

Figure 24. Turn-off time, $V_{CC} = 5 V$, Vout pulled down, T = 25 °C

Vout

0.15



Package information LMV82x, LMV82xA

5 Package information

In order to meet environmental requirements, ST offers these devices in different grades of ECOPACK[®] packages, depending on their level of environmental compliance. ECOPACK[®] specifications, grade definitions and product status are available at: www.st.com. ECOPACK[®] is an ST trademark.



LMV82x, LMV82xA Package information

5.1 SC70-5 (or SOT323-5) package information

DIMENSIONS IN MM

SIDE VIEW

GAUGE PLANE

GAUGE PLANE

GOTTO

COPPLANIAR LEADS

TOP VIEW

TOP VIEW

Figure 25. SC70-5 (or SOT323-5) package mechanical drawing

Table 10. SC70-5 (or SOT323-5) package mechanical data

				Dimensions				
Ref		Millimeters			Inches			
	Min	Тур	Max	Min	Тур	Max		
А	0.80		1.10	0.032		0.043		
A1			0.10			0.004		
A2	0.80	0.90	1.00	0.032	0.035	0.039		
b	0.15		0.30	0.006		0.012		
С	0.10		0.22	0.004		0.009		
D	1.80	2.00	2.20	0.071	0.079	0.087		
Е	1.80	2.10	2.40	0.071	0.083	0.094		
E1	1.15	1.25	1.35	0.045	0.049	0.053		
е		0.65			0.025			
e1		1.30			0.051			
L	0.26	0.36	0.46	0.010	0.014	0.018		
<	0°		8 °	0°		8°		



Package information LMV82x, LMV82xA

SOT23-5 package information 5.2

Figure 26. SOT23-5 package mechanical drawing

Table 11. SOT23-5 package mechanical data

			Dimer	nsions		
Ref.		Millimeters			Inches	
	Min.	Тур.	Max.	Min.	Тур.	Max.
А	0.90	1.20	1.45	0.035	0.047	0.057
A1			0.15			0.006
A2	0.90	1.05	1.30	0.035	0.041	0.051
В	0.35	0.40	0.50	0.013	0.015	0.019
С	0.09	0.15	0.20	0.003	0.006	0.008
D	2.80	2.90	3.00	0.110	0.114	0.118
D1		1.90			0.075	
е		0.95			0.037	
Е	2.60	2.80	3.00	0.102	0.110	0.118
F	1.50	1.60	1.75	0.059	0.063	0.069
L	0.10	0.35	0.60	0.004	0.013	0.023
K	0 °		10 °	0 °		10 °

LMV82x, LMV82xA Package information

5.3 SOT23-6 package information

Figure 27. SOT23-6 package mechanical drawing

Table 12. SOT23-6 package mechanical data

	Dimensions						
Ref.		Millimeters			Inches		
	Min.	Тур.	Max.	Min.	Тур.	Max.	
Α	0.90		1.45	0.035		0.057	
A1			0.10			0.004	
A2	0.90		1.30	0.035		0.051	
b	0.35		0.50	0.013		0.019	
С	0.09		0.20	0.003		0.008	
D	2.80		3.05	0.110		0.120	
Е	1.50		1.75	0.060		0.069	
е		0.95			0.037		
Н	2.60		3.00	0.102		0.118	
L	0.10		0.60	0.004		0.024	
θ	0°		10°	0°		10 °	

Package information LMV82x, LMV82xA

5.4 DFN8 2 x 2 mm package information




Figure 28. DFN8 2 x 2 mm package mechanical drawing (pitch 0.5 mm)

Table 13. DFN8 2 x 2 mm package mechanical data (pitch 0.5 mm)

			Dimer	nsions					
Ref.		Millimeters			Inches				
	Min.	Тур.	Max.	Min.	Тур.	Max.			
Α	0.51	0.55	0.60	0.020	0.022	0.024			
A1			0.05			0.002			
А3		0.15			0.006				
b	0.18	0.25	0.30	0.007	0.010	0.012			
D	1.85	2.00	2.15	0.073	0.079	0.085			
D2	1.45	1.60	1.70	0.057	0.063	0.067			
Е	1.85	2.00	2.15	0.073	0.079	0.085			
E2	0.75	0.90	1.00	0.030	0.035	0.040			
е		0.50			0.020				
L			0.425			0.017			
ddd			0.08			0.003			

LMV82x, LMV82xA Package information

5.5 MiniSO-8 package information




Figure 29. MiniSO-8 package mechanical drawing

Table 14. MiniSO-8 package mechanical data

			Dime	nsions					
Ref.	Millimeters			Inches					
	Min.	Тур.	Max.	Min.	Тур.	Max.			
А			1.1			0.043			
A1	0		0.15	0		0.006			
A2	0.75	0.85	0.95	0.030	0.033	0.037			
b	0.22		0.40	0.009		0.016			
С	0.08		0.23	0.003		0.009			
D	2.80	3.00	3.20	0.11	0.118	0.126			
Е	4.65	4.90	5.15	0.183	0.193	0.203			
E1	2.80	3.00	3.10	0.11	0.118	0.122			
е		0.65			0.026				
L	0.40	0.60	0.80	0.016	0.024	0.031			
L1		0.95			0.037				
L2		0.25			0.010				
k	0 °		8°	0°		8°			
ccc			0.10			0.004			



DocID022467 Rev 4

23/32

Package information LMV82x, LMV82xA

5.6 MiniSO-10 package information

E1

O 25 mm

Figure 30. MiniSO-10 package mechanical drawing

Table 15. MiniSO-10 package mechanical data

			Dimer	nsions		
Ref.		Millimeters			Inches	
	Min.	Тур.	Max.	Min.	Тур.	Max.
А			1.10			0.043
A1	0.05	0.10	0.15	0.002	0.004	0.006
A2	0.78	0.86	0.94	0.031	0.034	0.037
b	0.25	0.33	0.40	0.010	0.013	0.016
С	0.15	0.23	0.30	0.006	0.009	0.012
D	2.90	3.00	3.10	0.114	0.118	0.122
Е	4.75	4.90	5.05	0.187	0.193	0.199
E1	2.90	3.00	3.10	0.114	0.118	0.122
е		0.50			0.020	
L	0.40	0.55	0.70	0.016	0.022	0.028
L1		0.95			0.037	
k	0°	3°	6 °	0 °	3 °	6°
aaa			0.10			0.004

LMV82x, LMV82xA Package information

5.7 TSSOP14 package information

Figure 31. TSSOP14 package mechanical drawing

Table 16. TSSOP14 package mechanical data

			Dimer	nsions		
Ref.		Millimeters			Inches	
	Min.	Тур.	Max.	Min.	Тур.	Max.
А			1.20			0.047
A1	0.05		0.15	0.002	0.004	0.006
A2	0.80	1.00	1.05	0.031	0.039	0.041
b	0.19		0.30	0.007		0.012
С	0.09		0.20	0.004		0.0089
D	4.90	5.00	5.10	0.193	0.197	0.201
Е	6.20	6.40	6.60	0.244	0.252	0.260
E1	4.30	4.40	4.50	0.169	0.173	0.176
е		0.65			0.0256	
L	0.45	0.60	0.75	0.018	0.024	0.030
L1		1.00			0.039	
k	0°		8°	0°		8°
aaa			0.10			0.004

Package information LMV82x, LMV82xA

5.8 TSSOP16 package information

PIN 1 DENIFICATION

SEATING PLANE

COAGE PLANE

CLUB P

Figure 32. TSSOP16 package mechanical drawing

Table 17. TSSOP16 package mechanical data

			Dime	nsions		
Ref.		Millimeters			Inches	
	Min.	Тур.	Max.	Min.	Тур.	Max.
Α			1.20			0.047
A1	0.05		0.15	0.002		0.006
A2	0.80	1.00	1.05	0.031	0.039	0.041
b	0.19		0.30	0.007		0.012
С	0.09		0.20	0.004		0.008
D	4.90	5.00	5.10	0.193	0.197	0.201
E	6.20	6.40	6.60	0.244	0.252	0.260
E1	4.30	4.40	4.50	0.169	0.173	0.177
е		0.65			0.0256	
k	0°		8°	0°		8 °
L	0.45	0.60	0.75	0.018	0.024	0.030
L1		1.00			0.039	
aaa			0.10			0.004

57

LMV82x, LMV82xA Package information

5.9 SO-8 package information

SEATING PLANE

COCC C

SEATING PLANE

GAGE PLANE

1 4 e

Figure 33. SO-8 package mechanical drawing

Table 18. SO-8 package mechanical data

			Dime	nsions			
Ref.	Millimeters				Inches		
	Min.	Тур.	Max.	Min.	Тур.	Max.	
А			1.75			0.069	
A1	0.10		0.25	0.004		0.010	
A2	1.25			0.049			
b	0.28		0.48	0.011		0.019	
С	0.17		0.23	0.007		0.010	
D	4.80	4.90	5.00	0.189	0.193	0.197	
Е	5.80	6.00	6.20	0.228	0.236	0.244	
E1	3.80	3.90	4.00	0.150	0.154	0.157	
е		1.27			0.050		
h	0.25		0.50	0.010		0.020	
L	0.40		1.27	0.016		0.050	
L1		1.04			0.040		
k	1°		8 °	1°		8°	
ccc			0.10			0.004	



DocID022467 Rev 4

Package information LMV82x, LMV82xA

5.10 SO-14 package information

D hx45'

A2 A

A3 A

A45'

C

SEATING PLANE

C

GAGE PLANE

T

T

C

Figure 34. SO-14 package mechanical drawing

Table 19. SO-14 package mechanical data

	Dimensions						
D-f		Millimeters		Inches			
Ref.	Min.	Тур.	Max.	Min.	Тур.	Max.	
Α	1.35		1.75	0.05		0.068	
A1	0.10		0.25	0.004		0.009	
A2	1.10		1.65	0.04		0.06	
В	0.33		0.51	0.01		0.02	
С	0.19		0.25	0.007		0.009	
D	8.55		8.75	0.33		0.34	
Е	3.80		4.0	0.15		0.15	
е		1.27			0.05		
Н	5.80		6.20	0.22		0.24	
h	0.25		0.50	0.009		0.02	
L	0.40		1.27	0.015		0.05	
k		8 ° (max.)					
ddd			0.10			0.004	

577

6 Ordering information

Table 20. Order codes

Order code	Temperature range	Package	Packing	Marking
LMV821ICT		SC70-5		K1S
LMV821ILT		SOT23-5	Tape & reel	K155
LMV822IQ2T		DFN8 2x2		K1S
LMV822IST	-40 °C to +125 °C	MiniSO8		K155
LMV822IDT		SO8		LMV822I
LMV824IPT		TSSOP14		LMV824I
LMV824IDT		SO14		LMV824I
LMV821AICT		SC70-5		K1T
LMV821AILT		SOT23-5		K156
LMV822AIST	-40 °C to +125 °C	MiniSO8	Tono 9 rool	K156
LMV822AIDT	-40 °C to +125 °C	SO8	Tape & reel	LMV822AI
LMV824AIPT		TSSOP14		LMV824AI
LMV824AIDT		SO14		LMV824AI

Table 21. Order codes (with shutdown pin)

Order code	Temperature range	Package	Packing	Marking
LMV820ILT		SOT23-6		K155
LMV823IST	-40 °C to +125 °C	MiniSO10	Tape & reel	K155
LMV825IPT		TSSOP16		LMV825I
LMV820AILT		SOT23-6		K156
LMV823AIST	-40 °C to +125 °C	MiniSO10	Tape & reel	K156
LMV825AIPT		TSSOP16		LMV825AI

Ordering information LMV82x, LMV82xA

Table 22. Order codes (automotive grade parts)

Order code	Temperature range	Package	Packing	Marking
LMV821IYLT	-40 ° C to +125 ° C Automotive grade ⁽¹⁾	SOT23-5	Tape & reel	K167
LMV822IYST		MiniSO8		K167
LMV822IYDT		SO8		LMV822IY
LMV824IYDT		SO14		LMV824IY
LMV824IYPT		TSSOP14		
LMV821AIYLT	-40 ° C to +125 ° C Automotive grade ⁽¹⁾	SOT23-5	Tape & reel	K168
LMV822AIYST		MiniSO8		K168
LMV822AIYDT		SO8		LMV822AY
LMV824AIYDT		SO14		LMV824AIY
LMV824AIYPT		TSSOP14		

Qualification and characterization according to AEC Q100 and Q003 or equivalent, advanced screening according to AEC Q001 & Q002 or equivalent.



LMV82x, LMV82xA Revision history

7 Revision history

Table 23. Document revision history

Date	Revision	Changes	
10-Nov-2011	1	Initial release.	
06-Jul-2012	2	Addition of automotive grade parts.	
29-Jan-2013	3	Description and Section 4.6: Macromodel: small text changes. Updated Figure 1. Updated titles of Figure 3, Figure 13, and Figure 27. Updated Table 10, Table 11, Table 12, and Table 22: Order codes (automotive grade parts). Section 4.7: Shutdown function: added explanation of Figure 23 ar Figure 24.	
10-Apr-2017	4	Updated <i>Table 13</i> : "L" dimension changed from 0.5 mm to 0.425 mm. Minor text revisions throughout the document,	



IMPORTANT NOTICE - PLEASE READ CAREFULLY

STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgement.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of Purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2017 STMicroelectronics – All rights reserved

57