


CUSTOMER *ELTECH company*

DATE 2017-05-17

SPECIFICATION FOR APPROVAL

CUSTOMER P/N	FW44-EF20/20/11 GAP=0.5mm
FERRIWO P/N	FW44-EF20/20/11 GAP=0.5mm
SPEC.NO.	FSN170517ABD
CORE SHAPE	

APPROVED BY:

1. DIMENSIONS (mm)

	DIMENSIONS (mm)	
	A	20.2±0.50
	B	10.1±0.30
	C	10.8±0.30
	D	5.7±0.30
	E	14.1min
	F	7.6±0.20

CORE PARAMETERS	
Effective Length L_e	0.73mm
Effective Cross Area A_e	63.4mm ²
Effective Volume V_e	2956.4mm ³
Approx. Weight W	

Item:	P/N:	SPEC. /N
FERRITE CORE	FW44-EF20/20/11 GAP=0.5mm	FSN170517ABD

2. ELECTRICAL CHARACTERISTICS

ITEMS	SPEC	TESTING METHOD	TESTING INSTRUMENT
INDUCTANCE	GAP=0.5mm×2 for 2 pcs cores GAP 0.5mm the one pcs	1KHz,1V,25±3℃	HP4284 OR YD2810

3.MATERIAL CHARACTERISTICS

MATERIAL: FW44

CHARACTERISTICS		UNIT	VALUE
INITIAL PERMEABILITY	μi	—	2400±25%
SATURATION MAGNETIC FLUX DENSITY (H=1194A/m)	Bs	mT (25/100℃)	500
			390
REMANENT FLUX DENSITY	Br	MT (25/100℃)	110
COERCIVE FORCE	Hc	A/m (25/100℃)	13
RELATIVE LOSS FACTOR	Tanδ/ui		
RELATIVETEMP.FACTOR	αair		
CURIE TEMP.	Tc	℃	>215
ELECTRICAL RESISTIVITY	ρ	Ω	6.5
DENSITY	d	kg/m ³	4.8×10 ³
Item:	P/N:	SPEC. /N	
FERRITE CORE	FW44-EF20/20/11 GAP=0.5mm	FSN170517ABD	

4. Maximum chip off:

a.

The depth of crack in the ground surface should be no more than 0.3mm, length is no more than 1/4 length of lengthen line. In the non-ground surface, the depth should be no more than 0.5mm length is no more than 1/3 length of lengthen line.

b. 对于磁芯的外观检验方面，执行如下标准规格：

		接合面	其他表面
破损	1 处破损的面积	≤0.7mm ²	≤1.0mm ²
	2 处以上破损面积的合计	≤2.0mm ²	≤5.0mm ²
	破损深度	≤0.7mm	≤1.0mm
其他	实际使用中无有害毛刺，裂纹，气孔等		

5. (Inspection Method) :

According to GB/T2828.1-2003.one time normal random sampling,Inspect level II ,AQL.should be as follows;

	AQL	Inspect Item
A	0.65	Electromagnetic Property
B	1.0	Outside Size
C	1.5	Outside Quality

6.Packing:

plastic sack is used to inside packing,paper box is used to outside packing,Qualify Certification is attached on every box,including Item (Product name or type),Quantity,Lot No.and Tester.

6.2.QTTY in carton

Item	(PRS/CTN)	Remark
FW44-EF20/20/11 GAP=0.5mm		

Item:	P/N:	SPEC./N
FERRITE CORE	FW44-EF20/20/11 GAP=0.5mm	FSN170517ABD