

# HUBER+SUHNER® DATA SHEET RF ASSEMBLIES

## Test Lead: TL-8A



Rev.: A

### Description

Test Lead assembly for indoor applications (Test and Measurement) consisting of a high flexible PE foamed cable with armouring protection and 2x SMA male straight connectors for frequency up to 8 GHz.

**ID (Material/Item No.)** 85014638  
**Description (Product)** TL-8A-11SMA-11SMA-01500-51



### Product Configuration

Cable type 50Ω +/-1Ω, PE Foam double screen  
 Armour Steel wire spring, steel braid, TPU blue, max. dia. 10.4 mm  
 Length of Assembly 1500 mm +/- 15 mm  
 Connector A SMA straight male, hex. 8 mm, *Quick-Lock*  
 Nut: steel; Body: steel; Center Contact: Cu-Be/Gold  
 Connector B SMA straight male, hex. 8 mm, *Quick-Lock*  
 Nut: steel; Body: steel; Center Contact: Cu-Be/Gold  
 Cable entry protection PA, black

### Technical Data

#### Mechanical Data

Mating cycle *)	> 3000	Bending Radius repeated (min.)	55 mm (preferred: 100 mm)
Tensile Force (max.)	200 N	Connector interface	IEC 61169-15 / MIL-STD-348A/310
Recom. mating torque **)	1.0 Nm	Weight	0.295 kg

#### Environmental Data

Operating Temperature - 5°C to + 85°C  
 Storage Temperature - 40°C to + 85°C  
 RoHS, REACH compliant  
 Water protection SMA-Connector without gasket on Interface

#### Electrical Data

Impedance	50 Ω +/-1 Ω	Operating Frequency	up to 8 GHz
Velocity of propagation	82 %	Insulation resistance	> 5 x 10 <sup>3</sup> MΩ
Capacitance	82 pF / m	Time delay	4.3 ns / m
Dielectric withstand voltage	500 V rms		

	Frequency	1 GHz	2 GHz	3 GHz	4 GHz	6 GHz	8 GHz
Return Loss	equal or better	- 32 dB	- 29 dB	- 26 dB	- 26 dB	- 25 dB	- 22 dB
Attenuation (assembly)	typically, at 25°C	0.54 dB	0.80 dB	1.00 dB	1.16 dB	1.50 dB	1.84 dB
Power handling	sea level, at 40°C	150 W	105 W	80 W	75 W	62 W	50 W
Screening effectiveness		> 80 dB	> 76 dB	> 70 dB	> 65 dB	> 60 dB	> 50 dB
Insertion Loss stability ***)		< 0.02 dB	< 0.03 dB	< 0.04 dB	< 0.05 dB	< 0.08 dB	< 0.10 dB
Phase stability ***)		+/- 1.5° el.	+/- 2.5° el.	+/- 4° el.	+/- 5° el.	+/- 8° el.	+/- 10° el.

### General Information

\*) Number of Mating With use of torque wrench at recommended value, clean interface after each 20 matings, mated with connector according IEC or MIL standard  
 \*\*) H+S torque wrench H+S description: 74\_Z-0-0-21 // material/item number: 22543130  
 \*\*\*) Stability test One, 180° revers bends, 75 mm radius mandrel

HUBER+SUHNER is certified according to ISO 9001 and ISO 14001

**WAIVER!**  
 It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical specifications and/or the fitness for any particular purpose. The facts and figures contained herein are carefully compiled to the best of our knowledge, but they are intended for general informational purposes only.



**HUBER+SUHNER AG**  
 RF Technology  
 9100 Herisau, Switzerland  
 Phone +41 (0)71 353 41 11  
 Fax +41 (0)71 353 45 90  
 www.hubersuhner.com

**HUBER+SUHNER – Excellence in Connectivity Solutions**