


POWER RELAY

1 POLE - 8A Medium Load Control

JS Series

- UL class B (130°C) coil wire insulation
- 1 form A (SPST-NO) or 1 form C (SPDT) contact
- Low profile and space saving
Height: 12.5mm - Mounting space: 290mm²
- High sensitivity in small package
Operating power 110 to 140mW
Nominal power 220 to 290mW
- High insulation in small package
Insulation distance: 8.0mm (between coil and contacts) Dielectric strength: 5,000VAC
Surge strength: 10,000V
- Plastic materials
UL 94 flame class V-0 UL CTI level class 2
- Plastic sealed
- Various contact material options
- RoHS compliant (Please see page 6 for more information)



■ PARTNUMBERS

[Example] JS - 12 M F - K T - V3*

 (a) (b) (c) (d) (e) (f) (g)

(a)	Relay type	JS : JS series
(b)	Coil Voltage	12 : 5...60VDC (Coil rating table at page 3)
(c)	Coil configuration	Nil : 1 form C (SPDT) M : 1 form A (SPST-NO)
(d)	Contact material	D : Silver nickel F : Gold flash silver nickel N : Gold flash silver tin oxide
(e)	Enclosure	K : Plastic sealed type
(f)	Construction	Nil : 3.2mm T : 5.0mm (only JS-MN)
(g)	Gold plating	Nil : Standard V3 : 3.0μm gold plating for lower current applications (available with N contact, not available for T, 5.0mm type) V1 : 1.0μm gold plating for lower current applications (available with N contact, not available for T, 5.0mm type)

Note: Actual marking omits the hyphen (-) or (*)
*: V3, V1 are marked at different position on the relay
E.g.: Ordering code: JS-12F actual marking: JS12F-K

JS Series

■ Specifications

Item			JS-() F/N-K	JS-()D -K	JS-() N-K-V1	JS-() N-K-V3	Remarks / conditions	
Contact data	Configuration		1 form A (SPST-NO), 1 form C (SPDT)					
	Construction		Single					
	Plating		Au flash	-	1μm Au plated	3μm Au plated		
	Material		See partnumber information					
	Resistance		Max. 100mΩ		Max. 30mΩ		6VDC, 1A	
	Contact rating		8A, 250VAC / 24VDC				Resistive	
	Max. carrying current		10A					
	Max. switching voltage		400VAC / 300VDC					
	Max. switching power		2000VA / 192W					
	Min. switching load *1		100mA, 5VDC		10mA, 5VDC			
Coil	Rated power (20°C)		220 to 290mW					
	Operate power (20°C)		110 to 140mW					
	Operating temperature range		-40°C ~ +85°C (at rated voltage)				No frost	
Timing data	Operate		Max. 10ms				Without bounce	
	Release		Max. 5ms				Without bounce, no diode	
Life	Mechanical		Min. 20 x 10 ⁶ operations					
	Electrical (resistive)	AC contact rating	Min. 50 x 10 ³ operations (AgSnO ₂) Min. 20 x 10 ³ operations (AgNi)				At rated load	
		DC contact rating	Min. 50 x 10 ³ operations (AgSnO ₂) Min. 20 x 10 ³ operations (AgNi)				At rated load	
Insulation	Insulation resistance		1000VAC (50/60Hz), 1 minute					
	Dielectric strength	Open contacts	Min. 1000MΩ at 500VDC					
		Coil contact	5000VAC (50/60Hz), 1 minute					
	Surge strength	Coil to contacts	10000V / 1.2 x 50μs standard wave					
	Clearance		8mm					
	Creepage		8mm					
	EN61810-1, VDE0435	Voltage		250V				
		Pollution		3				
Material group		III a						
Category		C / 250V (reference voltage) (VDE 01106)						
Other	Vibration resistance	Misoperation	10~55~10Hz single amplitude 0.825mm					
		Endurance	10~55~10Hz single amplitude 1.65mm					
	Shock resistance	Misoperation	Min. 100m/s ² (11±1ms)				Direction X, Y, Z contact ON/OFF total 36 times	
		Endurance	Min. 1,000m/s ² (6±1ms)				Direction X, Y, Z contact OFF total 18 times	
	Dimensions / weight		10.0 x 29.0 x 12.5 mm / approx. 8.0g					
	Sealing		Plastic sealed					

*1: Minimum switching loads mentioned above are reference values. Please perform the confirmation test with actual load before production since reference values may vary according to switching frequencies, environmental conditions and expected reliability levels.

JS Series

■ Coil Data

Coil Code	Rated Coil Voltage (VDC)	Coil Resistance $\pm 10\%$ (Ω)	Must Operate Voltage* (VDC)	Must Release Voltage* (VDC)	Rated Power (mW)
005	5	112	3.5	0.5	225
006	6	160	4.2	0.6	
009	9	360	6.3	0.9	
012	12	660	8.5	1.2	220
018	18	1,455	12.7	1.8	225
024	24	2,350	16.8	2.4	245
048	48	8,000	33.4	4.8	290
060	60	12,500	41.7	6.0	

Note: All values in the table are valid at 20°C and zero contact current, unless otherwise specified.

*: Specified operate values are valid for pulse wave voltage.

Note: Please use at rated coil voltage. Please refer to characteristic data and set up adequate voltage in case of use at over voltage.

Note: Care shall be taken on the heat generated on PC board when maximum carrying current exceeds 10A. Please perform the confirmation test with actual conditions.









■ Safety Standards

Type	Compliance	Contact rating		
UL	UL508 File No. E56140	Flammability: UL94-V-0 (plastics)		
		Contact material: Nil, E	N	D, F
		8A, 24VDC (resistive) 100k 8A, 250VAC (resistive) 100k 10A, 30VDC (resistive) 10A, 250VAC (resistive) 1/4HP, 125VAC/250VAC 1/3HP, 125VAC 1/2HP, 250VAC Pilot duty: C150, B300 Pilot duty: 0.27A, 250VDC	8A, 24VDC (resistive) 100k 8A, 250VAC (resistive) 100k 10A, 30VDC (resistive) 10A, 250VAC (resistive) 1/4HP, 125VAC/250VAC 1/3HP, 125VAC 1/2HP, 250VAC Pilot duty: A300, B300, C150, R300	8A, 24VDC (resistive) 8A, 250VAC (resistive)
CSA	C22.2 No. 14 File No. LR35579			
VDE	IEC/EN61810 EN60335-1 clause 15.3; 16.3; 29.1; 29.2; 29.3 EN60730-1 clause 12.2; 13.2; 20.1; 20.2; 20.3 EN60947-5-1 Appendix C	8A, 250VAC ($\cos\phi=1$) 8A, 24VDC (L/R=0ms)		JS-()D-K, JS-()F-K: 6A, 250VAC ($\cos\phi=1$) 8A, 24VDC (L/R=0ms) JS-()MD-K, JS-()MF-K: 8A, 240VAC ($\cos\phi=1$) 8A, 24VDC (L/R=0ms)
CQC	GB15092.1 File No. 17001162883	10A, 30VDC/250VAC (except -V3 type)		

JS Series

■ Characteristic Data (Reference)



* Characteristic data is not guaranteed value but measured values of samples from production line.



JS Series

■ Characteristic Data (Reference)

* Characteristic data is not guaranteed value but measured values of samples from production line.




JS Series


■ Dimensions

- Dimensions


JS-M(-K)



JS(-K)




JS-MN-(K)T




* Dimensions of the terminals do not include thickness of pre-solder.

- Schematics (BOTTOM VIEW)


JS-M(-K)



JS(-K)




JS-MN-(K)T




- PC Board Mounting Hole Layout (BOTTOM VIEW)


JS-M(-K)



JS(-K)



JS-MN-(K)T



* Tolerance of PC board mounting hole layout: ± 0.1 unless otherwise specified.

(): Reference value
Unit: mm

CAUTIONS

- All values mentioned in this datasheet are provided under ideal conditions. Please perform the confirmation test before actual use.
- Reflow soldering is prohibited.
- Do not use relays in the atmosphere with sulfide gas, chloride gas or nitric oxide. Contact resistance may increase.
- Do not use silicon or silicon-containing product or materials near relays. It may cause contact failure.

GENERAL INFORMATION

1. ROHS Compliance

- All relays produced by Fujitsu Components are compliant with RoHS directive 2011/65/EU, including commission delegated directive 2015/863.

2. Recommended lead free solder condition

- Lead free solder plating on relay terminals is Sn-3.0Ag-0.5Cu, unless otherwise specified. This material has been verified to be compatible with PbSn assembly process.
- Recommended solder for assembly: Sn-3.0Ag-0.5Cu.

Flow Solder Condition:

Pre-Heating: Maximum 120°C within 90 sec.

Soldering: Eip within 5 sec. at 255°C±5°C solder bath

Relay must be cooled by air immediately after soldering

Solder by Soldering Iron:

Soldering Iron: 30-60W

Temperature: Maximum 340-360°C

Duration: Maximum 3 sec.

We highly recommend that you confirm your actual solder conditions

3. Moisture Sensitivity

- Moisture Sensitivity Level standard is not applicable to electromechanical relays, unless otherwise indicated.

4. Tin Whiskers

- Dipped SnAgCu solder is known as presenting a low risk to tin whisker development. No considerable length whisker was found by our in house test.

JS Series

Contact

Japan

FUJITSU COMPONENT LIMITED
Shinagawa Seaside Park Tower
12-4, Higashi-shinagawa 4-chome,
Tokyo 140 0002, Japan
Tel: +81-3-3450-1682
Email: fcl-contact@cs.fcl-components.com

North and South America

FUJITSU COMPONENTS AMERICA
2055 Gateway Place Suite 480,
San Jose, CA 95110 USA
Tel: +1-408-745-4900
Email: fcai.components@fcl-components.com

Europe

FUJITSU COMPONENTS EUROPE
Diamantlaan 25
2132 WV Hoofddorp, Netherlands
Tel: +31-23-556-0910
Email: info.fceu@cs.fcl-components.com

Asia Pacific

FUJITSU COMPONENTS ASIA.
No. 20 Harbour Drive, #07-01B
Singapore 117612
Tel: +65-6375-8560
Email: fcal@fcl-components.com

China

FUJITSU ELECTRONIC COMPONENTS
(SHANGHAI)
Unit 4306, InterContinental Business Center
100 Yu Tong Road, Shanghai 200070, China
Tel: +86-21-3253 0998
Email: fcsh@fcl-components.com

Hong Kong

FUJITSU COMPONENTS HONG KONG
Unit 2313, Seapower Tower, Concordia
Plaza, No.1 Science Museum Road,
TST, Kowloon, Hong Kong
Tel: +852-2881-8495
Email: fcal@fcl-components.com

Web: www.fcl.fujitsu.com/en/

© 2023 Fujitsu Component Limited. All rights reserved. All trademarks or registered trademarks are the property of their respective owners.

Fujitsu Products are intended for general use, including without limitation, in personal, household and office environments, in buildings and for ordinary use in the industry. Fujitsu Products are not intended to be used in applications where extremely high safety is required ("High Safety Required Applications"), such as, but not limited to, applications in nuclear facilities, in aircraft automatic flight control, in air traffic control, in mass transit system control, in missile launch system, in weapon systems, in medical equipment for life support or any application involving a direct serious risk of physical injury or death.

Please do not use Fujitsu Products without securing the sufficient safety and reliability required for the High Safety Required Applications. In addition, Fujitsu shall not be liable against the customer and/or any third party for any claims or damages arising in connection with the use of Fujitsu Products in the High Safety Required Applications.

Fujitsu warrants that its Products, if properly used and services, will conform to their specification and will be free from defects in material and workmanship for twelve months from delivery.

The implied warranties of merchantability and fitness for a particular purpose and all other warranties, representations and conditions, express or implied by statute, trade usage or otherwise, except as set forth in this warranty, are excluded and shall not apply to the Products delivered.

The contents, data and information in this datasheet are provided by Fujitsu Component Ltd. as a service only to its user and only for general information purposes. The use of the contents, data and information provided in this datasheet is at the users' own risk.

Fujitsu has assembled this datasheet with care and will endeavor to keep the contents, data and information correct, accurate, comprehensive, complete and up to date.

Fujitsu Component Limited and affiliated companies do however not accept any responsibility or liability on their behalf, nor on behalf of its employees, for any loss or damage, direct, indirect or consequential, with respect to this datasheet, its contents, data, and information and related graphics and the correctness, reliability, accuracy, comprehensiveness, usefulness, availability and completeness thereof.

Nor do Fujitsu Component Limited and affiliated companies accept on their behalf, nor on behalf of its employees, any responsibility or liability with respect to these datasheets, its contents, data, information and related graphics and the correctness, reliability, accuracy, comprehensiveness, usefulness, availability and completeness thereof. Rev. July 3, 2023.