

Han 4 Quintax Stift, 3-9.5mm



Image is for illustration purposes only. Please refer to product description.

Part number	09 15 004 3013
Specification	Han 4 Quintax Stift, 3-9.5mm
HARTING eCatalogue	https://b2b.harting.com/09150043013

Identification

Category	Inserts
Series	Han-Quintax®
Description of the contact	for Han D® crimp contacts

Version

Gender	Male
Number of contacts	4
Additional contacts	+ shielding
Details	Please order crimp contacts separately.

Technical characteristics

Conductor cross-section	0.14 ... 2.5 mm ²
Rated current	10 A
Rated voltage	50 V
Rated impulse voltage	0.8 kV
Pollution degree	3
Contact resistance, shielding	≤100 mΩ
Limiting temperature	-40 ... +85 °C
Mating cycles	≥500

Material properties

Material (insert)	Polycarbonate (PC)
Colour (insert)	RAL 7032 (pebble grey)



Pushing Performance

Material properties

Material (shielding)	Zinc die-cast, nickel-plated
Material flammability class acc. to UL 94	V-0
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead

Specifications and approvals

Specifications	EN 60664-1 IEC 61984
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076

Commercial data

Packaging size	1
Net weight	23 g
Country of origin	Germany
European customs tariff number	85366990
eCl@ss	27440218 Module for industrial connectors (data)