



263.G - Sheathed chisels



Description:

- Engineers chisels.
- Hardness: - Tip hardened to 57 - 60 HRc. - Head hardened to 36 - 44 HRc.
- Cutting angle: 60°.



	A [mm]	A [in]	Diameter [mm]	Length L [mm]	Length L1 [mm]	Weight [Kg]
263.G19	15.0		12.0	190.0	15.0	0.165
263.G20	20.0		16.0	200.0		0.305
263.G22	25.0		18.0	20.0		0.415