Model 7274 / 7276

Features:

- 7/8" diameter
- Plastic 10-turn
- Wirewound





Model Styles

7274	6mm Shaft, 3/8" Bushing
7276	1/4" Shaft, 3/8" Bushing

Electrical

Standard Resistance Tolerance±5%Independent Linearity±0.25%Power Rating, Watts2.0 at 25°C derating to 0 at 105°CDielectric Strength1,000V rmsInsulation Resistance, Minimum1,000 MegohmsNoise, Maximum100 OhmsActual Electrical Travel3600° + 10° - 0°Tap Tolerance±3°End Voltage, Maximum (% of input voltage)0.25%	Resistance Range, Ohms	100 to 100K
Power Rating, Watts2.0 at 25°C derating to 0 at 105°CDielectric Strength1,000V rmsInsulation Resistance, Minimum1,000 MegohmsNoise, Maximum100 OhmsActual Electrical Travel3600° + 10° - 0°Tap Tolerance±3°	Standard Resistance Tolerance	±5%
Dielectric Strength1,000V rmsInsulation Resistance, Minimum1,000 MegohmsNoise, Maximum100 OhmsActual Electrical Travel3600° + 10° - 0°Tap Tolerance±3°	Independent Linearity	±0.25%
Insulation Resistance, Minimum1,000 MegohmsNoise, Maximum100 OhmsActual Electrical Travel3600° + 10° - 0°Tap Tolerance±3°	Power Rating, Watts	2.0 at 25°C derating to 0 at 105°C
Noise, Maximum100 OhmsActual Electrical Travel3600° + 10° - 0°Tap Tolerance±3°	Dielectric Strength	1,000V rms
Actual Electrical Travel $3600^{\circ} + 10^{\circ} - 0^{\circ}$ Tap Tolerance $\pm 3^{\circ}$	Insulation Resistance, Minimum	1,000 Megohms
Tap Tolerance ±3°	Noise, Maximum	100 Ohms
	Actual Electrical Travel	3600° + 10° – 0°
End Voltage, Maximum (% of input voltage) 0.25%	Tap Tolerance	±3°
	End Voltage, Maximum (% of input voltage)	0.25%

Environmental

Operating Temperature Range	-25°C to +105°C
Temperature Cycling	5 cycles, -25°C to +105°C (5% ΔR)
Shock, 6ms Sawtooth	100G's (0.1ms discontinuity max.)
Vibration	10G's, 10 to 500 Hz (5% Δ R, 0.1ms discontinuity max.)
Moisture Resistance	Five 24 hour cycles (3% ΔR)
High Temperature Exposure	1,000 hours at 105°C (5% ΔR)
Rotational Load Life	500K shaft rev. + 900 hrs. at rated wattage at 25°C (5% Δ R)

Specifications subject to change without notice.

General Note TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.



Mechanical

Total Mechanical Travel	3600° + 15° – 0°
Number of Gangs, Maximum	1
Weight, Nominal	0.42 oz.
Static Stop Strength, Maximum	60 ozin.
Backlash, Maximum	2°
Panel Nut Tightening Torque, Maximum	8 lbin.
Shaft End Play, Maximum	.010"
Shaft Radial Play, Maximum	.010"
Start/Run Torque, Maximum	1.5 ozin.

Standard Resistance Values, Ohms

	Theor	retical	
Total	Reso	lution	Tempco
Resistance	(% No	minal)	of Wire
100	0.0	059	±20 ppm/°C
200	0.0	037	±20 ppm/°C
500	0.0	030	±20 ppm/°C
1K	0.0)24	±20 ppm/°C
2K	0.0)20	±20 ppm/°C
5K	0.0	018	±20 ppm/°C
10K	0.0	017	±20 ppm/°C
20K	0.0	016	±20 ppm/°C
50K	0.0	010	±20 ppm/°C
100K	0.0	009	±20 ppm/°C
METRIC CONVERSIONS			
1 in.	25.4 mm	1 ozin.	0,007 N-m
1 oz.	28.4 gm	1 lbin.	0,113 N-m

Special Features


Center Tap	CT
Linearity Tape	LT
Flatted Shaft	FS
Shaft Lock	SL
Gold Plated Solder Lug Terminals (see optional terminal configuration)	FT

General Note


TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

BI Technologies 4200 Bonita Place, Fullerton, CA 92835 |Ph: +1 714 447 2300 www.bitechnologies.com | www.ttelectronics.com





OPTIONAL TERMINAL CONFIGURATION



General Note

TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

BI Technologies 4200 Bonita Place, Fullerton, CA 92835 | Ph: +1 714 447 2300 www.bitechnologies.com | www.ttelectronics.com




MATCHING TURNS COUNTING DIALS

2606, 2606S, 2607, 2607S, 2626, 2627, 2646, 2646S, 2647, 2647S, 2126, RB

CIRCUIT DIAGRAM

NOTES



General Note

TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

BI Technologies 4200 Bonita Place, Fullerton, CA 92835 | Ph: +1 714 447 2300 www.bitechnologies.com | www.ttelectronics.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

TT Electronics:

<u>7276R10KL.25</u> <u>7276R20KL.25</u> <u>7276R5KL.25</u> <u>7276R100KL.25</u> <u>7276R100L.25</u> <u>7276R1KL.25</u> <u>7276R200L.25</u> 7276R2KL.25 <u>7276R500L.25</u> <u>7276R50KL.25</u>