

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0934444101](#)
Status: **Active**
Overview: [ML-XT™ Sealed Connection System](#)
Description: ML-XT™ Sealed 6 Circuit Receptacle Housing, Pre-Assembled with Small Rear Seal and Cover, Black

Documents:

[Drawing \(PDF\)](#) [Packaging Specification 934430002-K \(PDF\)](#)
[Product Specification 934430010-P \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Application Specification 934430010-A \(PDF\)](#)

General

Product Family	Crimp Housings
Series	93444
Application	Power, Signal, Wire-to-Wire
Application Tooling Part Link	63824-5300
Overview	ML-XT™ Sealed Connection System
Product Name	ML-XT™
UPC	889056164597

Physical

Circuits (maximum)	6
Color - Resin	Black
Gender	Receptacle
Glow-Wire Compliant	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	9.410/g
Number of Rows	3
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	N/A
Polarized to Mating Part	Yes
Temperature Range - Operating	-55°C to +125°C

Electrical

Current - Maximum per Contact	13.0A
-------------------------------	-------

Material Info

Reference - Drawing Numbers

Application Specification	934430010-A
Packaging Specification	934430002-K
Product Specification	934430010-P
Sales Drawing	934430040-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/21/2016 (20 June
2016)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[93444 Series](#)

Mates With

[ML-XT™ Sealed 6 Circuit Plug Housing 93445-4101](#)

Use With

[ML-XT™ Male \(Pin\) Terminal 84524-0004 \(Nickel\)](#), [ML-XT™ Male \(Pin\) Terminal 84524-0014 \(Selective Gold\)](#), [ML-XT™ 6 Circuit Receptacle Wedgelock 93447](#), [ML-XT™ Blind Cavity Plug 93494-1000](#)