LIECHTENSTEIN (HEADQUARTERS) NEUTRIK AG, Im alten Riet 143, 9494 Schaan T +423 237 24 24, F +423 232 53 93, neutrik@neutrik.com

GERMANY / NETHERLANDS / DENMARK / AUSTRIA Neutrik Vertriebs GmbH, Felix-Wankel-Strasse 1, 85221 Dachau, Germany T +49 8131 28 08 90, neutrik@neutrik.de

GREAT BRITAIN

Neutrik (UK) Ltd., Westridge Business Park, Cothey Way Ryde, Isle of Wight PO33 1 QT T +44 1983 811 441, sales@neutrik.co.uk

FRANCE

Neutrik France SARL, Rue du Parchamp13, 92100 Boulogne-Billancourt T +33 1 41 31 67 50, info@neutrik.fr

USA / CANADA / MEXICO / SOUTH AMERICA

Neutrik USA Inc., 4115 Taggart Creek Road, Charlotte, North Carolina, 28208 T +1 704 972 3050, info@neutrikusa.com

JAPAN

Neutrik Limited, Yusen-Higashinihonbashi-Ekimae Bldg., 3-7-19 Higashinihonbashi, Chuo-ku, Tokyo 103 T +81 3 3663 47 33, mail@neutrik.co.jp

HONG KONG

Neutrik Hong Kong Ltd., Suite 18, 7th Floor Shatin Galleria T +852 2687 6055, sales@neutrik.com.hk

CHINA

Ningbo Neutrik Trading Co., Ltd., Shiqi Street, Yinxian Road West Fengjia Villiage, Hai Shu Area, Ningbo, Zhejiang, 315153 T +86 574 88250833, sales@neutrik.com.cn

Product Guide

THE SMART WAY TO CONNEC¹

ASSOCIATED COMPANIES

Contrik AG Steinackerstrasse 35, 8902 Urdorf, Switzerland T +41 44 736 50 10, contrik@contrik.ch

H. Adam GmbH Felix-Wankel-Straße 1, 85221 Dachau, Germany T +49 08131 28 08-0, anfrage@adam-gmbh.de



www.rean-connectors.com



















REAN

Excellent cost-performance ratio, robust design and reliable functionality are the strengths of REAN.

Based on long-time know-how connectors for professional audio-/ lighting- and digital signage applications are developed and produced on up to date production facilities. An efficient logistics system and a global sales network make a high availability and short delivery times possible. The REAN product range is the alternative solution for cost sensitive applications.

AUDIO

ROBUST RELIABLE COMPREHENSIVE

With REAN, the world's leading supplier of professional audio and video connectors - the Neutrik Group - offers a second global brand with a comprehensive product range.

REAN - A brand of Neutrik Group.





OUTDOOR XLR



Outdoor Z Series XLR










RCX3M-Z-000

RRX3F-Z-000


RRX3M-Z-001

- Rugged sealed XLR connector range for outdoor application
- UL94 V-0 rated materials
- Chrome&Black plated with fashionable finish and better abrasion performance
- IP65 rating provides outdoor protection under mated condition
- · Gold&Tin plated for best conductivity

RCX*F-Z-00*




RCX*M-Z-00*



RRX3F-Z-00*

REAN

RRX3M-Z-00*



RCX*F-Z-000 3/5 pole female XLR cable connector, IP65 rating protection, chrome plated housing, tin plated contacts RCX*F-Z-001 3/5 pole female XLR cable connector, IP65 rating protection, black plated housing, tin plated contacts RCX*F-Z-002 3/5 pole female XLR cable connector, IP65 rating protection, chrome plated housing, gold plated contacts RCX*M-Z-000 3/5 pole male XLR cable connector, IP65 rating protection, chrome plated housing, tin plated contacts RCX*M-Z-001 3/5 pole male XLR cable connector, IP65 rating protection, black plated housing, tin plated contacts RCX*M-Z-002 3/5 pole male XLR cable connector, IP65 rating protection, chrome plated housing, gold plated contacts RRX*F-Z-000 3/5 pole female XLR receptacle, D-Size Flange, solder cups, IP65 protection, chrome plated housing, tin plated contacts RRX*F-Z-001 3/5 pole female XLR receptacle, D-Size Flange, solder cups, IP65 protection, black plated housing, tin plated contacts RRX*F-Z-002 3/5 pole female XLR receptacle, D-Size Flange, solder cups, IP65 protection, black plated housing, gold plated contacts RRX*M-Z-000 3/5 pole male XLR receptacle, D-Size Flange, solder cups, IP65 protection, chrome plated housing, tin plated contacts RRX*M-Z-001 3/5 pole male XLR receptacle, D-Size Flange, solder cups, IP65 protection, black plated housing, tin plated contacts RRX*M-Z-002 3/5 pole male XLR receptacle, D-Size Flange, solder cups, IP65 protection, black plated housing, gold plated contacts Note: 1) Above products are provided in REAN plastic package with -1 for the article suffix, if need bulk package, - 0 for the article suffix and must be ordered in multiples of 100 pcs; 2) *: contact number (3 or 5)

| Specification | Cable Connectors | Receptacles |
|---------------------------|----------------------------------|----------------------------------|
| Electrical | | |
| Contact resistance | ≤5 mΩ | \leq 5 m Ω |
| Dielectric strength | 1.5 kV dc | 1.5 kV dc |
| Insulation resistance | $> 10 \text{ G}\Omega$ (initial) | $> 10 \text{ G}\Omega$ (initial) |
| Rated current per contact | 16 A (3 pole) / 7.5 A (5 pole) | 16 A (3 pole) / 7.5 A (5 pole) |
| Rated voltage | < 50 V | < 50 V |
| | | |

| Mechanical | | | |
|------------------------------|---|--------------------|----------------|
| Lifetime | > 1'000 mating cycles | > 1'000 ma | ating cycles |
| Insertion / Withdrawal force | ≤ 60 N | ≤ 60 |) N |
| Cable O.D. | 5.0 - 8.0 mm | Mounting direction | Front mounting |
| Wiresize (max.) | 1.5 mm²/16 AWG(3 pole)/1.0 mm²/18 AWG(5 pole) | Chassis shape | D |
| Wiring | Solder contacts | Solder co | ontacts |
| Locking device | Locking device | Locking | device |

| Material | |
|--------------------------------|-----------------|
| Bushing | |
| Bronze contact and plating | Tin (-000 & - |
| Insert | Polya |
| Locking element | Zinc |
| Zinc diecast shell and plating | Chrome (-000) / |
| Strain relief | |
| Sealing jacket | |
| | |

| Environmental | |
|-----------------------------|--|
| Flammability | |
| Protection class | |
| Standard compliance | |
| Solderability complies with | |
| Temperature range | |

Ordering Information

Details

Article Name

Z Series XLR

| U | U | D | U |
|---|---|---|---|
| | | | |



REAN

Polyamide - 001) / AU (-002) plating Tin (-000 & - 001) / AU (-002) plating amide (UL94-V0) Polyamide (UL94-V0) c diecast (latch) CK67 (spring) / Black (-001 & -002) plating Chrome (-000) / Black (-001 & -002) plating Polyamide Rubber Rubber

> UL 94-V0 IP65 (Mated or closed with rubber cap) IEC 61076-2-103 IEC 68-2-20 -20 °C to +70 °C



OUTDOOR RJ45



Outdoor RJ45/Ethernet Connectors





RRE8F-Z-00*





RCEM-Z-000

RRE8F-Z-000

- The RJ45 protection system for harsh and demanding environment
- Provide protection for the fragile RJ45 to ensure a stable Ethernet connection
- D-shape metal flange, stable and reliable
- IP65 protection when mating with coped Z-Series Ethernet receptacle
- UL94 V-0 rated materials
- Diecast shell cable carrier accepts the most common RJ45 plugs

RCEM-Z-00*





Ordering Information

| Article Name | Details |
|------------------------|---|
| RJ45 Cable Carr | iers |
| | |
| RCEM-Z-000 | Rugged RJ45 cable connector carrier, IP65 ratin |
| RCEM-Z-001 | Rugged RJ45 cable connector carrier, IP65 ratin |
| | |
| RJ45 Receptacle | S |
| | |
| RRE8F-Z-000 | Rugged RJ45 D-size feedthrough, IP65 rating p |
| RRE8F-Z-001 | Rugged RJ45 D-size feedthrough, IP65 rating p |

Note: Above products are provided in REAN plastic package with -1 for the article suffix, if need bulk package, -0 for the article suffix and must be ordered in multiples of 100 pcs

| Specification | Cable carriers | Receptacles |
|---------------------------|----------------|-------------------------|
| Electrical | | |
| Contact resistance | | ≤ 100 mΩ |
| Dielectric strength | - | 1kV dc |
| Frequency range | - | 1 – 100 MHz |
| Insulation resistance | - | $> 5 G\Omega$ (initial) |
| Rated current per contact | - | 1.5 A |
| Rated voltage | - | < 50 V |
| Transmission performance | - | CAT 5e |

| Mechanical | | |
|------------------------------|-----------------------|-----------------------|
| Lifetime | > 1'000 mating cycles | > 1'000 mating cycles |
| Insertion / Withdrawal force | ≤ 60 N | ≤ 60 N |
| Cable O.D. | 5.0 - 8.0 mm | - |
| Wiring | - | Feedthrough |
| Locking device | - | Latch lock |
| Mounting direction | - | Front mounting |
| Chassis shape | - | D |
| Chassis shape | - | D |

| Material | | |
|-----------------|------------------------------|------------------------------|
| Shell | Zinc diecast | Zinc diecast |
| Shell plating | Chrome (-000) / Black (-001) | Chrome (-000) / Black (-001) |
| Strain relief | Polyacetal (POM) | - |
| Contact | - | Bronze |
| Contact plating | - | AU |
| Insert | - | Polyamide (UL94-V0) |
| Locking element | - | Zinc diecast |

| Environmental | |
|---------------------|--|
| Flammability | |
| Protection class | |
| Standard compliance | |
| Temperature range | |





ing protection, chrome plated housing ing protection, black plated housing

g protection, chrome plated housing, with sealing cap g protection, black plated housing, with sealing cap

> UL 94-V0 IP65 (Mated or closed with rubber cap) TIA/EIA 586B, IEC 11801 -20 °C to +70 °C



TINY XLR



TINY XLR Cable Connectors










RT3FC-B

RT4FC-B-W


RT4FCT-B

RT5MC-B


- Available in 3,4,5 pin configuration
- Quick and easy assembly
- Rugged metal shell, excellent flexibility
- Shielding system Isolate noise and electromagnetic interference
- Rugged direct locking mechanism ensures a secure connection
- RT*FC-B sealing cap is available, waterproof when mated with RT*MP









Female Pin Layout (Front)






RT3MC-B



Male Pin Layout(Front)



Ordering Information

| Article Nan | ne | Details | | |
|-------------------|-----------------------|--|---|--|
| Female | Male | | | |
| RT3FC-B | RT3MC-B | 3 pole female/male TINY | XLR cable connector, black metal housing, gold pla | ted contacts, REAN plastic packaging |
| RT4FC-B | RT4MC-B | 4 pole female/male TINY | XLR cable connector, black metal housing, gold pla | ted contacts, REAN plastic packaging |
| RT5FC-B | RT5MC-B | 5 pole female/male TINY | XLR cable connector, black metal housing, gold pla | ted contacts, REAN plastic packaging |
| Waterproo | of Female (| Cable Connectors | | |
| RT3FC-B-W | | 3 pole female TINY XLR | connector, black metal housing, waterproof bushing | , gold plated contacts, REAN plastic packaging |
| RT4FC-B-W | | 4 pole female TINY XLR | connector, black metal housing, waterproof bushing | , gold plated contacts, REAN plastic packaging |
| RT5FC-B-W | | 5 pole female TINY XLR | connector, black metal housing, waterproof bushing | , gold plated contacts, REAN plastic packaging |
| Screw Loc | king Femal | e Connectors | | |
| RT3FCT-B | | 3 pole female TINY XLR | connector, black metal housing and nut, gold plated | contacts, REAN plastic packaging |
| RT4FCT-B | | 4 pole female TINY XLR | connector, black metal housing and nut, gold plated | contacts, REAN plastic packaging |
| RT5FCT-B | | 5 pole female TINY XLR | connector, black metal housing and nut, gold plated | contacts, REAN plastic packaging |
| Note: Above produ | cts provide bulk pack | age with -0 for the article suffix and | d must be ordered in multiples of 100 pcs | |
| Specificat | ion | | Cable Connectors | Screw Locking |
| | | | RT*FC-B/RT*MC-B* | RT*FCT-B |
| Electrica | I | | | |
| Contact rated | current | | < 5 A | < 5 A |
| Contact resista | ince | | ≤ 10 mΩ | \leq 10 m Ω |
| Dielectric stren | igth | | >1 GΩ | >1 GΩ |
| Insulation resi | stance | | >500 V rms | >500 V rms |
| Mechani | cal | | | |
| 116 | | | | |

| Mechanical | | |
|-----------------|-----------------------|-----------------------|
| Lifetime | > 1'000 mating cycles | > 1'000 mating cycles |
| Cable O.D. | 2.0 - 4.5 mm | 2.0 - 4.5 mm |
| Wiring | Solder contacts | Solder contacts |
| Wiresize (max.) | 0.22 mm² / 24 AWG | 0.22 mm² / 24 AWG |

| Material | | |
|----------------------|-------------------------------|-------------------------|
| Boot | ABS+TPU | ABS+TPU |
| Contact | Female : Bronze / Male: Brass | Bronze |
| Contact plating | Au | Au |
| Insert | PA66+30% GF | PA66+30% GF |
| Shell / Tube | Zinc alloys / Aluminum | Zinc alloys / Aluminum |
| Shell / Tube plating | Nickel / Black anodized | Nickel / Black anodized |
| Strain relief | POM | POM |
| Carrier | EPDM | - |
| Locking nut | - | Al, black anodized |
| - | | |

| Environmental | | |
|---------------|-----------------------------|--|
| | Temperature range | |
| | Solderability complies with | |







-30°C to +85°C IEC68-2-20







TINY XLR Receptacles



TINY XLR Adapters







RT5MPR



RA3MT-B

- 3, 4, 5 pole front / rear mountable
- Waterproof even under unmated condition
- Waterproof conncetiaon when mated with RT*FC-B-W 3 pole TINY XLR male / female XLR
- Convenient and quicl TINY XLR interconnected solution
- Ruggedized metal shell

RT3MP




Panel Cutouts




Pin Layout (front)

12 **REAN**






RA3FT-B







Ordering Information

| Article Name | Details | |
|---|---|--|
| Receptacles | | |
| RT3MP | | |
| R I SIVIF | 3 pole male TINY XLR receptacle, nickel plated metal he | |
| RT4MP | 4 pole male TINY XLR receptacle, nickel plated metal he | |
| RT5MP | 5 pole male TINY XLR receptacle, nickel plated metal he | |
| | | |
| Rear Mountable | Receptacles | |
| | | |
| RT3MPR | 3 pole male receptacle, rear mountable, nickel plated h | |
| RT4MPR | 4 pole male receptacle, rear mountable, nickel plated h | |
| RT5MPR | 5 pole male receptacle, rear mountable, nickel plated h | |
| | | |
| Adapters | | |
| DADET D | | |
| RA3FT-B | 3 pole TINY XLR adapter, male to female, black meta | |
| RA3MT-B | 3 pole TINY XLR adapter, female to male, black meta | |
| Note: Above products provide bulk package with -0 for the article suffix and must be ordered in m | | |

| Specification | Receptacles | Adapters |
|-----------------------------|-------------------------------|------------------------------|
| | RT*MP | RA3F/M-B |
| Electrical | | |
| Contact rated current | < 5 A | < 5 A |
| Contact resistance | ≤ 5 mΩ | $\leq 5 \text{ m}\Omega$ |
| Insulation resistance | >1 GΩ | >1 GΩ |
| Dielectric strength | >500 V rms | >500 V rms |
| Mechanical | | |
| Lifetime | > 1'000 mating cycles | > 1'000 mating cycles |
| Wiring | Solder contacts | |
| Wiresize (max.) | 0.22 mm ² / 24 AWG | - |
| | | |
| Material | | |
| Contact | Brass | Female: Bronze / Male: Brass |
| Contact plating | Au | Au |
| Insert | PA66+30% GF | PA66+30% GF |
| Shell | Zinc alloys | Zinc alloys |
| Shell plating | Nickel | Black |
| | | |
| Environmental | | |
| Temperature range | -30°C to +85°C | -20°C to +65°C |
| Colderability complian with | | |

| Specification | Receptacles RT*MP | Adapters RA3F/M-B |
|-----------------------------|-----------------------|------------------------------|
| Electrical | | |
| Contact rated current | < 5 A | < 5 A |
| Contact resistance | ≤ 5 mΩ | $\leq 5 \text{ m}\Omega$ |
| Insulation resistance | >1 GΩ | >1 GΩ |
| Dielectric strength | >500 V rms | >500 V rms |
| | | |
| Mechanical | | |
| Lifetime | > 1'000 mating cycles | > 1'000 mating cycles |
| Wiring | Solder contacts | - |
| Wiresize (max.) | 0.22 mm² / 24 AWG | - |
| | | |
| Material | | |
| Contact | Brass | Female: Bronze / Male: Brass |
| Contact plating | Au | Au |
| Insert | PA66+30% GF | PA66+30% GF |
| Shell | Zinc alloys | Zinc alloys |
| Shell plating | Nickel | Black |
| | | |
| Environmental | | |
| Temperature range | -30°C to +85°C | -20°C to +65°C |
| Calderability complies with | | |

| Specification | Receptacles RT*MP | Adapters RA3F/M-B |
|-----------------------------|-----------------------------|------------------------------|
| Electrical | | |
| Contact rated current | < 5 A | < 5 A |
| Contact resistance | ≤ 5 mΩ | \leq 5 m Ω |
| Insulation resistance | >1 GΩ | >1 GΩ |
| Dielectric strength | >500 V rms | >500 V rms |
| Mechanical | | |
| Lifetime | > 1'000 mating cycles | > 1'000 mating cycles |
| Wiring | Solder contacts | - |
| Wiresize (max.) | 0.22 mm² / 24 AWG | - |
| Material | | |
| Contact | Brass | Female: Bronze / Male: Brass |
| Contact plating | Au | Au |
| Insert | PA66+30% GF | PA66+30% GF |
| Shell | Zinc alloys | Zinc alloys |
| Shell plating | Nickel | Black |
| Environmental | | |
| Temperature range | -30°C to +85°C | -20°C to +65°C |
| Solderability complies with | IEC68-2-20 | - |

CONNECT

10



nousing, gold plated contacts, max. panel thickness: 3 mm, REAN plastic package nousing, gold plated contacts, max. panel thickness: 3 mm, REAN plastic package nousing, gold plated contacts, max. panel thickness: 3 mm, REAN plastic package

housing, gold plated contacts, max. panel thickness: 3 mm, REAN plastic package housing, gold plated contacts, max. panel thickness: 3 mm, REAN plastic package housing, gold plated contacts, max. panel thickness: 3 mm, REAN plastic package

tal housing, gold plated contacts, REAN plastic package tal housing, gold plated contacts, REAN plastic package

multiples of 100 pcs



XLR CABLE CONNECTORS



XLR Cable Connectors









- Ergonomic design, easy to use
- Rugged zinc diecast housing, long lifetime
- Chuck type strain relief provides the best cable retention, easy to assembly
- Provide rotable angle of right-angle products
- Rubber boot ensure the best cable protection
- Rugged latch locking system, provides secure connection

RC*F 70.0 [2.76*****] 019.3 (0.76") RC*M 67.0 [2.64*****] 019.3 10.76*1



Ø15.



@18.8

Ordering Information

| Article Nam | ie | Details |
|-------------|-----------|---|
| Straight A | ngle XLR | |
| | | |
| RC*F | RC*M | 3, 4, 5, 7 pole female/male XLR connectors, |
| RC*F-B | RC*M-B | 3, 4, 5, 7 pole female/male XLR connectors, |
| RC*F-BAG | RC*M-BAG | 3, 4, 5, 7 pole female/male XLR connectors, |
| | | |
| Right-angl | e XLR | |
| | | |
| RC*FR | RC*MR | 3, 4, 5, 7 pole female/male right-angle XLR |
| RC*FR-B | RC*M-B | 3, 4, 5, 7 pole female/male right-angle XLR |
| RC*FR-BAG | RC*MR-BAG | 3, 4, 5, 7 pole female/male right-angle XLR |
| | | |

Note: Above products provide bulk package with -0 for the article suffix and must be ordered in multiples of 100 pcs

| Specification | |
|------------------------------|--|
| Electrical | |
| Contact rated current | |
| Contact resistance | |
| Insulation resistance | |
| Dielectric strength | |
| | |
| Mechanical | |
| Lifetime | |
| Cable O.D. | |
| Wiring | |
| Wiresize (max.) | |
| Insertion / Withdrawal force | |
| | |

| Material | |
|-----------------|--|
| | |
| Bushing | |
| Contact | |
| Contact plating | |
| Insert | |
| Shell | |
| Shell plating | |
| Strain relief | |
| Button | |
| Button plating | |
| | |

| E | Environmental | |
|---|----------------------------|--|
| Т | emperature range | |
| S | olderability complies with | |



14 REAN

s, nickel plated metal housing, silver plated contacts, REAN plastic package s, black plated metal housing, gold plated contacts, REAN plastic package s, black plated metal housing, silver plated contacts, REAN plastic package

connectors, nickel plated metal housing, silver plated contacts, REAN plastic package connectors, black plated metal housing, gold plated contacts, REAN plastic package connectors, black plated metal housing, silver plated contacts, REAN plastic package

10 A (3/4 pole) / 7.5 A (5 pole) / 5 A (7 pole) $\leq 5 \text{ m}\Omega$ >1.5 GΩ >1kV dc

> > 1'000 mating cycles 4.0 - 7.0 mm Solder contacts 1.5 mm² / 16 AWG \leq 30 N / \leq 20 N

PA6+30% GF Female: Bronze / Male: Brass Ag / Au PA6+30% GF Zinc alloys Nickel / Black POM Zinc alloys Nickel





XLR Receptacles








RC3FDL-B

RC3MDL


RC5FDL

- Universal D-size metal shell
- Rugged zinc dieast shell, long-lasting
- Soldered 3, 4, 5 pole receptacles
- Black or nickel plating shell, nickel or gold plating contact
- Rugged latch locking system of female receptacles, provides secure connection

RC*FDL



RC*MDL



Ordering Information

| Article Name | Details |
|--------------|---|
| Female | |
| | |
| RC*FDL | 3, 4, 5 pole female XLR receptacles, nickel plate |
| RC*FDL-B | 3, 4, 5 pole female XLR receptacles, black plate |
| | |
| Male | |
| RC*MDL | 3, 4, 5 pole male XLR receptacles, nickel plated |
| RC*MDL-B | 3, 4, 5 pole male XLR receptacles, black plated |

| Specification | |
|---|--|
| Electrical | |
| Contact rated current Contact resistance | |
| Insulation resistance | |
| Dielectric strength | |

Mechanical

| Lifetime | |
|------------------|--|
| Insertion force | |
| Withdrawal force | |
| Locking device | |
| | |

| Material |
|-----------------|
| Contact |
| Contact plating |
| Insert |
| Shell |
| Shell plating |
| Button |
| Button plating |
| |
| Environmental |

| LIIVIIOIIIIIEIILAI | |
|--------------------|--|
| | |
| Temperature range | |

Solderability complies with

XLR RECEPTACLES

ated housing, tin plated contacts, bulk package ted housing, gold plated contacts, bulk package

ed housing, tin plated contacts, bulk package ed housing, gold plated contacts, bulk package

> 10 A (3/4 pole) / 7 A (5 pole) 5 m Ω (3/4 pole) / 7 m Ω (5 pole) >1 GΩ >1.5 kV dc

> > > 1'000 mating cycles $\leq 20 \text{ N}$ ≤20 N Latch lock (Female)

Female: Bronze / Male: Brass Tin / Au PA 6+30% GF Zinc alloys Nickel / Black 65 Mn Steel Nickel



XLR RECEPTACLES





Combo I Series







RCJ9FI-V-0




RCJ9FI-H-0


- Combined 3 pole XLR and 6.35mm jack space saving
- Horizontal / vertical PCB mount conformed to industry standards
- Stereo or mono version
- Full switching product is avaliable
- Latch lock or retention spring version

RCJ9FI-H-0

18 **REAN**



RCJ9FI-V



Ordering Information

| Article Name | 1/4" Jacks | 1/4" Switching | PCB Mount | Locking | Bulk Package |
|---------------|------------|----------------|------------|------------------|--------------|
| Combo I Recep | tacles | | | | |
| RCJ6FI-H | TRS | - | Horizontal | Latch Lock | - |
| RCJ6FI-H-0 | TRS | - | Horizontal | Retention Spring | - |
| RCJ6FI-V | TRS | - | Vertical | Latch Lock | - |
| RCJ6FI-V-0 | TRS | - | Vertical | Retention Spring | - |
| RCJ9FI-H | TRS | • | Horizontal | Latch Lock | - |
| RCJ9FI-H-0 | TRS | • | Horizontal | Retention Spring | - |
| RCJ9FI-V | TRS | • | Vertical | Latch Lock | - |
| RCJ9FI-V-0 | TRS | • | Vertical | Retention Spring | - |
| RCJ10FI-H | TRS | • | Horizontal | Latch Lock | - |
| RCJ10FI-H-0 | TRS | • | Horizontal | Retention Spring | - |
| RCJ10FI-V | TRS | • | Vertical | Latch Lock | - |
| RCJ10FI-V-0 | TRS | • | Vertical | Retention Spring | - |

Specification

Electrical Contact rated current Contact resistance Insulation resistance Dielectric strength Rated voltage

| Mechanical | |
|------------------|--|
| Lifetime | |
| Insertion force | |
| Withdrawal force | |
| Locking device | |
| | |

Material

| Contact | |
|--------------------|--|
| Contact plating | |
| Insert | |
| Shell | |
| Latch lock | |
| Latch lock plating | |
| Retention spring | |

Environmental

| Temperature range | |
|-----------------------------|--|
| Flammability complies with | |
| Solderability complies with | |

XLR RECEPTACLES

7.5 A \leq 10 m Ω > 10 GΩ 1500 V dc 50 V ac

> 1'000 mating cycles ≤25 N ≤25 N Latch lock (non -0) Retention Spring (-0)

Bronze Ni+Sn+Au Plating PA6+30% GF PA6+30% GF Stainless Steel Nickel Stainless Steel

-20 °C to +70 °C UL 94 HB IEC68-2-20



XLR RECEPTACLES





Combo A Series







RCJ6FA-H


RCJ9FA-V




RCJ9FA-H-0


- Combined 3 pole XLR and 6.35mm jack space saving
- Space saving 15% over the Combo I Series
- Horizontal / vertical PCB mount
- Latch lock or retention spring version

RCJ9FA-H-0



RCJ9FA-V





Ordering Information

| Article Name | 1/4" Jacks | 1/4" Switching | PCB Mount | Locking | Bulk Package |
|--------------|------------|----------------|------------|------------------|--------------|
| Combo A Rece | ptacles | | | | |
| RCJ6FA-H | TRS | - | Horizontal | Latch Lock | - |
| RCJ6FA-H-0 | TRS | - | Horizontal | Retention Spring | - |
| RCJ6FA-V | TRS | - | Vertical | Latch Lock | - |
| RCJ6FA-V-0 | TRS | | Vertical | Retention Spring | - |
| RCJ9FA-H | TRS | • | Horizontal | Latch Lock | - |
| RCJ9FA-H-0 | TRS | • | Horizontal | Retention Spring | - |
| RCJ9FA-V | TRS | • | Vertical | Latch Lock | - |
| RCJ9FA-V-0 | TRS | • | Vertical | Retention Spring | - |
| RCJ10FA-H | TRS | • | Horizontal | Latch Lock | - |
| RCJ10FA-H-0 | TRS | • | Horizontal | Retention Spring | - |
| RCJ10FA-V | TRS | • | Vertical | Latch Lock | - |
| RCJ10FA-V-0 | TRS | • | Vertical | Retention Spring | - |

Specification

Electrical Contact rated current Contact resistance Insulation resistance Dielectric strength Rated voltage

| Mechanical | |
|------------------|--|
| Lifetime | |
| Insertion force | |
| Withdrawal force | |
| Locking device | |
| | |

Material

| Contact | |
|--------------------|--|
| Contact plating | |
| Insert | |
| Shell | |
| Latch lock | |
| Latch lock plating | |
| Retention spring | |

Environmental

| Temperature range |
|-----------------------------|
| Flammability complies with |
| Solderability complies with |



XLR RECEPTACLES

3 A \leq 15 m Ω >10 GΩ 1500 V dc 50 V ac

> 1'000 mating cycles \leq 20 N \leq 20 N Latch lock (non -0) Retention Spring (-0)

Bronze Ni+Sn+Au Plating PA6+30% GF PA6+30% GF Stainless Steel Nickel Stainless Steel

-20 °C to +70 °C UL 94-V0 IEC68-2-20



PLUGS&JACKS





6.35mm Plugs







RP2RC-BAG

- Rugged Zinc alloy shell reliable quality
- Chuck type strain relief excellent cable retention, easy to assembly
- Ergonomic compact right-angle plug high storage density
- Nickel / gold plated mono / stereo 1/4" plug
- Optional right-angle version

RP2C

RP3RC





Ordering Information

| | Article Name | Details |
|--|--------------|--|
| | 6.35mm Plugs | |
| | RP2C | Mono 1/4" plug, nickel plated housing, nicke |
| | RP2C-B | Mono 1/4" plug, black plated housing, gold |
| | RP2C-BAG | Mono 1/4" plug, black plated housing, nicke |
| | RP3C | Stereo 1/4" plug, nickel plated housing, nick |
| | RP3C-B | Stereo 1/4" plug, black plated housing, gold |
| | RP3C-BAG | Stereo 1/4" plug, black plated housing, nicke |
| | RP2RC | Mono 1/4" right-angle plug, nickel plated ho |
| | RP2RC-B | Mono 1/4" right-angle plug, black plated ho |
| | RP2RC-BAG | Mono 1/4" right-angle plug, black plated ho |
| | RP3RC | Stereo 1/4" right-angle plug, nickel plated he |
| | RP3RC-B | Stereo 1/4" right-angle plug, black plated ho |
| | RP3RC-BAG | Stereo 1/4" right-angle plug, black plated ho |

Note: Above products provide bulk package with -0 for the article suffix and must be ordered in multiples of 100 pcs

| Specification | |
|-----------------------|--|
| Electrical | |
| Contact rated current | |
| Contact resistance | |
| Insulation resistance | |
| Dielectric strength | |
| | |
| Mechanical | |
| Lifetime | |
| Cable O.D. | |
| Wiring | |
| Wiresize (max.) | |

| Material | | |
|-----------------|--|--|
| Boot | | |
| Contact | | |
| Contact plating | | |
| Shell | | |
| Shell plating | | |
| Strain relief | | |

Environmental

| Temperature range | |
|-----------------------------|--|
| Flammability complies with | |
| Solderability complies with | |



PLUGS&JACKS

el plated contacts, REAN plastic packaging plated contacts, REAN plastic packaging el plated contacts, REAN plastic packaging kel plated contacts, REAN plastic packaging d plated contacts, REAN plastic packaging kel plated contacts, REAN plastic packaging ousing, nickel plated contacts, REAN plastic packaging ousing, gold plated contacts, REAN plastic packaging ousing, nickel plated contacts, REAN plastic packaging nousing, nickel plated contacts, REAN plastic packaging ousing, gold plated contacts, REAN plastic packaging nousing, nickel plated contacts, REAN plastic packaging


> depends on mating connector depends on mating connector >1.5 GΩ 1kV dc

> > > 1'000 mating cycles 4.0 - 7.0 mm Solder contacts 1.0 mm² / 18 AWG

PA6+30% GF Brass (CuZn39Pb3) Nickel / Au Zinc alloy Nickel / Black POM

-20 °C to +70 °C UL 94 HB IEC68-2-20





6.35mm Plugs NYS Series

NYS204





• 6.35mm plug for various engineering applications


• Optional different cable sizes


NYS201

- Unique design of spring bushing, provide excellent cable protection
- Large taper diecast housing and cable O.D.


NYS201

NYS204





NYS225



Ordering Information

| Article Name | Details |
|--------------|--|
| NYS Series | |
| NYS201 | Mono 1/4" plug, diecast metal handle, flexib |
| NYS202 | Stereo 1/4" plug, diecast metal handle, flexi |
| NYS203 | Mono 1/4" plug, plastic handle, flexible anti |
| NYS204 | Stereo 1/4" plug, plastic handle, flexible ant |
| NYS225 | Mono 1/4" plug, large metal nickel plated h |
| NYS225B | Mono 1/4" plug, large metal black plated ha |
| NYS225L | Mono 1/4" plug, large metal nickel plated hand |
| NYS225GS | Mono 1/4" plug, tip switched to ground if n |

| Specification | NYS201/202 Series | NYS203/204 Series | NYS225 Series |
|------------------------------|-----------------------------|-----------------------------|-----------------------------|
| Electrical | | | |
| Contact rated current | depends on mating connector | depends on mating connector | depends on mating connector |
| Insulation resistance | >1 GΩ | >1 GΩ | >1 GΩ |
| Dielectric strength | 0.5kV dc | 0.5kV dc | 0.5kV dc |
| Mechanical | | | |
| Lifetime | > 1'000 mating cycles | > 1'000 mating cycles | > 1'000 mating cycles |
| Insertion / Withdrawal force | ≤ 60 N | ≤ 60 N | ≤ 60 N |
| Cable O.D. | ≤ 8.5 mm | ≤ 6.5 mm | ≤ 10 mm |
| Material | | | |
| Boot | POM | POM | POM |
| Sleeve & Inner | Zinc alloy | Zinc alloy | Zinc alloy |
| Sleeve plating | Nickel | Nickel | Nickel |
| Inner plating | Nickel | Nickel | Nickel |
| Shell | Zinc diecast (ZnAl4Cu1) | ABS | Zinc diecast (ZnAl4Cu1) |
| Shell plating | Nickel | Nickel / Black | Nickel / Black |
| Bushing | Polyamides | Polyamides | Polyamides |
| Cable Clamp | Steel | Steel | Steel |
| Spring | - | High quality spring steel | - |
| Environmental | | | |
| Temperature range | | -20 °C to +70 °C | |
| 1 | | | |

| Contact rated current Insulation resistancedepends on mating connector > 1 GQdepends on mating connector > 1 GQdepends on mating connector > 1 GQDielectric strength $0.5kV dc$ $0.5kV dc$ $0.5kV dc$ Me c h a n i c alLifetime Insertion / Withdrawal force C able O.D.> 1'000 mating cycles $\leq 60 N$ > 1'000 mating cycles $\leq 6.5 mm$ > 1'000 mating cycles $\leq 10 mm$ Material | Specification | NYS201/202 Series | NYS203/204 Series | NYS225 Series |
|---|------------------------------|-----------------------------|-----------------------------|-----------------------------|
| Insulation resistance Dielectric strength> 1 GO O.5kV dc> 1 GO O.5kV dcMechanicalLifetime Insertion / Withdrawal force Cable O.D.> 1'000 mating cycles ≤ 60 N> 1'000 mating cycles ≤ 60 N> 1'000 mating cycles ≤ 60 NMaterialBoot Sleeve & Inner Sleeve plating NickelPOM Nickel NickelPOM Nickel Nickel Nickel Nickel NickelPOM Nickel Nickel Nickel Nickel Nickel Nickel Nickel Nickel Sleit Steel Shell platingPOI POI POI ABSBoshing Cable Clamp SteelPOI Steel Steel SteelPOI Steel Steel SteelPOI Steel Steel SteelEnvironmental | Electrical | | | |
| Dielectric strength Dielectric strength Dielectric strength Dielectric strength Dielectric strength 0.5kV dc 0.5kV dc Mechanical Lifetime > 1'000 mating cycles > 1'000 mating cycles Insertion / Withdrawal force ≤ 60 N ≤ 60 N Cable 0.D. ≤ 8.5 mm ≤ 6.5 mm Material Boot POM POM Sleeve & Inner Zinc alloy Zinc alloy Sleeve & Inner Zinc alloy Zinc alloy Sleeve plating Nickel Nickel Inner plating Nickel Nickel Shell Zinc diecast (ZnAl4Cu1) ABS Shell plating Nickel Nickel / Black Bushing Polyamides Polyamides Cable Clamp Steel Steel Spring - High quality spring steel | Contact rated current | depends on mating connector | depends on mating connector | depends on mating connector |
| Mechanical Lifetime > 1'000 mating cycles > 1'000 mating cycles Insertion / Withdrawal force ≤ 60 N ≤ 60 N ≤ 60 N Cable O.D. ≤ 8.5 mm ≤ 6.5 mm ≤ 10 mm Material Boot POM POM POM Sleeve & Inner Zinc alloy Zinc alloy Zinc alloy Sleeve & Inner Zinc diloy Zinc alloy Zinc alloy Sleeve & Inner Zinc diloy Zinc alloy Zinc alloy Sleeve & Inner Zinc diloy Zinc alloy Zinc alloy Sleeve Blating Nickel Nickel Nickel Inner plating Nickel Nickel Nickel Shell Zinc diecast (ZnAl4Cu1) ABS Zinc diecast (ZnAl4Cu1) Shell plating Nickel Nickel / Black Nickel / Black Bushing Polyamides Polyamides Polyamides Cable Clamp Steel Steel Steel Spring - High quality spring steel - | Insulation resistance | >1 GΩ | >1 GΩ | >1 GΩ |
| Lifetime > 1'000 mating cycles > 1'000 mating cycles > 1'000 mating cycles Insertion / Withdrawal force ≤ 60 N ≤ 60 N ≤ 60 N Cable O.D. ≤ 8.5 mm ≤ 6.5 mm ≤ 10 mm Material Material Boot POM POM POM Sleeve & Inner Zinc alloy Zinc alloy Zinc alloy Sleeve plating Nickel Nickel Nickel Inner plating Nickel Nickel Nickel Shell Zinc diecast (ZnAl4Cu1) ABS Zinc diecast (ZnAl4Cu1) Shell plating Nickel Nickel / Black Nickel / Black Bushing Polyamides Polyamides Polyamides Cable Clamp Steel Steel Steel Spring - High quality spring steel - | Dielectric strength | 0.5kV dc | 0.5kV dc | 0.5kV dc |
| Insertion / Withdrawal force ≤ 60 N ≤ 60 N ≤ 60 N Cable O.D. ≤ 8.5 mm ≤ 6.5 mm ≤ 10 mm Material Material POM POM POM Boot POM POM POM Seve a long Zinc alloy Seve a long Nickel Nickel Nickel Nickel Nickel Nickel Nickel Nickel Seve a long Seve a long Seve a long Nickel Nickel / Black Seve a long Seve a l | Mechanical | | | |
| Cable O.D. ≤ 8.5 mm ≤ 6.5 mm ≤ 10 mm Material Boot POM POM POM Sleeve & Inner Zinc alloy Zinc alloy Zinc alloy Sleeve plating Nickel Nickel Nickel Inner plating Nickel Nickel Nickel Shell Zinc diecast (ZnAl4Cu1) ABS Zinc diecast (ZnAl4Cu1) Shell plating Nickel Nickel / Black Nickel / Black Bushing Polyamides Polyamides Polyamides Cable Clamp Steel Steel Steel Spring - High quality spring steel - | Lifetime | > 1'000 mating cycles | > 1'000 mating cycles | > 1'000 mating cycles |
| MaterialPOMPOMPOMBootPOMPOMPOMSleeve & InnerZinc alloyZinc alloyZinc alloySleeve platingNickelNickelNickelInner platingNickelNickelNickelShellZinc diecast (ZnAl4Cu1)ABSZinc diecast (ZnAl4Cu1)Shell platingNickelNickel / BlackNickel / BlackBushingPolyamidesPolyamidesPolyamidesCable ClampSteelSteelSteelSpring-High quality spring steel- | Insertion / Withdrawal force | ≤ 60 N | ≤ 60 N | ≤ 60 N |
| BootPOMPOMPOMSleeve & InnerZinc alloyZinc alloyZinc alloySleeve platingNickelNickelNickelInner platingNickelNickelNickelShellZinc diecast (ZnAl4Cu1)ABSZinc diecast (ZnAl4Cu1)Shell platingNickelNickel / BlackNickel / BlackBushingPolyamidesPolyamidesPolyamidesCable ClampSteelSteelSteelSteelSteelFnvironmental | Cable O.D. | ≤ 8.5 mm | ≤ 6.5 mm | ≤ 10 mm |
| BootPOMPOMPOMSleeve & InnerZinc alloyZinc alloyZinc alloySleeve platingNickelNickelNickelInner platingNickelNickelNickelShellZinc diecast (ZnAl4Cu1)ABSZinc diecast (ZnAl4Cu1)Shell platingNickelNickel / BlackNickel / BlackBushingPolyamidesPolyamidesPolyamidesCable ClampSteelSteelSteelSteelSteelFnvironmental | | | | |
| Sleeve & InnerZinc alloyZinc alloyZinc alloySleeve platingNickelNickelNickelInner platingNickelNickelNickelShellZinc diecast (ZnAl4Cu1)ABSZinc diecast (ZnAl4Cu1)Shell platingNickelNickelNickel / BlackBushingPolyamidesPolyamidesPolyamidesCable ClampSteelSteelSteelSpring-High quality spring steel- | Material | | | |
| Sleeve platingNickelNickelInner platingNickelNickelInner platingNickelNickelShellZinc diecast (ZnAl4Cu1)ABSShell platingNickelNickel / BlackBushingPolyamidesPolyamidesCable ClampSteelSteelSpring-High quality spring steel- | Boot | POM | POM | POM |
| Inner platingNickelNickelInner platingNickelNickelShellZinc diecast (ZnAl4Cu1)ABSZinc diecast (ZnAl4Cu1)Shell platingNickelNickel / BlackNickel / BlackBushingPolyamidesPolyamidesPolyamidesCable ClampSteelSteelSteelSpring-High quality spring steel- | Sleeve & Inner | Zinc alloy | Zinc alloy | Zinc alloy |
| ShellZinc diecast (ZnAl4Cu1)ABSZinc diecast (ZnAl4Cu1)Shell platingNickelNickel / BlackNickel / BlackBushingPolyamidesPolyamidesPolyamidesCable ClampSteelSteelSteelSpring-High quality spring steel- | Sleeve plating | Nickel | Nickel | Nickel |
| Shell platingNickelNickel / BlackNickel / BlackBushingPolyamidesPolyamidesPolyamidesCable ClampSteelSteelSteelSpring-High quality spring steel- | Inner plating | Nickel | Nickel | Nickel |
| Bushing Polyamides Polyamides Cable Clamp Steel Steel Spring - High quality spring steel - | Shell | Zinc diecast (ZnAl4Cu1) | ABS | Zinc diecast (ZnAl4Cu1) |
| Cable Clamp Steel Steel Steel Spring - High quality spring steel - | Shell plating | Nickel | Nickel / Black | Nickel / Black |
| Spring - High quality spring steel - Environmental | Bushing | Polyamides | Polyamides | Polyamides |
| Environmental | Cable Clamp | Steel | Steel | Steel |
| | Spring | - | High quality spring steel | - |
| Temperature range -20 °C to +70 °C | Environmental | | | |
| | Temperature range | | -20 °C to +70 °C | |

| Specification | NYS201/202 Series | NYS203/204 Series | NYS225 Series |
|------------------------------|-----------------------------|-----------------------------|-----------------------------|
| Electrical | | | |
| Contact rated current | depends on mating connector | depends on mating connector | depends on mating connector |
| Insulation resistance | >1 GΩ | >1 GΩ | >1 GΩ |
| Dielectric strength | 0.5kV dc | 0.5kV dc | 0.5kV dc |
| Mechanical | | | |
| Lifetime | > 1'000 mating cycles | > 1'000 mating cycles | > 1'000 mating cycles |
| Insertion / Withdrawal force | ≤ 60 N | ≤ 60 N | ≤ 60 N |
| Cable O.D. | ≤ 8.5 mm | ≤ 6.5 mm | ≤ 10 mm |
| | | | |
| Material | | | |
| Boot | POM | POM | POM |
| Sleeve & Inner | Zinc alloy | Zinc alloy | Zinc alloy |
| Sleeve plating | Nickel | Nickel | Nickel |
| Inner plating | Nickel | Nickel | Nickel |
| Shell | Zinc diecast (ZnAl4Cu1) | ABS | Zinc diecast (ZnAl4Cu1) |
| Shell plating | Nickel | Nickel / Black | Nickel / Black |
| Bushing | Polyamides | Polyamides | Polyamides |
| Cable Clamp | Steel | Steel | Steel |
| Spring | - | High quality spring steel | - |
| Environmental | | | |
| Temperature range | | -20 °C to +70 °C | |

| | En | viro | n m e | ntal |
|--|----|------|-------|------|
|--|----|------|-------|------|

| Temperature range | |
|-----------------------------|--|
| Flammability complies with | |
| Solderability complies with | |



PLUGS&JACKS

ible anti-kink boot protection, REAN plastic package kible anti-kink boot protection, REAN plastic package ti-kink boot protection, tail spring, REAN plastic package ti-kink boot protection, tail spring, REAN plastic package handle for speaker cables, REAN plastic package nandle for speaker cables, REAN plastic package ndle for speaker cables, large cable outlet (10 mm), REAN plastic package not inserted (silent) for guitar cables, REAN plastic package

> UL 94 HB IEC68-2-20







6.35mm Plugs NYS Series







NYS207-2


- 6.35mm plug for engineering applications
- Right-angle plugs with (red / black) polyamides cover for selection
- Optional different plating for housing, contact, sleeves
- Optional different cable sizes





- Uniqed mono right-angle plug
 - Pan head space saving design for engineering applications
 - Optional bickel / black plated housing
 - Optional black / white Logo

NYS224









Ordering Information

| ordering inform | Ordering Information | | | |
|--------------------------------|----------------------|---|-------------------------------------|---------------------------------|
| Article Name | Detail | s | | |
| NYS Series | | | | |
| NYS224 | Mono 1 | /4" plug, long diecast nickel plated | handle | |
| NYS224G | Mono 1 | /4" plug, long diecast nickel plated | handle, gold plated sleeve and inne | r |
| NYS224AG | Mono 1 | /4" plug, long diecast gold plated h | andle, gold plated sleeve and inner | |
| NYS224BG | | /4" plug, long diecast black plated | • · | |
| NYS224GT | | Nono 1/4" plug, long diecast nickel plated handle, gold plated sleeve and inner | | |
| NYS224L | | Iono 1/4" plug, long diecast nickel plated handle, large cable outlet (9.5 mm) | | |
| NYS224S | | /4" plug, long diecast nickel plated | | ot inserted (silent) |
| NYS228 | | 1/4" plug, long diecast nickel plated | | |
| NYS228G | | 1/4" plug, long diecast nickel plated | | |
| NYS228BG | | 1/4" plug, long diecast black plated | | r |
| NYS228GT | | 1/4" plug, long diecast nickel plated | | ng provide red cover (pys207.2) |
| NYS207 NYS208 | | /4" right-angle plug, nickel plated h 1/4" right-angle plug, nickel plated l | | |
| Note: Above products are provi | | | | |
| Pancake | | ····· | | |
| RP2RCF | Mono 1 | /4" right-angle plug, pan head, nick | el plated bandle. REAN plastic pack | aging |
| RP2RCF-BAG | | /4" right-angle plug, pan head, blac | | |
| | | e with -0 for the article suffix and must be ordered | | |
| Specification | | NYS207/208 Series | NYS224/228 Series | Pancake Series |
| Electrical | | | | |
| | _ | | | |
| Contact rated current | | depends on mating connector | depends on mating connector | depends on mating connector |
| Insulation resistance | _ | >1 GΩ | >1 GΩ | >1 GΩ |
| Dielectric strength | | 0.5kV dc | 0.5kV dc | 0.5kV dc |
| Mechanical | | | | |
| Lifetime | | > 1'000 mating cycles | > 1'000 mating cycles | > 1'000 mating cycles |
| Insertion / Withdrawal | force | ≤ 60 N | ≤ 60 N | ≤ 60 N |
| Cable O.D. | | ≤ 7.5 mm | ≤ 9.5 mm | 4 - 7 mm |
| Wiresize | | | | |
| Material | | | | |
| | _ | 2014 | DOLL | |
| Boot | | POM | POM | - |
| Sleeve & Inner | _ | Brass | Brass | Brass |
| Sleeve plating | | Nickel | Nickel / Au | Nickel / Au |
| Inner plating | | Nickel | Nickel / Au | Nickel / Au |
| Shell | | Zinc alloy, red/black polyamides cover | Zinc alloy | Steel |
| Shell plating | | Nickel | Nickel / Black | Nickel / Black |
| Bushing | | Polyamides | - | - |
| Cable Clamp | | Steel | Steel | - |
| Environmenta | I | | | |
| Temperature range | | | -20 °C to +70 °C | |
| Flammability complies | with | | UL 94 HB | |
| Solderability complies | | | IEC68-2-20 | |
| ., | | | | |

| Temperature range | |
|-----------------------------|--|
| Flammability complies with | |
| Solderability complies with | |





3.5mm Plugs





RTP3C





NYS226BG


NYS231G

- Ergonomic space saving design
- Full metal rugged shell, reliable quality
- Easy to assembly and use


RTP2C

- Optional mono 2 pole and stereo 3 pole
- Max. cable O.D. up to 8.5mm


RTP2C




RTP3C



NYS226



NYS231



Ordering Information

| | Article Name | Details |
|--|--------------|--|
| | 3.5mm Plugs | |
| | DTD+C | |
| | RTP*C | 3.5mm mono / stereo plug, nickel plated har |
| | RTP*C-B | 3.5mm mono / stereo plug, black plated han |
| | RTP*C-BAG | 3.5mm mono / stereo plug, black plated han |
| | | Note: *2/3, above products provide bulk package with -0 for th |
| | NYS226 | 3.5mm mono plug, nickel plated handle, nick |
| | NYS226B | 3.5mm mono plug, black plated handle, nick |
| | NYS226BG | 3.5mm mono plug, black plated handle, gold |
| | NYS226G | 3.5mm mono plug, nickel plated handle, gol |
| | NYS226L | 3.5mm mono plug, nickel plated handle, nick |
| | NYS231 | 3.5mm stereo plug, nickel plated handle, nic |
| | NYS231B | 3.5mm stereo plug, black plated handle, nick |
| | NYS231BG | 3.5mm stereo plug, black plated handle, gold |
| | NYS231G | 3.5mm stereo plug, nickel plated handle, gol |
| | NYS231L | 3.5mm stereo plug, nickel plated handle, nic |
| | NYS231LBG | 3.5mm stereo plug, black plated handle, gold |
| | NYS231LL | 3.5mm stereo plug, nickel plated handle, nickel |
| | NYS231BG-LL | 3.5mm stereo plug, black plated handle, gold |
| | | |

| Specification | RTP*C Series | NYS226/231 Series | |
|------------------------------|-----------------------------|-----------------------------|--|
| Electrical | | | |
| Contact rated current | depends on mating connector | depends on mating connector | |
| Insulation resistance | \geq 1.5 G Ω | $\geq 1.5 \text{ G}\Omega$ | |
| Dielectric strength | 1kV dc | 1kV dc | |
| Mechanical | | | |
| Lifetime | > 1'000 mating cycles | > 1'000 mating cycles | |
| Insertion / Withdrawal force | ≤ 60 N | ≤ 60 N | |
| Cable O.D. | 2-6 mm | 2-8.5 mm | |
| Material | | | |
| Boot | PVC | - | |
| Sleeve & Inner | Brass | Brass | |
| Sleeve plating | Nickel / Au | Nickel / Au | |
| Inner plating | Nickel / Au | Nickel / Au | |
| Shell | Zinc alloy | Zinc alloy | |
| Shell plating | Nickel / Black | Nickel / Black | |
| Bushing | Polyamides | Polyamides | |
| Cable Clamp | Steel | Steel | |
| Environmental | | | |
| | | | |
| Temperature range | -20 °C to | | |

| Contact rated current | depends on mating connector | depends on mating connector |
|------------------------------|-----------------------------|-----------------------------|
| Insulation resistance | $\geq 1.5 \text{ G}\Omega$ | $\geq 1.5 \text{ G}\Omega$ |
| Dielectric strength | 1kV dc | 1kV dc |
| Mechanical | | |
| Lifetime | > 1'000 mating cycles | > 1'000 mating cycles |
| Insertion / Withdrawal force | ≤ 60 N | ≤ 60 N |
| Cable O.D. | 2-6 mm | 2-8.5 mm |
| Material | | |
| Boot | PVC | - |
| Sleeve & Inner | Brass | Brass |
| Sleeve plating | Nickel / Au | Nickel / Au |
| Inner plating | Nickel / Au | Nickel / Au |
| Shell | Zinc alloy | Zinc alloy |
| Shell plating | Nickel / Black | Nickel / Black |
| Bushing | Polyamides | Polyamides |
| | Steel | Steel |

| Environmental | |
|-----------------------------|--|
| Temperature range | |
| Flammability complies with | |
| Solderability complies with | |



28 **REAN**

PLUGS&JACKS

ndle, nickel plated sleeve and inner, REAN plastic packaging ndle, gold plated sleeve and inner, REAN plastic packaging ndle, nickel plated sleeve and inner, REAN plastic packaging the article suffix and must be ordered in multiples of 100 pcs ckel plated sleeve and inner, REAN plastic packaging kel plated sleeve and inner, REAN plastic packaging Id plated sleeve and inner, REAN plastic packaging old plated sleeve and inner, REAN plastic packaging ckel plated sleeve and inner, large cable outlet, REAN plastic packaging ckel plated sleeve and inner, REAN plastic packaging ckel plated sleeve and inner, REAN plastic packaging old plated sleeve and inner, REAN plastic packaging old plated sleeve and inner, REAN plastic packaging ckel plated sleeve and inner, large cable outlet, REAN plastic packaging Id plated sleeve and inner, large cable outlet, REAN plastic packaging el plated sleeve and inner, x-large cable outlet, REAN plastic packaging ld plated sleeve and inner, x-large cable outlet, REAN plastic packaging

UL 94 HB IEC68-2-20





6.35mm Vertical Jacks








RJ5VM


RJ3VM

RJ3VI-S


- 6.35mm vertical PCB mountable jack
- Knob mounting nut, less product assembly time
- Spring-loaded ground contact, excellent contact integrity
- Optional metal / plastic thread
- High density compact product design, space saving


RJ3VM





RJ5VM





Ordering Information

| Article Name | Details |
|-----------------|---|
| 6.35mm Vertical | Jacks |
| RJ3VM | 6.35mm mono jack, black plastic housing, m |
| RJ3VM-D1 | 6.35mm mono jack, black plastic housing, m |
| RJ3VM-S | 6.35mm mono jack, black plastic housing, m |
| RJ3VI | 6.35mm mono jack, black plastic housing, pl |
| RJ3VI-D1 | 6.35mm mono jack, black plastic housing, pla |
| RJ3VI-S | 6.35mm mono jack, black plastic housing, so |
| RJ5VM | 6.35mm stereo jack, normalling contacts, bla |
| RJ5VM-D1 | 6.35mm stereo jack, normalling contacts, blac |
| RJ5VM-S | 6.35mm stereo jack, normalling contacts, bla |
| RJ5VI | 6.35mm stereo jack, normalling contacts, bla |
| RJ5VI-D1 | 6.35mm stereo jack, normalling contacts, blac |
| RJ5VI-S | 6.35mm stereo jack, normalling contacts, bla |

Specification

| Electrical | |
|-----------------------|--|
| Contact rated current | |
| Contact resistance | |
| Insulation resistance | |
| Dielectric strength | |
| | |
| Mechanical | |

| Lifetime | |
|------------------|--|
| Insertion force | |
| Withdrawal force | |
| | |
| Material | |

| Contact | |
|-----------------|--|
| Contact plating | |
| Shell | |
| Thread nose | |
| Washer | |
| | |

Environmental

| Temperature range | |
|-----------------------------|--|
| Solderability complies with | |

netal nose, vertical PCB contacts, bulk package netal nose, vertical D1 PCB contacts, bulk package

netal nose, solder lugs, bulk package

lastic nose, vertical PCB contacts, bulk package

lastic nose, vertical D1 PCB contacts, bulk package

older lugs, bulk package

ack plastic housing, metal nose, vertical PCB contacts, bulk package ick plastic housing, metal nose, vertical D1 PCB contacts, bulk package lack plastic housing, solder lugs, bulk package

ack plastic housing, plastic nose, vertical PCB contacts, bulk package ick plastic housing, plastic nose, vertical D1 PCB contacts, bulk package lack plastic housing, solder lugs, bulk package

> 3 A < 10 mΩ ≥ 1 GΩ 500 V dc

> 1'000 mating cycles \leq 20 N \geq 10 N

Bronze Ag PA6+30% GF Plastic / Zinc alloy CRS(Cold Rolled Steel)





6.35mm Horizontal Jacks










NYS212

NYS215


NYS216H

NYS219

- 6.35mm horizontal PCB mountable jack
- Provide mono / stereo version
- Various pin lengths and types, meet different application requirements
- Optional metal / plastic threaded nose







Ordering Information

| Article Name | Details |
|------------------------------|---|
| 6.35mm Horizo | ntal Jacks |
| NYS212 | 6.35mm stereo jack, black plastic housing w |
| NYS2122 | 6.35mm mono jack, black plastic housing wi |
| NYS216 | 6.35mm stereo jack, black plastic housing w |
| NYS216G | 6.35mm stereo jack, black plastic housing w |
| NYS216H | 6.35mm stereo jack, black plastic housing w |
| NYS2162 | 6.35mm mono jack, black plastic housing wi |
| NYS2162H | 6.35mm mono jack, black plastic housing wi |
| NYS215 | 6.35mm stereo jack, black plastic housing, m |
| NYS2152 | 6.35mm mono jack, black plastic housing, m |
| NYS2152G | 6.35mm mono jack, black plastic housing, gold |
| NYS2152G-DI-U | 6.35mm mono jack, black plastic housing, g |
| NYS219 | 6.35mm stereo jack, black plastic housing, lo |
| NYS2192 | 6.35mm mono jack, black plastic housing, lo |
| Note: Above products are pro | ovided in bulk package |

| 5 m | ~ ~ | са | ÷ . | ~ ~ |
|-----|-----|--------|-----|------------|
| טכ | ec | La | uи | оп |
| | | | | |

| Electrical | |
|-----------------------|--|
| Contact rated current | |
| Contact resistance | |
| Insulation resistance | |
| Dielectric strength | |

Mechanical

| Lifetime | |
|------------------|--|
| Insertion force | |
| Withdrawal force | |
| | |

| Ма | terial | |
|-------|--------------|--|
| Cont | tact | |
| Cont | tact plating | |
| Shell | I | |
| Thre | ad nose | |
| Was | her | |

Environmental

| Temperature range | | |
|-----------------------|---------|--|
| Solderability complie | es with | |



with washer and nut, solder taps, normalling contacts with washer and nut, solder taps, normalling contacts with washer and nut, 8.2 mm distance to PCB with washer and nut, gold plated contacts, 8.2 mm distance to PCB with washer and nut, half threaded nose, 8.2 mm distance to PCB with washer and nut, 8.2 mm distance to PCB with washer and nut, half threaded nose, 8.2 mm distance to PCB with washer and nut, half threaded nose, 8.2 mm distance to PCB metal nut, two brown washers, 8.2 mm distance to PCB metal nut, two brown washers, 8.2 mm distance to PCB metal nut, two brown washers, 8.2 mm distance to PCB gold plated contacts, metal nut, two brown washers, 8.2 mm distance to PCB gold plated contacts, metal nut, two brown washers, solder tap version long contacts, 12.5 mm distance to PCB

> 3 A ≤ 10 mΩ > 2000 mΩ (initial) 500 V dc

> 5'000 mating cycles \leq 20 N \geq 10 N

Bronze Ag / Au PA6+30% GF Plastic / Zinc alloy PA6+15% GF / Epoxy plate





6.35mm Jacks





NYS230

- 6.35mm jacks, panel mountable
- Provide mono / stereo version
- Precision machined thread, nut and screw close combination
- Adapt various panel thickness




Metal Jacks




- 6.35mm / 3.5mm stereo metal jacks
- Simple design, easy installation
- Full metal design for engineering use


NYS229




NYS230



NYS2203



NYS240



Ordering Information

| Article Name | Details |
|--------------------------------|---|
| 6.35mm Jacks | |
| NYS229 NYS229L | 6.35mm mono open jack, with washer and n 6.35mm mono open jack, with washer and n |
| NYS230 | 6.35mm stereo open jack, with washer and n Note: Above products are provided in bulk package |
| Metal Jacks | |
| NYS221 NYS2202 NYS2203 | 6.35mm stereo jack, long-threaded bushing v6.35mm mono jack, long-threaded bushing v6.35mm stereo jack, long-threaded bushing v |
| NYS2202P NYS2203P NYS240 | 6.35mm mono jack, metal handle, max. cable 6.35mm stereo jack, metal handle, max. cable 3.5mm stereo jack, metal handle, max. cable |
| NYS240BG NYS240L | 3.5mm stereo jack, black metal handle, gold p 3.5mm stereo jack, metal handle, max. cable |

| Specification | NYS229/230 Series | |
|-----------------------|---------------------|--|
| Electrical | | |
| Contact rated current | 3 A | |
| Contact resistance | < 10 mΩ | |
| Insulation resistance | > 2000 mΩ (initial) | |
| Dielectric strength | 500 V dc | |
| | | |

| Mechanical | |
|------------------|-----------------------|
| Lifetime | > 5'000 mating cycles |
| Insertion force | ≤ 20 N |
| Withdrawal force | ≥ 10 N |

| Material | |
|-----------------|--------|
| Contact | Bronze |
| Contact plating | Tin |
| Shell | Brass |
| Thread nose | Brass |
| Washer | Steel |

| Envi | r o n | m e n | tal |
|------|-------|-------|-----|
|------|-------|-------|-----|

Temperature range Solderability complies with



nut, 0.205" faston tabs, for up to 3.5 mm panel thickness nut, 0.205" faston tabs, for up to 6.5 mm panel thickness nut, 0.205" faston tabs, for up to 3.5 mm panel thickness

with washer and nut, full metal design, bulk package with washer and nut, full metal design, REAN plastic package with washer and nut, full metal design, REAN plastic package e O.D. 6 mm, REAN plastic package le O.D. 6 mm, REAN plastic package O.D. 4 mm, REAN plastic package plated contacts, max. cable O.D. 4 mm, REAN plastic package

O.D. 6 mm, REAN plastic package

NYS221/2202 Series

3 A 3 A < 10 mΩ $< 10 \text{ m}\Omega$ $> 2000 \text{ m}\Omega \text{ (initial)}$ $> 2000 \text{ m}\Omega \text{ (initial)}$ 500 V dc 500 V dc > 5'000 mating cycles > 5'000 mating cycles ≤20 N ≤20 N ≥ 10 N ≥ 10 N Bronze Bronze

NYS240

| Tin | Tin / Au |
|-------|------------|
| Brass | Zinc alloy |
| Brass | Brass |
| Steel | - |
| | |
| | |

| -20 °C to +70 °C | |
|------------------|--|
| IEC68-2-20 | |
| | |








- Various range of converter products, meet the needs of different connectors
- Provide 6.35mm mono/stereo plug plug and jack jack adapters
- Optional 6.35mm stereo plug 3.5mm jack adapters
- Unique phono adapters, easy to operate
- Full metal shell design, increase the mating cycles, prolong lifetime

NYS355



NYS236



Ordering Information

| Article Name | Details |
|--------------|--|
| Adapters | |
| | |
| NYS227 | 3.5mm stereo plug - 6.35mm plug adapter, full |
| NYS236 | 6.35mm mono jack - 6.35mm mono jack adapt |
| NYS237 | 6.35mm mono plug - 6.35mm mono plug adap |
| NYS238 | 6.35mm stereo jack - 6.35mm stereo jack adap |
| NYS239 | 6.35mm stereo plug - 6.35mm stereo plug ada |
| NYS355 | Phono jack - jack adapter, full metal, REAN plas |

| Specification |
|--|
| Electrical |
| Contact resistance Insulation resistance Dielectric strength |
| Mechanical |
| Lifetime Insertion force |
| Withdrawal force |
| Material |
| Shell |

Environmental

Contact

| Temperature range | |
|-----------------------------|--|
| Solderability complies with | |




Ill metal, REAN plastic package pter, full metal, REAN plastic package apter, full metal, REAN plastic package apter, full metal, REAN plastic package apter, full metal, REAN plastic package astic package

> < 10 mΩ > 2000 m Ω (initial) 50Hz 500VAC

> 1'000 mating cycles ≤20 N ≥ 10 N

> Bronze Brass





RCA Plugs / Jacks





RF2C-AU-0


NYS352

NYS373-2


NYS367-4


- High quality RCA plugs and jacks, precision processing
- Color code ring and color bushing for channel identification
- Optional gold plated contact products, ensure the stability of signal transmission
- Ergonomic product design, easy to operate
- Plastic or metal shell products, meet various needs

NYS373




NYS352





NYS367



Ordering Information

| Article Name | Details |
|---|---|
| RCA Plugs / Jacl | ks |
| RF2C-AU-0 | RCA phono plug, nickel plated shell, gold pla |
| RF2C-AU-2 | RCA phono plug, nickel plated shell, gold pla |
| RF2C-B-0 | RCA phono plug, black plated shell, gold pla |
| RF2C-B-2 | RCA phono plug, black plated shell, gold pla |
| NYS352 | Heavy duty phono plug, nickel plated shell, r |
| NYS352AG | Heavy duty phono plug, gold plated shell, ni |
| NYS352B | Heavy duty phono plug, black plated shell, n |
| NYS352BG | Heavy duty phono plug, black plated shell, g |
| NYS352G | Heavy duty phono plug, nickel plated shell, g |
| NYS373-0 | Phono plug, black shell, black color coding, gold plate |
| NYS367-0 Note: 1) color coding for NYS36 | Phono plug, gold plated contacts, black colo |

Specification

| | Electrical | |
|---|-----------------------|--|
| 1 | Rated voltage | |
| j | Contact resistance | |
| | Insulation resistance | |
| | Dielectric strength | |

Mechanical

| Lifetime | |
|------------------|--|
| Insertion force | |
| Withdrawal force | |

| Material | |
|-----------------|--|
| Contact | |
| Contact plating | |
| Shell | |
| Shell pltating | |
| Boot | |
| Cable clamp | |
| Insert | |
| Lug | |
| | |

| Environmental | |
|-----------------------------|--|
| Temperature range | |
| Solderability complies with | |



38 REAN

RCA PLUGS/JACKS

lated contacts, black boot, REAN plastic packaing lated contacts, red boot, REAN plastic packaing lated contacts, black boot, REAN plastic packaing lated contacts, red boot, REAN plastic packaing

nickel plated contacts

nickel plated contacts

nickel plated contacts

gold plated contacts

gold plated contacts

ates contacts, rubber anti-kink boot, chuck type strain relief, cable O.D. 3.5 - 6.1 mm lor coding

5367/373 series are provided in REAN plastic package


depends on mating connector depends on mating connector > 2000 m Ω (initial) 500 V dc

> > 1'000 mating cycles \leq 20 N ≥ 10 N

> > Bronze Ag / Au / Nickel Zinc alloy Nickel / Black PVC Steel / POM Brass Brass



LOUDSPEAKER CONNECTORS



Loudspeaker Connectors








RLS4FC

RLS4MPZ


RLS4MDZ-H


- Using fiberglass material, rugged insert and shell
- Solid keyway, reliable and suitable
- Robust lock system, safe locking
- Chuck type strain relief, maximum cable capacity, quick and convenient installation
- Sealed design, model types in the speaker connector application field

RLS4FC




RLS4MPZ





03.3



Ordering Information

| Article Name | Details |
|----------------|--|
| Cable Connecto | rs |
| RLS4FC | 4 pole loudspeaker cable connector with late |
| Receptacles | |
| RLS4MDZ-H | 4 pole loudspeaker receptacle, D-Size front hori |
| RLS4MDZ-V | 4 pole loudspeaker receptacle, D-Size front vert |
| RLS4MPZ | 4 pole loudspeaker receptacle, D-Size front more |

| Specification | Cable connectors RLS4FC | Receptacles RLS4MDZ-*/RLS4MPZ |
|--|----------------------------|---|
| Electrical | | |
| Contact rated current | continuous 30 A rms | continuous 30 A rms |
| Contact resistance | $\leq 5 \text{ m}\Omega$ | $\leq 5 \text{ m}\Omega$ |
| Insulation resistance | >1 GΩ | >1 GΩ |
| Dielectric strength | 4kV dc | 4kV dc |
| Rated voltage | 250 V | 250 V |
| Attention: Cable connectors and receptacles are not to be used as an AC mains or power supply connector! | | |

| Mechanical | | |
|--------------------|-----------------------|--|
| Lifetime | > 1'000 mating cycles | > 1'000 mating cycles |
| Chassis type | - | D |
| Cable O.D. | 6.5 -10 mm | - |
| Wiring | Screw | flat tab (4.8 × 0.5 mm) or soldering |
| Locking device | Quick Lock | - |
| Mounting direction | - | Front or rear mounting |

| Material | | | |
|-----------------|------------|------------|--|
| Contact | Brass | Bronze | |
| Contact plating | Ag | Ag | |
| Insert | PBT | - | |
| Shell | PA6+30% GF | PA6+30% GF | |
| Strain relief | POM | - | |
| Locking element | Zinc alloy | - | |
| Boot | PA6+30% GF | - | |

| Environmental | | |
|-----------------------------|------------------|------------------|
| Temperature range | -30 °C to +80 °C | -30 °C to +80 °C |
| Flammability | UL 94-V0 | UL 94-V0 |
| Solderability complies with | - | IEC68-2-20 |

Solderability c




40 **REAN**

tch lock, chuck type strain relief, REAN plastic package

rizontal mounted, PCB contacts, REAN plastic package rtical mounted, PCB contacts, REAN plastic package punted, solder cup contacts, REAN plastic package





Power Connectors



RCAC3I-G-000



RRAC3I-G-000






RCAC30-G-000


RRAC3O-G-000

- High current capacity, rated at 20A / 250V ac
- Rugged twist lock system, ergonomic quick lock design
- Color coding divided, power-in and power-out versions with different keying, avoid the possibility of intermating
- UL recognized components
- Chuck type strain relief, reliable cable capacity

RCAC3I-G / RCAC3O-G



RRAC3I-G / RRAC3O-G



Ordering Information

| Article Name | Details |
|----------------|--|
| Power Connecto | rs |
| RCAC3I-G-000 | Cable connector, blue housing, twist lock, s |
| RRAC3I-G-000 | Receptacle, blue housing, air tight design, fl |
| RCAC3O-G-000 | Cable connector, grey housing, twist lock, s |
| RRAC3O-G-000 | Receptacle, grey housing, air tight design, fl |
| | |

Note: Above products are bulk packaged with -0 for the article suffix and must be ordered in multiples of 100 pcs

| Specification | Cable connectors | Receptacles |
|--|---------------------|---------------------|
| Electrical | | |
| Number of contacts | 2 + PE | 2 + PE |
| Rated current per contact | 20 A rms | 20 A rms |
| Rated Voltage | 250 V | 250 V |
| Dielectric strength | 4 kV ac | 4 kV ac |
| Contact resistance | \leq 3 m Ω | \leq 3 m Ω |
| Insulation resistance (after dampheat) | >0.1 GΩ | >0.1 GΩ |

| Mechanical | | |
|------------------|--|---------------------------------------|
| Retention method | Twist lock | Twist lock |
| Cable O.D. | 6 - 15 mm | 6 - 15 mm |
| Wiring | Screw type terminals or soldering | Flat tabs (4.8 x 0.5 mm) or soldering |
| | Wiresize: 2.5 mm ² / 14 AWG | |

| Shell | HC polymer HB | HC polymer HB |
|-----------------|---------------|---------------|
| Insert | PA6+30% GF | PA6+30% GF |
| Contact | Brass | Bronze |
| Contact plating | Ag | Ag |
| Strain relief | POM | POM |

| Temperature range | |
|-----------------------------|--|
| Solderability complies with | |




screw type terminals, power inlet flat tabs or soldering terminals, power inlet screw type terminals, power outlet flat tabs or soldering terminals, power outlet

| -30 °C to +80 °C | |
|------------------|--|
| IEC68-2-20 | |



POWER & DATA CONNECTORS



Ordering Information

| | Article Name | Details |
|---|-------------------------------|--|
| | | |
| | Cable Connector | rs |
| | RCAC3F-X-000 | Lockable cable connector, power inlet, screw |
| | RCAC3M-X-000 | Lockable cable connector, power outlet, scre |
| 1 | - | |
| | Receptacles | |
| | RRAC3F-X-000 | Receptacle, 1/4" flat tabs, power outlet |
| | RRAC3M-X-000 | Receptacle, 1/4" flat tabs, power inlet |
| | Note: Above products are bulk | packaged with -0 for the article suffix, plastic bag with -1 and mus |
| | | |

Accessories



RA-X-001

RRAC3M-X-000 sealing cover, IP 65

| Specification | Cable connectors | Receptacles |
|--|---------------------|------------------------|
| Electrical | | |
| Number of contacts | 2 + PE | 2 + PE |
| Rated current per contact | 20 A rms 1) | 20 A rms ¹⁾ |
| Rated Voltage | 250 V ac | 250 V ac |
| Dielectric strength | 4 kV dc / 2.8 kV ac | 4 kV dc / 2.8 kV ac |
| Contact resistance | $\leq 2 m\Omega$ | $\leq 2 m\Omega$ |
| Insulation resistance (after dampheat) | >0.1 GΩ | >1 GΩ |

| Mechanical | | |
|------------------|--|--------------------------|
| Retention method | Twist lock | Twist lock |
| Lifetime | > 5'000 mating cycles | > 5'000 mating cycles |
| Cable O.D. | 6 - 12 mm | - |
| Wiring | Screw type terminals | Flat tabs (4.8 x 0.5 mm) |
| | Wiresize: 1.0 - 2.5 mm ² / 12 AWG | - |

| Shell | Polyamide | Polyamide |
|-----------------|--------------|--------------|
| Insert | Polyamide | Polyamide |
| Contact | Copper alloy | Copper alloy |
| Contact plating | Ag | Ag |
| Strain relief | PBT | - |

| Temperature range |
|----------------------------|
| Flammability complies with |

1) : Appliance coupler acc. IEC 60320 limited to 16 A ac

44 REAN

w type terminals, IP65 rating ew type terminals, IP65 rating

st be ordered in multiples of 100 pcs



RA-X-003

RRAC3F-X-000 sealing cover, IP 65

-30 °C to +80 °C UL 94 V0



POWER & DATA CONNECTORS





Ethernet Connectors






Receptacles


RRE8F-D-001

- Cable carrier accepts the most common RJ45 plugs
- Industrial application design, provide protection for the fragile RJ45 to ensure stable connection
- Chrome / black plated housing
- Cable connectors do not include a RJ45 plug
- CAT5e according to ISO/IEC 11801 and TIA/EIA 568B
- D shape flange
- Rugged latch lock system
- Vertical PCB mount

RE8MY-1







| <u> </u> | | 1 | | 4 i |
|----------|-----|-------|-----|-----|
| | eri | ιητο | rma | тюп |
| •••• | | | | |

| Article Name | Details |
|------------------|--|
| RJ45 Cable Carri | iers |
| | |
| RE8MY-1 | Cable carrier, do not include RJ45 plug, chr |
| RE8MY-1-B | Cable carrier, do not include RJ45 plug, bla |
| | |
| RJ45 Receptacles | |
| | |
| RRE8F-D-001 | Rugged RJ45 receptacles, D shape mental fla |
| RRE8F-D-001 | Rugged RJ45 receptacles, D shape mental fla |

| Specification | | | |
|---------------------------|----------------|----------------------|--|
| Electrical | Cable Carriers | Receptacles | |
| Contact resistance | - | \leq 10 m Ω | |
| Dielectric strength | - | 1kV dc | |
| Frequency bandwidth | - | 1 – 100 MHz | |
| Insulation resistance | - | > 0.5 GΩ | |
| Rated current per contact | - | 1.5 A | |
| Rated Voltage | - | < 50 V | |
| Transmission performance | | CAT 5e | |

| Mechanical | | |
|------------------------------|-----------------------|---------------------------------|
| Lifetime | > 1'000 mating cycles | > 2'000 mating cycles |
| Insertion / Withdrawal force | ≤ 20 N | ≤ 20 N |
| Cable O.D. | 4.0 - 8.0 mm | Panel thickness max. 4 mm 0.16' |
| Wiring | - | Vertical PCB mount |
| Locking device | - | Latch lock |
| Mounting direction | - | Front mounting |
| Chassis shape | - | D |
| Power over Ethernet | - | PoE+ acc. IEEE 802.3at |

| Material | | |
|-----------------|----------------|--------------|
| Shell | Zinc alloy | Zinc alloy |
| Shell plating | Chrome / Black | Black |
| Strain relief | POM | - |
| Contact | - | Bronze |
| Contact plating | - | Au |
| Insert | - | PBTP 15 % GR |
| Locking element | - | Zinc diecast |
| Button | - | 65 Mn Steel |
| Button plating | - | Nickel |
| | | |

Environmental

| Flammability | |
|---------------------|--|
| Standard compliance | |
| Temperature range | |



rome plated housing ack plated housing

lange, vertical PCB mount, latch lock Note: Above products are bulk packaged with -0 for the article suffix and must be ordered in multiples of 100 pcs

> UL 94 V-0 TIA/EIA 586B, IEC11801 -30 °C to +80 °C





DIN Connectors






NYS323


NYS325

- Conformed to standard multi-pin connector series
- Unbalanced line inputs and outputs for device ports
- Optional gold plated housing and contacts
- Provide 3, 5, 7 pole version

NYS323







Ordering Information

| Article Name | Details |
|-----------------------|--|
| DIN Connectors | |
| | |
| NYS321 | 3 pole DIN cable connector, male, nickel plated |
| NYS321G | 3 pole DIN cable connector, male, nickel plated |
| NYS322 | 5 pole DIN cable connector, male, nickel plated |
| NYS322G | 5 pole DIN cable connector, male, nickel plated |
| NYS322AG | 5 pole DIN cable connector, male, gold plated h |
| NYS323 | 7 pole DIN cable connector, male, nickel plated |
| NYS323G | 7 pole DIN cable connector, male, nickel plated |
| | |
| DIN Receptacles | |
| | |
| NYS324 | 3 pole DIN receptacles, female, nickel plated ho |
| NYS325 | 5 pole DIN receptacles, female, nickel plated ho |
| NYS326 | 7 pole DIN receptacles, female, nickel plated ho |
| | |

| Specification | DIN Cable connectors | DIN Receptacles |
|---------------------------------|-----------------------|-----------------------|
| Electrical | | |
| Number of contacts | 3/5/7 | 3 / 5 / 7 |
| Contact resistance | ≤ 10 mΩ | \leq 10 m Ω |
| Insulation resistance (initial) | >1000 MΩ | >1000 MΩ |
| Rated Voltage | 50 V ac | 50 V ac |
| Withstand Voltage | 0.5kV dc | 0.5kV dc |
| Mechanical | | |
| Lifetime | > 1'000 mating cycles | > 1'000 mating cycles |
| Insertion force | ≤ 24 -56 N | ≤ 24 -56 N |
| Withdrawal force | > 3 - 7.5 N | > 3 - 7.5 N |
| Sanaration force per contact | > 120 N | > 120 N |

| Μ | e c | h a | ni | c a l | |
|---|-----|-----|----|-------|--|
| | | | | | |

| Specification | DIN Cable connectors | DIN Receptacles |
|---------------------------------|-----------------------|-----------------------|
| Electrical | | |
| Number of contacts | 3 / 5 / 7 | 3 / 5 / 7 |
| Contact resistance | \leq 10 m Ω | ≤ 10 mΩ |
| Insulation resistance (initial) | >1000 MΩ | >1000 MΩ |
| Rated Voltage | 50 V ac | 50 V ac |
| Withstand Voltage | 0.5kV dc | 0.5kV dc |
| | | |
| Mechanical | | |
| Lifetime | > 1'000 mating cycles | > 1'000 mating cycles |
| Insertion force | ≤ 24 -56 N | ≤ 24 -56 N |
| Withdrawal force | > 3 - 7.5 N | > 3 - 7.5 N |
| Separation force per contact | > 120 N | > 120 N |

| Material | | |
|-----------------|-------------|--------------------|
| Shell | Zinc alloy | High-Quality Steel |
| Shell plating | Nickel / Au | Nickel |
| Contact | Brass | Bronze |
| Contact plating | Ag / Au | Ag |
| Insert | PA6+30% GF | PA6+30% GF |
| Strain relief | PVC | - |

| Environmental | |
|-----------------------------|--|
| Temperature range | |
| Solderability complies with | |



I housing, silver plated contacts, REAN plastic package I housing, gold plated contacts, REAN plastic package housing, silver plated contacts, REAN plastic package housing, gold plated contacts, REAN plastic package housing, gold plated contacts, REAN plastic package housing, silver plated contacts, REAN plastic package housing, gold plated contacts, REAN plastic package

ousing, silver plated contacts, bulk package ousing, silver plated contacts, bulk package ousing, silver plated contacts, bulk package

| -30 °C to +85 °C | |
|------------------|--|
| IEC68-2-20 | |



DUAL BANANA PLUG



Dual banana plug






NYS508-B

NYS508-R

- Standard dual banana plug for high power output devices
- Gold plated contacts, ensure perfect transmission performance
- Optional black / red housing

NYS5508-B



Dual Banana Plug

| NYS508-B | Dual Banana Plug, cable O.D. 6.0 - 10.5 m |
|----------|---|
| NYS508-R | Dual Banana Plug, cable O.D. 6.0 - 10.5 m |

Details

Specification

Article Name

Ordering Information

| Electrical | |
|---------------------------------|--|
| Contact resistance | |
| Insulation resistance (initial) | |
| Dielectric strength | |
| Rated Voltage | |

Mechanical

| Lifetime | |
|------------------|--|
| Insertion force | |
| Withdrawal force | |

Material

| Contact | |
|-----------------|--|
| Contact plating | |
| Shell | |
| Shell color | |
| Retainers | |
| Nut | |
| Nut plating | |
| Strain relief | |

Environmental

| Temperature range | |
|-----------------------------|--|
| Solderability complies with | |



DUAL BANANA PLUG

nm, gold plated contacts, black, bulk package mm, gold plated contacts, red, bulk package

> \leq 10 m Ω > 1000 MΩ 500V dc 50 Vac

> 1'000 mating cycles $\leq 56 \text{ N}$ > 7.5 N

Bronze Au PA6+30%GF Black / Red / Customize PA6+30%GF Steel Nickel POM







Patch Panels






Stage Box




В

120 (4.



- 8 I/O 1/4" patch panels
- Rugged metal housing
- Convenient assembly, easy to use

NYS SSR-8





52 **REAN**


| Special module system for size and space customization |
|--|
|--|


- Personalized I/O connector combination, optional various length
- Convenient assembly
- 3 pole IDC XLR, no stripping or soldering required
- Does not contain self-adhesive channel digital label, need to be ordered separately

87 1347

Cost-effective

| A型 | |
|-------|--|
| | |
| CTELL | |
| | |





| NSB3A | 372 (14.65') |
|------------|----------------------|
| NSB4A | 491 (19.33') |
| | |
| | |
| В | Length |
| B NSB1B | Length 132 (5.2') |

Length

132 (5.2')

252 (9.93')

372 (14.65')

Α

NSB1A NSB2A

NSB3B

NSB1C-8/0

| С | Length |
|-------|--------------|
| NSB1C | 132 (5.2') |
| NSB2C | 252 (9.93') |
| NSB3C | 372 (14.65') |

| Ordering Inform | nation | |
|---------------------------|--|-----------|
| Article Name | Details | |
| Patch Panels | | |
| NYS-SSR-8 | 8 line in - 8 line out 1/4" patch panels | |
| Stage Box - A | | |
| NSB1A-8/4 | Length 1, 8 line in (female/output) - 4 line out (male/ input) | |
| NSB2A-12/4 | Length 2, 12 line in (female/output) - 4 line out (male/ input) | |
| NSB2A-20/4 | Length 2, 20 line in (female/output) - 4 line out (male/ input) | |
| NSB3A-32/4 | Length 3, 32 line in (female/output) - 4 line out (male/ input) | |
| NSB4A-40/4 | Length 4, 40 line in (female/output) - 4 line out (male/ input) | |
| NSB4A-40/8 | Length 4, 40 line in (female/output) - 8 line out (male/ input) | |
| Stage Box - B | | |
| NSB1B-8/0 | Length 1, 8 line in (female/output) | |
| NSB2B-12/4 | Length 2, 12 line in (female/output) - 4 line out (male/ input) | |
| NSB2B-16/0 | Length 2, 16 line in (female/output) | |
| NSB3B-20/4 | Length 3, 20 line in (female/output) - 4 line out (male/ input) | |
| Stage Box - C | | |
| NSB1C-8/0 | Length 1, 8 line in (female/output) | |
| NSB2C-12/4 | Length 2, 12 line in (female/output) - 4 line out (male/ input) | |
| NSB3C-20/4 | Length 3, 20 line in (female/output) - 4 line out (male/ input) | |
| (Delivery of bulk product | ts, including boxes, cover plates, brackets, cable joints and screws) | |
| | | |
| Specification | Patch Panels | Stage Box |
| Electrical | | |
| Pated current | depends on mating connector | 2 ^ |

| Specification | Patch Panels | Stage Box | | |
|------------------------------|-----------------------------|--|--|--|
| Electrical | | | | |
| Rated current | depends on mating connector | 2 A | | |
| Contact resistance | depends on mating connector | < 5 mΩ | | |
| Insulation resistance | >1 GΩ | >1 GΩ | | |
| Dielectric strength | 500 V dc | 500 V dc | | |
| | | | | |
| Mechanical | | | | |
| Lifetime | > 1'000 mating cycles | > 1'000 mating cycles | | |
| Insertion / Withdrawal force | \leq 10 N / \geq 10 N | \leq 10 N / \geq 10 N | | |
| Cable O.D. | - | 15 -20 mm | | |
| Wiresize | - | 0.22 mm ² /24 AWG or 0.14 mm ² /26 AWG | | |
| | | | | |

| Material | | | |
|-------------------|----------------|------------------|------------------|
| Housing | | Al | Al |
| Square plate | | - | POM |
| Cover | | Thermoplastic | Thermoplastic |
| Contact | Brass / Bronze | Nickel plated | Gold plated |
| Temperature range | | -25 °C to +70 °C | -25 °C to +70 °C |
| | | | |

THE

| Ρ | Δ | Т | C | н | Ρ | Δ | Ν | F | S |
|---|---|---|----------|---|---|---|---|---|---|
| | | | | | | | | | |

