3M[™] Power Clamp Header

3 mm, Straight, 1 and 2 Row, 5 and 10 Contacts

356 Series



- · Accepts one or two Power Clamp Wiremount Sockets
- · Accepts branch and terminator connectors
- Side to side stackable at 9 mm pitch on PCB
- Integrated press-fit board retention pins retain the connector to the board during wave soldering
- Polarization of retention pins on two-row header and polarization pin on one-row header prevent incorrect mounting.
- · CC-Link Communication Interconnect Standard
- One touch latching mechanism maintains a reliable interconnection in demanding field applications
- Keyed to prevent reverse insertion of sockets
- Polarization options ensures proper interconnection of mated connectors
- RoHS Compliant. See paragraphs E1 and C1 of RoHS
 Compliant. See the Regulatory Information Appendix (RIA) in
 the "RoHS compliance" section of www.3M.com/Interconnects
 for compliance information (RIA E1 & C1 apply).

Date Modified: December 20, 2009

TS-2274-C Sheet 1 of 3

Physical

Insulation:

Body Material: 1 Row - PBT, 2 Row - Nylon

Flammability: UL 94V-0 Body Color: Black

Contact:

Material: Copper Alloy

Plating:

Underplating: 2.5 μm Ni minimum Wiping Area: 0.5 μm Au minimum

Solder Tails Au Flash

Mating Compatability: 355, 357, 35T series products (with same polarization)

Electrical

Current Rating: 18 AWG: 10A (1 contact/socket); 7A (2 - 5 contacts/socket)

20 AWG: 9A (1 contact/socket); 6A (2 - 5 contacts/socket) Rating Conditions: 30° C maximum temperature rise

Voltage Rating: 250 V

Insulation Resistance: $10^3 \text{ M}\Omega \text{ min. at } 600 \text{ V}_{DC}$ **Withstanding Voltage:** $1,000 \text{ V}_{RMS}$ for 1 minute

Environmental

Process Rating: 260°C maximum for wave solder process


390°C for 3 seconds maximum for soldering iron

Temperature Rating: -20°C to +75°C ambient


UL Rating: 65° C

UL File No: E68080

3 mm, Straight, 1 and 2 Row, 5 and 10 Contacts



3 mm, Straight, 1 and 2 Row, 5 and 10 Contacts



Important Notice All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product which are not contained in 3M's current publications, or any contrary statements contained on your purchase order shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M. Warranty; Limited Remedy; Limited Liability. This product will be free from defects in material and manufacture for a period of one (1) year from the time of purchase. 3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. If this product is defective within the

warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. Except where prohibited by law, 3M will not be liable for any indirect, special, incidental or consequential loss or damage arising from this 3M product, regardless of

the legal theory asserted.

6801 River Place Blvd. Austin, TX 78726-9000

www.3m.com/interconnects

U.S.A. 1-800-225-5373

3M Electronics Solutions Division

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

3M:

35610-6234-B00PE 35610-6224-A00PE 35605-6114-A00PE 35605-6114-B00PE