





THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.


| LOC | DIST | REVISIONS | | | |
|-----|------|-------------|---------------------------|-----------|-------|
| P | LTR | DESCRIPTION | DATE | DWN | APVD |
| H | - | C | REVISED PER ECR-18-012809 | 15AUG2018 | FL HL |



SCALE 3:1



SECTION W-W
(KEY POSITION)



SECTION Y-Y

NOTES:

- 1 PLATING: 0,5µm MIN. TIN OVER NICKEL.
- 2 PLATING:

| PARTNUMBER | PERFORMANCE LEVEL |
|------------|---|
| 1857657-1 | PERFORMANCE LEVEL 1: CONNECTOR TESTED AND QUALIFIED AGAINST TELCORDIA GR-1217-CORE QUALITY LEVEL III: UNCONTROLLED ENVIRONMENT APPLICATIONS. SEE PRODUCT SPEC 108-19353 |
| 1857657-2 | PERFORMANCE LEVEL 2: CONFORMS TO ALL TESTING ACCORDING PRODUCT SPEC 108-19320, -250 MATING CYCLES, 4 DAYS MIXED GAS TEST PER IEC 60068-2-60 METHOD 1 |


- 3 CONSULT APPLICATION SPEC OR CONTACT TE CONNECTIVITY FOR PERMISSIBLE CONTACT ASSIGNMENTS.
- 4 CONNECTOR MARKED WITH PARTNUMBER AND DATE CODE. DATE CODE DEFINITION: YYWW.

| 3 | OVERMOLD | LCP 30% GF NATURAL |
|----------|-------------|--------------------|
| 2 | HOUSING | LCP 30% GF NATURAL |
| 1 | CONTACT | COPPER ALLOY |
| ITEM NO. | DESCRIPTION | MATERIAL |

| | | | | |
|--|--|--------------------------------------|--|--|
| THIS DRAWING IS A CONTROLLED DOCUMENT. | | DWN J.V.D. HELLDEN 30 OCT 2006 | TE Connectivity | |
| DIMENSIONS: mm | | CHK J.TUIN 30 OCT 2006 | | |
| TOLERANCES UNLESS OTHERWISE SPECIFIED: | | APVD J.BROEKSTEEG 30 OCT 2006 | NAME FEMALE CONNECTOR Z-PACK Slim UHD High Speed | |
| 0 PLC ± | | PRODUCT SPEC SEE NOTE 1 | SIZE CAGE CODE DRAWING NO RESTRICTED TO | |
| 1 PLC ± | | APPLICATION SPEC 114-19106 | A2 00779 C-1857657 | |
| 2 PLC ± | | WEIGHT | SCALE 5:1 SHEET 1 OF 2 REV C | |
| 3 PLC ± | | CUSTOMER DRAWING | | |
| 4 PLC ± | | | | |
| ANGLES ± | | | | |
| FINISH | | | | |


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

| LOC | DIST | REVISIONS | | | |
|-----|------|-------------|------|-----|------|
| P | LTR | DESCRIPTION | DATE | DWN | APVD |
| H | - | SEE SHEET 1 | - | - | - |
| | | | | | |
| | | | | | |



BOARD THICKNESS 1,2 MIN

RECOMMENDED PCB LAYOUT
(COMPONENT SIDE SHOWN)



| | | | | |
|---|--|--------------------------------------|--|--------------------|
| THIS DRAWING IS A CONTROLLED DOCUMENT. | | DWN J.V.D. HEIJDEN 30 OCT 2006 | TE Connectivity | |
| DIMENSIONS: mm | | CHK J.TWIN 30 OCT 2006 | | |
| TOLERANCES UNLESS OTHERWISE SPECIFIED: | | APVD J.BROEKSTEEG 30 OCT 2006 | NAME FEMALE CONNECTOR Z-PACK Slim UHD High Speed | |
| 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ± FINISH | | PRODUCT SPEC SEE NOTE 2 | RESTRICTED TO | |
| MATERIAL | | APPLICATION SPEC 114-19106 | SIZE A2 | CAGE CODE 00779 |
| | | WEIGHT - | DRAWING NO C-1857657 | |
| | | CUSTOMER DRAWING | SCALE 5:1 | SHEET 2 OF 2 |
| | | | REV C | |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1857657-1](#)