



Products | Custom Design | Media | Optic Types | Where To Buy | Contact Us

 sales@carclo-optics.com

 +44 1753 575 011

 [LinkedIn](#) 

26.5mm Medium Spot Frosted TIR (10393)










Part no.	10393
Drawing no.	60509
Family	26.5mm
Type	TIR
Diameter	26.5
Beam	Medium Spot
Finish	Frosted




LEDs & Performances

Select LED to view available holders

Manu.	Performance Data	Images	IES/STP
 Avago Moonstone RGB	Eff: 81 FWHM: 27 Cd/lm: 2.4	 	View
 Avago Moonstone White	Eff: 78.5 FWHM: 25 Cd/lm: 2.8		View
	Eff: 85.5 FWHM: 23		View


[Cree XLamp CSP XD16 Cool White](#)

Cd/lm: 3.8



[Cree XLamp MC-E RGBW](#)

Eff: 81.4
FWHM: 26
Cd/lm: 5.4



[View](#)



[Cree XLamp MC-E White](#)

Eff: 77.8
FWHM: 26
Cd/lm: 3.2




[View](#)



[Cree XLamp MH-B White](#)

Eff: 85
FWHM: 27
Cd/lm: 2.2



[View](#)




[Cree XLamp XHP-50 Gen 2 White](#)

Eff: 84
FWHM: 28
Cd/lm: 2.6




[View](#)



[Cree XLamp XHP-50 White](#)

Eff: 85.3
FWHM: 28
Cd/lm: 2.1




[View](#)



[Cree XLamp XHP35 HI White](#)

Eff: 84.8
FWHM: 22
Cd/lm: 3.3




[View](#)



[Cree XLamp XHP35 White](#)

Eff: 84
FWHM: 25
Cd/lm: 2.7




[View](#)



[Cree XLamp XP-G3 White](#)

Eff: 85
FWHM: 22
Cd/lm: 3.24




[View](#)



[Cree XLamp XP-L HI White](#)

Eff: 84.8
FWHM: 21
Cd/lm: 3.5




[View](#)



[Cree XLamp XP-L White](#)

Eff: 85.2
FWHM: 24
Cd/lm: 2.9



[View](#)




[Cree XLamp XP-L2 White](#)

Eff: 84.5
FWHM: 25
Cd/lm: 3.2



[View](#)




[Cree XLamp XQ-A Blue](#)

Eff: 85.5
FWHM: 22
Cd/lm: 4.3



[View](#)




[Cree XLamp XQ-A Green](#)

Eff: 85.5
FWHM: 22
Cd/lm: 4.3



[View](#)




[Cree XLamp XQ-A Red](#)

Eff: 85.5
FWHM: 22
Cd/lm: 4.3




[View](#)





[Cree XLamp XQ-A White](#)

Eff: 85
FWHM: 15
Cd/lm: 5.31




[View](#)



[Cree XLamp XQ-E HI Blue](#)

Eff: 84.5
FWHM: 22
Cd/lm: 3.9




[View](#)



[Cree XLamp XQ-E HI Green](#)

Eff: 84.5
FWHM: 22
Cd/lm: 3.9



[View](#)




[Cree XLamp XQ-E HI Red](#)

Eff: 85
FWHM: 22
Cd/lm: 4




[View](#)



[Cree XLamp XQ-E HI White](#)

Eff: 85
FWHM: 17
Cd/lm: 4.18




[View](#)




[Cree XLamp XTE HE White](#)

Eff: 85.5
FWHM: 23
Cd/lm: 3.7



[View](#)



[LEDEngin 10W White](#)

Eff: 79
FWHM: 27
Cd/lm: 3




[View](#)

Eff: 91





FWHM: 23
Cd/lm: 4.3




[View](#)

[Lite-On R38386AS - S R38 IR](#)



Eff: 83
FWHM: 21
Cd/lm: 3.56




[View](#)

[LUMILEDS LUXEON 3030 White](#)



Eff: 84.6
FWHM: 21
Cd/lm: 3.63




[View](#)

[LUMILEDS LUXEON 3535 HV White](#)



Eff: 84.7
FWHM: 21
Cd/lm: 3.61




[View](#)

[LUMILEDS LUXEON 3535 L White](#)



[LUMILEDS LUXEON 3535L Blue](#)

Eff: 86
FWHM: 23
Cd/lm: 3.8





[View](#)



[LUMILEDS LUXEON 3535L Green](#)

Eff: 86
FWHM: 23
Cd/lm: 3.9




[View](#)



[LUMILEDS LUXEON 3535L Red](#)

Eff: 86
FWHM: 23
Cd/lm: 4.1




[View](#)



[LUMILEDS LUXEON 5050 White](#)

Eff: 86
FWHM: 27
Cd/lm: 3




[View](#)



[LUMILEDS LUXEON C Blue](#)

Eff: 79.5
FWHM: 22
Cd/lm: 3.6




[View](#)



[LUMILEDS LUXEON C Lime](#)

Eff: 81.5
FWHM: 22
Cd/lm: 3.8




[View](#)



[LUMILEDS LUXEON C Red](#)

Eff: 3.6
FWHM: 22
Cd/lm: 13.8



[View](#)




[LUMILEDS LUXEON CSP 05 White](#)

Eff: 82
FWHM: 19
Cd/lm: 3.42



[View](#)




[LUMILEDS LUXEON CSP 10 White](#)

Eff: 82
FWHM: 21
Cd/lm: 2.86



[View](#)




[LUMILEDS LUXEON CZ](#)

Eff: 87
FWHM: 22
Cd/lm: 4.4



[View](#)




[LUMILEDS LUXEON IR Compact 850nm](#)

Eff: 90.5
FWHM: 22
Cd/lm: 4.4



[View](#)




Eff: 88.5



FWHM: 24
Cd/lm: 3.9

[LUMILEDS LUXEON IR Domed 60 Degree](#)




[View](#)



Eff: 90
FWHM: 23
Cd/lm: 4.3

[LUMILEDS LUXEON IR Domed 90 Degree](#)




[View](#)



Eff: 84
FWHM: 29
Cd/lm: 2.4

[LUMILEDS LUXEON MX White](#)




[View](#)



Eff: 85.3
FWHM: 25
Cd/lm: 2.7

[LUMILEDS LUXEON MZ White](#)




[View](#)



[LUMILEDS LUXEON Q White](#)

Eff: 82.9
FWHM: 22
Cd/lm: 3.1




[View](#)



[LUMILEDS LUXEON TX White](#)

Eff: 84.8
FWHM: 21
Cd/lm: 3.4




[View](#)



[LUMILEDS LUXEON V White](#)

Eff: 83
FWHM: 25
Cd/lm: 3.1




[View](#)





[LUMILEDS LUXEON V2 White](#)

Eff: 85.5
FWHM: 24
Cd/lm: 3.7




[View](#)



[LUMILEDS LUXEON Z ES White](#)

Eff: 84.6
FWHM: 19
Cd/lm: 3.95




[View](#)



[LUMILEDS LUXEON Z White](#)

Eff: 84.6
FWHM: 17
Cd/lm: 4.35



[View](#)



[Luminus Devices SST-50 White](#)

Eff: 76.3
FWHM: 25
Cd/lm: 3.6




[View](#)



[Luminus Devices SST-90 White](#)

Eff: 79.6
FWHM: 30
Cd/lm: 2.4



[View](#)



[Nichia 229A White](#)

Eff: 83.5
FWHM: 25
Cd/lm: 3.2



[View](#)



[Nichia 757G White](#)

Eff: 86
FWHM: 23
Cd/lm: 3.9



[View](#)




Eff: 85
FWHM: 22
Cd/lm: 4.1




[View](#)

[Nichia NCSW E17A White](#)



[Nichia NF2W 385AR-V2 White](#)

Eff: 85.5
FWHM: 24
Cd/lm: 3.7



[View](#)



[Nichia NFMW 481AR White](#)

Eff: 77.5
FWHM: 27
Cd/lm: 2.6



[View](#)



[Nichia NFMW 484AR White](#)

Eff: 86
FWHM: 27
Cd/lm: 2.9



[View](#)




Eff: 86
FWHM: 27
Cd/lm: 3



[View](#)

[Nichia NFMW 486AR White](#)




[Nichia NFMW 488AR White](#)

Eff: 86
FWHM: 27
Cd/lm: 2.9



[View](#)



[Nichia NV4W 144AR White](#)

Eff: 83
FWHM: 28
Cd/lm: 2.5



[View](#)




[Nichia NVSL 219B White](#)

Eff: 83.5
FWHM: 23
Cd/lm: 3.8




[View](#)





[Nichia NVSW 219C White](#)

Eff: 84.5
FWHM: 24
Cd/lm: 3.7




[View](#)



[Nichia NVSW 319A White](#)

Eff: 84
FWHM: 24
Cd/lm: 3.5




[View](#)



[Nichia NVSW E21A White](#)

Eff: 84
FWHM: 21
Cd/lm: 3.5



[View](#)




[Nichia Top Emitting 083 White](#)

Eff: 79.1
FWHM: 26
Cd/lm: 3



[View](#)




OSRAM
Opto Semiconductors

[Osram OS DURIS E 2835 White](#)

Eff: 86
FWHM: 23
Cd/lm: 3.9



[View](#)




OSRAM
Opto Semiconductors

[Osram OS DURIS E3 White](#)

Eff: 88.3
FWHM: 19
Cd/lm: 4.2



[View](#)



OSRAM
Opto Semiconductors

[Osram OS DURIS P10 White](#)

Eff: 85.2
FWHM: 28
Cd/lm: 2.1



[View](#)




Eff: 84.6

OSRAM
Opto Semiconductors

[Osram OS DURIS P8 White](#)

FWHM: 21
Cd/lm: 3.5




[View](#)

OSRAM
Opto Semiconductors

[Osram OS DURIS S10 White](#)

Eff: 85
FWHM: 31
Cd/lm: 2.2




[View](#)

OSRAM
Opto Semiconductors

[Osram OS DURIS S2 White](#)

Eff: 88.8
FWHM: 21
Cd/lm: 3.7



[View](#)

OSRAM
Opto Semiconductors

[Osram OS DURIS S5 Deep Blue](#)

Eff: 84.5
FWHM: 24
Cd/lm: 3.9





[View](#)

OSRAM
Opto Semiconductors

[Osram OS DURIS S5 Green](#)

Eff: 87
FWHM: 23
Cd/lm: 4




[View](#)

OSRAM
Opto Semiconductors

[Osram OS DURIS S5 Red](#)

Eff: 88
FWHM: 23
Cd/lm: 4.2




[View](#)

OSRAM
Opto Semiconductors

[Osram OS DURIS S5 White](#)

Eff: 85
FWHM: 21
Cd/lm: 3.51



[View](#)


OSRAM
Opto Semiconductors

[Osram OS DURIS S8 Gen2 White](#)

Eff: 89
FWHM: 27
Cd/lm: 2.58



[View](#)




OSRAM
Opto Semiconductors

[Osram OS DURIS S8 White](#)

Eff: 89.55
FWHM: 27
Cd/lm: 2.43




[View](#)



OSRAM
Opto Semiconductors

[Osram OS Golden DRAGON Plus W5AM White](#)

Eff: 81.8
FWHM: 22
Cd/lm: 4.3




OSRAM
Opto Semiconductors

[Osram OS GOLDEN DRAGON W5SM White](#)

Eff: 79.1
FWHM: 23
Cd/lm: 4.1



[View](#)




Eff: 83.5

OSRAM
Opto Semiconductors

[Osram OS Osconiq P3737 White](#)

FWHM: 25
Cd/lm: 3.4




[View](#)

OSRAM
Opto Semiconductors

[Osram OS OSLON Black SFH 4725S IR](#)

Eff: 92
FWHM: 23
Cd/lm: 4.3




[View](#)

OSRAM
Opto Semiconductors

[Osram OS OSLON Pure CSP GW VJLPE 1 White](#)

Eff: 86.5
FWHM: 22
Cd/lm: 4.4




[View](#)

OSRAM
Opto Semiconductors

[Osram OS OSLON Square Flat White](#)

Eff: 85.5
FWHM: 23
Cd/lm: 4




[View](#)



[Osram OS OSOLON Square Gen 3 White](#)

Eff: 84.7
FWHM: 21
Cd/lm: 3.5




[View](#)



[Osram OS OSOLON Square White](#)

Eff: 84
FWHM: 21
Cd/lm: 3.48




[View](#)



[Osram OS OSTAR Lighting White](#)

Eff: 78.3
FWHM: 22
Cd/lm: 3.8




[View](#)



[Osram OS PLATINUM DRAGON W5SN White](#)

Eff: 78.9
FWHM: 22
Cd/lm: 4.1





[View](#)



[Plessey PLW 7070GA White](#)

Eff: 84.5
FWHM: 30
Cd/lm: 2.4




[View](#)



[Samsung 3535 LH351B White](#)

Eff: 85
FWHM: 22
Cd/lm: 3.3




[View](#)



[Samsung 3535 LH351D White](#)

Eff: 86
FWHM: 25
Cd/lm: 3.5



[View](#)




[Samsung 3535 LH351Z White](#)

Eff: 84.7
FWHM: 21
Cd/lm: 3.66



[View](#)




[Samsung CSP LH181B White](#)

Eff: 87
FWHM: 23
Cd/lm: 3.9



[View](#)




[Samsung CSP LH231B White](#)

Eff: 86.5
FWHM: 24
Cd/lm: 3.7



[View](#)




[Samsung CSP LM101B White](#)

Eff: 86.5
FWHM: 22
Cd/lm: 4.2




[View](#)





[Seoul CSP SZ8Y22 White](#)

Eff: 86
FWHM: 24
Cd/lm: 3.7




[View](#)



[Seoul CSP SZ8Y22P White](#)

Eff: 84
FWHM: 24
Cd/lm: 3.4




[View](#)



[Seoul CSP SZ8Y50 White](#)

Eff: 86.5
FWHM: 30
Cd/lm: 2.5




[View](#)



[Seoul MidPower MJT3030 White](#)

Eff: 84.7
FWHM: 21
Cd/lm: 3.55




[View](#)



[Seoul MidPower MJT4040 White](#)

Eff: 85
FWHM: 23
Cd/lm: 3



[View](#)



[Seoul MJT 5050 White](#)

Eff: 84.8
FWHM: 25
Cd/lm: 2.8




[View](#)



[Seoul P4 White](#)

Eff: 83.7
FWHM: 23
Cd/lm: 3.07



[View](#)




Eff: 83.5
FWHM: 23



[View](#)


[Seoul SZ8Y11 White](#)

Cd/lm: 4



[Seoul SZ8Y15 White](#)

Eff: 85
FWHM: 22
Cd/lm: 4.2




[View](#)



[Seoul SZ8Y19 White](#)

Eff: 85
FWHM: 22
Cd/lm: 3.1



[View](#)



[Seoul Z - Power Z5 M1 White](#)

Eff: 85
FWHM: 22
Cd/lm: 3.4




[View](#)



[Seoul Z - Power Z5 M1 White](#)

Eff: 85
FWHM: 22
Cd/lm: 3.4



[View](#)



[SSC Acrich A2000 White](#)

Eff: 76.6
FWHM: 26
Cd/lm: 2.3




[View](#)



[Stanley 6J White](#)

Eff: 85
FWHM: 27
Cd/lm: 2.35



[View](#)



[Toshiba TL 1L2 White](#)

Eff: 85
FWHM: 22
Cd/lm: 3.4





[View](#)

TOSHIBA

[Toshiba TL 1L4 White](#)

Eff: 84
FWHM: 22
Cd/lm: 3.4



[View](#)