

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1053001100](#)
Status: **Active**
Overview: [Nano-Fit Power Connectors](#)
Description: Nano-Fit Crimp Terminal, Female, 2.54µm Matte Tin (Sn) Plating, 24-26 AWG

Documents:

Drawing (PDF)	Application Specification AS-105300-100-001 (PDF)
Product Specification 1053001000-PS-CH-000 (PDF)	Packaging Specification PK-105300-100-000 (PDF)
Product Specification 1053001000-PS-ES-000 (PDF)	Test Summary 1053001000-TS-000 (PDF)
Product Specification 1053001000-PS-JP-000 (PDF)	Datasheet (PDF)
Product Specification 1053001000-PS-SK-000 (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-105300-100-001 (PDF)	

General

Product Family	Crimp Terminals
Series	105300
Application	Power, Wire-to-Board
Crimp Quality Equipment	Yes
Overview	Nano-Fit Power Connectors
Product Name	Nano-Fit
UPC	889056003247

Physical

Durability (mating cycles max)	25
Gender	Female
Material - Metal	High Conductivity Copper
Material - Plating Mating	Matte Tin
Material - Plating Termination	Matte Tin
Net Weight	0.100/g
Packaging Type	Reel
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.30mm
Wire Size AWG	24, 26
Wire Size mm ²	0.13-0.20

Electrical

Current - Maximum per Contact	6.0A
Voltage - Maximum	250V AC (RMS)/DC

Material Info

Reference - Drawing Numbers

Application Specification	AS-105300-100-001
Packaging Specification	PK-105300-100-000
Product Specification	1053001000-PS-CH-000, 1053001000-PS-ES-000, 1053001000-PS-JP-000, 1053001000-PS-SK-000, PS-105300-100-001
Sales Drawing	2004570710-000
Test Summary	1053001000-TS-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)4578-DC (25
June 2020)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[105300 Series](#)

Use With

Nano-Fit Receptacle Housing [105307](#) ,
[105308](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

Extraction Tool for [638244600](#)

Nano-Fit Power Connectors and Crimp Terminals, 20-26 AWG

Hand Crimp Tool for [638276000](#)

Nano-Fit Receptacle Terminals, 24 AWG and 26 AWG,

UL1061 and UL1007
Insulations
FineAdjust Applicator [639032500](#)
for Insulation OD
0.90-1.15mm -
UL1061
FineAdjust Applicator [639034800](#)
for Insulation OD
1.20-1.45mm -
UL1007

Japan

Description	Product #
S-1 Applicator for Nano-Fit Terminals, 24-26 AWG, UL1061 Wires	2047483710
S-1 Applicator for Nano-Fit Terminals, 24-26 AWG, UL1007 Wires	2047483720

This document was generated on 09/08/2020

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION