

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1053071208](#)
Status: **Active**
Overview: [Nano-Fit Power Connectors](#)
Description: Nano-Fit Receptacle Housing, TPA Capable, 2.50mm Pitch, Single Row, 8 Circuits, Black, Glow-Wire Capable

Documents:

| | |
|--|---|
| 3D Model | Product Specification PS-105300-100-001 (PDF) |
| 3D Model (PDF) | Application Specification AS-105300-100-001 (PDF) |
| Drawing (PDF) | Packaging Specification PK-105307-100-000 (PDF) |
| Product Specification 1053001000-PS-CH-000 (PDF) | Test Summary 1053000000-TS-000 (PDF) |
| Product Specification 1053001000-PS-ES-000 (PDF) | Test Summary 1053001000-TS-000 (PDF) |
| Product Specification 1053001000-PS-JP-000 (PDF) | Datasheet (PDF) |
| Product Specification 1053001000-PS-SK-000 (PDF) | RoHS Certificate of Compliance (PDF) |

Agency Certification

| | |
|-----|---------|
| CSA | LR19980 |
| UL | E29179 |

Application tooling part link

| | |
|-------------------------------|------------|
| Application Tooling Part Link | 63824-4600 |
|-------------------------------|------------|

General

| | |
|----------------|---|
| Product Family | Crimp Housings |
| Series | 105307 |
| Application | Power, Wire-to-Board |
| Comments | Operating temperature is -40#C to +105#C for tin and -40#C to +115#C for gold |
| Overview | Nano-Fit Power Connectors |
| Product Name | Nano-Fit |
| UPC | 889056026499 |

Physical

| | |
|-------------------------------|--------------------------------|
| Circuits (maximum) | 8 |
| Color - Resin | Black |
| Flammability | 94V-0 |
| Gender | Receptacle |
| Glow-Wire Capable | Yes |
| Keying to Mating Part | Yes |
| Lock to Mating Part | Yes |
| Material - Resin | Nylon |
| Net Weight | 0.850/g |
| Number of Rows | 1 |
| Packaging Type | Bag |
| Panel Mount | No |
| Pitch - Mating Interface | 2.50mm |
| Pitch - Termination Interface | 2.50mm |
| Polarized to Mating Part | Yes |
| Temperature Range - Operating | -40° to +105°C, -40° to +115°C |


Electrical

| | |
|-------------------------------|------|
| Current - Maximum per Contact | 6.5A |
|-------------------------------|------|

Material Info

Reference - Drawing Numbers

| | |
|---------------------------|-------------------|
| Application Specification | AS-105300-100-001 |
| Packaging Specification | PK-105307-100-000 |



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[105307](#) Series

Mates With

Nano-Fit Vertical Headers [1053091108](#) ,
[1053091208](#) , [1053091308](#) , [1053111108](#) ,
[1053111208](#) , [1053111308](#) , [1054311108](#) ,
[1054311208](#) , [1054311308](#) , [1054311408](#) .
Nano-Fit Right-Angle Headers [1053131108](#)
 , [1053131208](#) , [1053131308](#) , [1054301108](#)
 , [1054301208](#) , [1054301308](#) , [1054301408](#)
 . Nano-Fit Plug Housings [2002771108](#) ,
[2002771208](#)

Use With

Nano-Fit Crimp Terminal [105300](#) . Nano-Fit Pre-Crimped Leads (Gold) [797582129](#) , [797582130](#). Nano-Fit Pre-Crimped Leads (Tin) [797582139](#) , [797582140](#). Nano-Fit TPA Retainer [105325](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then

Product Specification

Sales Drawing
Test Summary

1053001000-PS-CH-000, 1053001000-PS-ES-000,
1053001000-PS-JP-000, 1053001000-PS-SK-000,
PS-105300-100-001
SD-105307-100-000
1053000000-TS-000, 1053001000-TS-000

*contained in the Application Tooling
Specification document.*

Global

Description

Product #

Extraction Tool for 638244600

Nano-Fit Power
Connectors and
Crimp Terminals,
20-26 AWG

This document was generated on 11/10/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION