

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1053122212](#)
Status: **Active**
Overview: [Nano-Fit Power Connectors](#)
Description: Nano-Fit Vertical Header, Through Hole, 2.50mm Pitch, Dual Row, 12 Circuits, with Solder Clips, 0.38µm Gold (Au) Plating, Natural, Glow-Wire Capable, Tray

Documents:

3D Model	Product Specification PS-105300-100-001 (PDF)
Drawing (PDF)	Application Specification AS-105300-100-001 (PDF)
3D Model (PDF)	Packaging Specification PK-105309-100-000 (PDF)
Product Specification 1053001000-PS-CH-000 (PDF)	Test Summary 1053000000-TS-000 (PDF)
Product Specification 1053001000-PS-ES-000 (PDF)	Datasheet (PDF)
Product Specification 1053001000-PS-JP-000 (PDF)	Symbol Footprint Data SYM-105312-XX12 (PDF)
Product Specification 1053001000-PS-SK-000 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification


CSA	LR19980
UL	E29179

General

Product Family	PCB Headers
Series	105312
Application	Power, Wire-to-Board
Overview	Nano-Fit Power Connectors
Packaging Alternative	1053124712
Product Name	Nano-Fit
UPC	887191931296

Physical

Breakaway	No
Circuits (Loaded)	12
Circuits (maximum)	12
Color - Resin	Natural
Durability (mating cycles max)	50
Flammability	94V-0
Glow-Wire Capable	Yes
Guide to Mating Part	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Liquid Crystal Polymer
Net Weight	1.190/g
Number of Rows	2
Orientation	Vertical
PC Tail Length	3.20mm
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm, 2.40mm
Packaging Type	Tray
Pitch - Mating Interface	2.50mm
Pitch - Termination Interface	2.50mm
Plating min - Mating	0.381µm
Plating min - Termination	1.524µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Contained Per -
D(2020)4578-DC (25
June 2020)
decamethylcyclotetrasiloxane
benzene-1,2,4-
tricarboxylic acid 1,2-
anhydride
decamethylcyclotetrasiloxane
dodecamethylcyclohexasiloxane
octamethylcyclotetrasiloxane
disodium 3,3'-[[1,1'-
biphenyl]-4,4'-
diylbis(azo)
dodecamethylcyclohexasiloxane
heptacosafuorotetradecanoic
acid
tricosafuorododecanoic
acid
di-n-pentyl phthalate
(DPP)
6-methoxy-m-toluidine
diisopentylphthalate
methoxyacetic acid
dibutyltin dichloride
4,4'-methylenedi-o-
toluidine
1-vinylimidazole
1,3-propanesultone
chromium trioxide
disodium 4-
amino-3-[[4'-[(2,4-
diaminophenyl)azo]
henicosafuoroundecanoic
acid
Silicic acid (H₂Si₂O₅),
barium salt (1:1),
lead-
[phthalato(2-)]dioxotrilead

China RoHS

Shrouded Yes
Stackable No
Surface Mount Compatible (SMC) No
Temperature Range - Operating -40° to +115°C
Termination Interface: Style Through Hole

Electrical

Current - Maximum per Contact 8.0A
Voltage - Maximum 250V AC (RMS)/DC

Material Info

Reference - Drawing Numbers

Application Specification AS-105300-100-001
Packaging Specification PK-105309-100-000
Product Specification 1053001000-PS-CH-000, 1053001000-PS-ES-000,
1053001000-PS-JP-000, 1053001000-PS-SK-000,
PS-105300-100-001
SD-105312-100-000
Sales Drawing SYM-105312-XX12
Symbol/Footprint Data
Test Summary 1053000000-TS-000

Fatty acids, C16-18,
lead salts
4-aminoazobenzene
diethyl sulphate
dimethyl sulphate
N-methylacetamide
dicyclohexyl phthalate
dihexyl phthalate
(DnHP)
dinoseb (ISO)
butyl 4-
hydroxybenzoate
o-toluidine
4-methyl-m-
phenylenediamine
ethylene thiourea
4-o-tolylazo-o-
toluidine
nitrobenzene
1-bromopropane
furan
ammoniumpentadecafluorooctanoate
Zirconia
Aluminosilicate
Refractory Ceramic
Fibr
Trixylyl phosphate
4-(1,1,3,3-
tetramethylbutyl)phenol,
ethoxylated
2,3,3,3-tetrafluoro-2-
(heptafluoropropoxy)propio
Tris(4-nonylphenyl,
branched and linear)
phosphi
Pyrene
Cadmium nitrate
Chrysene
Dodecachloropentacyclo[12.2.1.16,9.02,13.05,10]o
Reaction
products of 1,3,4-
thiadiazolidine-2,5-d
Perfluorononan-1-
oic acid
(2,2,3,3,4,4,5,5,6,6,7
4-(1,1,3,3-
tetramethylbutyl)phenol,
ethoxylated
hexahydro-2-
benzofuran-1,3-dione
Sodium perborate;
perboric acid, sodium
salt
Cadmium sulphate
1,2-
benzenedicarboxylic
acid, di-C6-10-alkyl
est
5-sec-butyl-2-(2,4-
dimethylcyclohex-3-
en-1-yl)-5
Perfluorohexane-1-
sulphonic acid and its
salts
ammoniumpentadecafluorooctanoate

sodium
peroxometaborate
disodium octaborate
2-ethylhexyl 10-
ethyl-4,4-dioctyl-7-
oxo-8-oxa-3,
dibutylbis(pentane-2,4-
dionato-O,O')tin
2-(2H-benzotriazol-2-
yl)-4,6-
ditertpentylphenol
2-(2H-benzotriazol-2-
yl)-4-(tert-butyl)-6-
(sec-b
Terphenyl,
hydrogenated
1,2-
Benzenedicarboxylic
acid, dihexyl ester,
bra
pentacosafuorotridecanoic
acid
1,2-
benzenedicarboxylic
acid, dipentylester,
bra
3-ethyl-2-methyl-2-
(3-methylbutyl)-1,3-
oxazolidi
n-pentyl-
isopentylphthalate
1,3-BENZENEDIOL,
TRINITRO-, LEAD
SALT
Hydrazine
Disodium tetraborate
Boric acid
Aluminosilicate
Refractory Ceramic
Fibres
Sulfurous acid, lead
salt, dibasic
sodium chromate
tetraboron disodium
heptaoxide, hydrate
cobalt carbonate
cobalt di(acetate)
cobalt sulphate
2-ethoxyethyl acetate
1,2-
benzenedicarboxylic
acid; di-C7-11-
branched
N-methyl-2-
pyrrolidone
1,2-
benzenedicarboxylic
acid; di-C6-8-
branched a
calcium arsenate
bis(2-methoxyethyl)
ether
potassium
hydroxyoctaoxodizincatedichromate(1-)
lead dipicrate

N,N-
dimethylacetamide
arsenic acid
2-methoxyaniline
trilead diarsenate
1,2-dichloroethane
triethyl arsenate
4,4'-
diaminodiphenylmethane
dibutyl phthalate
(DBP)
bis(2-ethylhexyl)
phthalate (DEHP)
lead hydrogen
arsenate
Butylbenzylphthalate
(BBP)
Anthracene oil,
anthracene paste;
Anthracene Oil
Anthracene oil,
anthracene paste,
anthracene fra
Anthracene oil,
anthracene paste,
distn. lights;
Anthracene oil,
anthracene-low;
Anthracene Oil F
lead chromate
Lead chromate
molybdate sulfate red
Lead sulfochromate
yellow
tris(2-chloroethyl)
phosphate
ammonium
dichromate
potassium chromate
potassium dichromate
sodium chromate
pentazinc chromate
octahydroxide
1,3,5-
tris(oxiranylmethyl)-1,3,5-
triazine-2,4,6(
[4-[[4-anilino-1-
naphthyl]]4-
(dimethylamino)phen
 α,α #Bis[4-
(dimethylamino)phenyl]-4
(phenylamino)
lead
cadmium
cadmium fluoride
pyrochlore, antimony
lead yellow
lead dinitrate
cadmium chloride
Silicic acid, lead salt
lead oxide sulfate
pentalead tetraoxide
sulphate
trilead dioxide
phosphonate

tetralead trioxide
sulphate
dioxobis(stearato)trilead
Lead titanium
zirconium oxide
cadmium hydroxide
Acetic acid, lead salt,
basic
Sulfurous acid, lead
salt, dibasic
pentazinc chromate
octahydroxide
Formaldehyde,
polymer with
benzenamine
bis(2-methoxyethyl)
phthalate
lead diazide
phenolphthalein
dichromium
tris(chromate)
4,4'-
bis(dimethylamino)benzophenone
1,2-dimethoxyethane
cadmium carbonate
[4-[4,4'-
bis(dimethylamino)
benzhydrylidene]cycl
4,4'-
bis(dimethylamino)-4''-
(methylamino)trityl
bis(pentabromophenyl)
ether
diboron trioxide
cadmium oxide (non-
pyrophoric)
cadmium sulphide
orange lead
trilead bis(carbonate)
dihydroxide
Lead oxide
1,3,5-
tris(oxiranylmethyl)-1,3,5-
triazine-2,4,6(

**Halogen-Free
Status**

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
[105312 Series](#)

Mates With
Nano-Fit Receptacle Housing [1053082212](#)