

WEW 35/1**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Product image**Klippon® Connect with clamping yoke Technology**

The high reliability and variety of designs of the terminal blocks with clamping yoke connections make planning easier and optimises operational safety. Klippon® Connect provides a proven response to a range of different requirements.

General ordering data

Version	W-Series, End bracket
Order No.	1059000000
Type	WEW 35/1
GTIN (EAN)	4008190172282
Qty.	50 pc(s).

WEW 35/1**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Depth	62.5 mm	Depth (inches)	2.461 inch
Height	56 mm	Height (inches)	2.205 inch
Net weight	36.3 g	Width	12 mm
Width (inches)	0.472 inch		

Material data

Material	Wemid	Colour	dark beige
UL 94 flammability rating	V-2		

System specifications

Version	For the terminals	Rail	TS 35
---------	-------------------	------	-------

Additional technical data

Installation advice	Direct mounting	Interlock	for screw fixing
Type of mounting	when screwed in		

Conductors for clamping (rated connection)

Tightening torque, max.	2.4 Nm	Tightening torque, min.	1.2 Nm
-------------------------	--------	-------------------------	--------

Dimensions

TS 35 offset	28 mm
--------------	-------

General

Installation advice	Direct mounting	Rail	TS 35
---------------------	-----------------	------	-------

Classifications

ETIM 6.0	EC001041	ETIM 7.0	EC001041
eClass 9.0	27-14-11-35	eClass 9.1	27-14-11-35
eClass 10.0	27-14-11-35	eClass 11.0	27141135

Approvals

ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	CAT 1 TERM 16/17 EN
Engineering Data	STEP
Engineering Data	EPLAN, WSCAD, Zuken E3.S
User Documentation	StorageConditionsTerminalBlocks