



THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION  
 © COPYRIGHT - By - ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
E		ECO-20-008201	16JUN2020	TS	DW

1. THE MT FERRULE IS TERMINATED AND POLISHED, BUT NOT TESTED.
2. PART INTENDED AS SAMPLE OR DUMMY ASSEMBLY.



0.048+0/-0.013 [1.89+0/-0.05]	SHORT PIGTAIL WITH SPRING & PINS	1938401-4
	SHORT PIGTAIL WITHOUT SPRING & PINS	1938401-3
0.127±0.025 [5.0±1.0]	PIGTAIL WITH SPRING & PINS	1938401-2
	PIGTAIL WITHOUT SPRING & PINS	1938401-1
L	CONFIGURATION	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. GLATFELTER 16SEP2009	<b>TE</b> TE Connectivity	
DIMENSIONS: METERS [INCHES]		CHK J. BARRY 16SEP2009		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD J. BARRY 16SEP2009	NAME PIGTAIL, FIBER OPTIC, MT FERRULE TO 12 FIBER RIBBON, DUMMY	
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		PRODUCT SPEC -	SIZE A2	
MATERIAL -		FINISH -	CAGE CODE 00779	DRAWING NO. 1938401
		WEIGHT 0.000000	RESTRICTED TO -	
		CUSTOMER DRAWING	SCALE NTS	SHEET 1 of 1
			REV E	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1938401-1](#)