



What can we help you find?

Home > Products > RF & Coax > Product Feature Selector > Product Details

1-1337582-0 Product Details

Share Print Email



1-1337582-0

MCX (OSX) RF Connectors

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Connector - RF
- Jack
- Body Style = Straight
- Applies To Printed Circuit Board
- Without Panel Mount Retention

[View all Features](#)

Quick Links

- ▶ Pricing & Availability
- ▶ Search for Tooling
- ▶ Product Feature Selector
- ▶ Contact Us About This Product

TE Internal Number: 1-1337582-0

Active

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [MCX SURFACE MOUNT STRAIGHT PCB SOCKET 50 Ohm \(PDF, English\)](#)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- [MCX SERIES COAXIAL CONNECTORS - TYCO GREENPAR \(PDF, English\)](#)

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Connector - RF
- Gender = Jack
- PCB Mount Retention = Without
- Dielectric Material = PTFE
- Grade = Professional
- Sealed = No
- Isolated = No

Mechanical Attachment:

- Panel Mount Retention = Without
- Flange Dimension [Sq.] (mm [in]) = 6.00 [0.236]

Electrical Characteristics:

- Connector Impedance (Ω) = 50

Termination Features:

- Contact Termination Type = Surface Mount

Dimensions:

- PCB Height (mm [in]) = 5.90 [0.232]

Body Features:

- Body Style = Straight
- Body Plating = Gold
- Body Material = Brass
- Body Shape = Square
- Polarized = No

Contact Features:

- Center Contact Plating = Gold
- Center Contact Material = Brass

Industry Standards:

- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Wave solder capable to 260°C, Wave solder capable to 240°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant

Environmental:

- Operating Temperature (Max.) (°C) = 165

Conditions for Usage:

- Applies To = Printed Circuit Board

Packaging Features:

- Packaging Quantity = 50
- Packaging Method = Individual

Other:

- Brand = Greenpar

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)

Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

