



[CONNECTORS](#)

[RF CONNECTORS](#)



✓ Active

TE CONNECTIVITY (TE)

SMA PNL SKT RCPT, 2/FLNG GSS

Subminiature Coax | SMA

1-1478963-0

TE Internal Number: 1-1478963-0

[EU RoHS Compliant with Exemptions](#)

[EU ELV Compliant with Exemptions](#)

Connector Interface SMA

Mated Outer Diameter (Approximate) 6.35 mm [.25 in]

Sealable No

Connector Mounting Type Panel

Termination Method to Wire & Cable Solder Terminal

[↓ PRODUCT DRAWING](#)
English

DOCUMENTATION

Product Drawings

SMA STRAIGHT PANEL SOCKET RECEPTACLE 2 HOLE FLANGE SOLDER SPILL

PDF

English

FEATURES

Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Connector Interface SMA

Sealable No

Body Features

Cable Connector Orientation Straight

Body Material Stainless Steel

Body Plating Material Gold

Contact Features

Center Contact Plating Material Gold

Center Contact Material Beryllium Copper

Connector Product Type Connector Assembly

RF Connector Contact Configuration Captivated Contacts

Termination Features

Termination Method to Wire & Cable Solder Terminal

Mechanical Attachment

Panel Mount Retention Type Flange

Connector Mounting Type Panel

Panel Attachment Style Front/Rear Mount

Dimensions

Mated Outer Diameter (Approximate) 6.35 mm [.25 in]

Panel Cutout 3 x 2.6 Front Mount, 1 x 6.4 + 2 x 2.6 Rear Mount

Length 14.4 mm [.567 in]

Packaging Features

Packaging Method Bag

Packaging Quantity 100

Other

Dielectric Material PTFE

Flange and Thread Material Stainless Steel

Number of Panel Mounting Holes 2

Grade Professional

PRODUCT COMPLIANCE



Statement of Compliance

Statement of Compliance

PDF
