

Product Type Features:	Contact Features:
<ul> <li>Product Type = Connector</li> </ul>	<ul> <li>Contact Plating, Mating Area, Material = Gold Flash</li> </ul>
<ul> <li>Jack Type = RJ22</li> </ul>	<ul> <li>Contact Base Material = Phosphor Bronze</li> </ul>
<ul> <li>PCB Mounting Orientation = Side Entry (Right Angle)</li> </ul>	
<ul> <li>PCB Mount Style = Through Hole</li> </ul>	Housing Features:
<ul> <li>Termination Method to PC Board = Solder</li> </ul>	<ul> <li>Housing Material = PBT - GF</li> </ul>
<ul> <li>Performance Category = Cat 3</li> </ul>	<ul> <li>UL Flammability Rating = UL 94V-0</li> </ul>
<ul> <li>LED = Without</li> </ul>	
<ul> <li>Grounding Options = Without</li> </ul>	Configuration Features:
<ul> <li>Panel Stops = With</li> </ul>	<ul> <li>Preloaded = Yes</li> </ul>
<ul> <li>Keyed = No</li> </ul>	<ul> <li>Port Configuration = Single</li> </ul>
Profile = Standard	<ul> <li>Jack Configuration = 1 x 1</li> </ul>
	<ul> <li>Number of Positions = 4</li> </ul>
<ul> <li>Color = Black</li> </ul>	<ul> <li>Number of Contacts Loaded = 4</li> </ul>
<ul> <li>Latch Style = Standard</li> </ul>	
	Industry Standards:
Mechanical Attachment:	<ul> <li>RoHS/ELV Compliance = RoHS compliant, ELV compliant</li> </ul>
<ul> <li>Panel Mount Retention = With</li> <li>Flanged = No</li> </ul>	<ul> <li>Lead Free Solder Processes = Wave solder capable to 260°C, Wave solder capable to 240°C, Wave solder capable to 265°C</li> </ul>
	<ul> <li>RoHS/ELV Compliance History = Always was RoHS compliant</li> </ul>
Electrical Characteristics:	
<ul> <li>Shielded = No</li> </ul>	Packaging Features:
	<ul> <li>Packaging Method = Tray</li> </ul>
Termination Features:	<ul> <li>Packaging Quantity = 290 Pieces</li> </ul>
<ul> <li>Solder Tail Contact Plating = Tin over Nickel</li> </ul>	
	Product Availability:
Dimensions:	<ul> <li>Region = Asia, North America</li> </ul>
<ul> <li>Height (mm [in]) = 11.50 [0.453]</li> <li>DOD T it is a the (mm [in]) = 2.10 [0.400]</li> </ul>	
<ul> <li>PCB Tail Length (mm [in]) = 3.10 [0.122]</li> </ul>	Other:
<ul> <li>PCB Thickness, Recommended (mm [in]) = 1.60 [0.063]</li> </ul>	Brand = TE Connectivity
Body Features:	
<ul> <li>Inverted Jack Face = No</li> </ul>	

Corporate Information	
About TE	
Investors	
News Room	
Supplier Portal	
Careers	
Terms & Conditions	
Privacy Policy	

Quick Links Distributor Inventory Product Cross Reference Documents & Drawings Product Compliance Support Center Site Map Customer Support Email or Chat With Us Find a Phone Number Knowledge Base Manage Your Account

## Keep Me Informed

