



CONNECTORS

AUTOMOTIVE, TRUCK, BUS, & OFF-ROAD HOUSINGS



✓ Active

TE CONNECTIVITY (TE)

MQS SOCKET HSG 2POS.

AMP | MQS

1-1718333-1

TE Internal Number: 1-1718333-1

EU RoHS Compliant

EU ELV Compliant

Connector Style Housing for female terminals

Mating Tab Width .63 mm [.025 in]

Connector System Wire-to-Board, Wire-to-Device, Wire-to-Wire

Number of Positions 2

Centerline (Pitch) 2.54 mm [.1 in]

↓ **PRODUCT DRAWING**
English

↓ **3D PDF**

DOCUMENTATION

Product Drawings

Micro Quadlok System SOCKET HOUSING,2 POS. Buchsengehaeuse, 2 Polig.

PDF

English

CAD Files

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

Customer View Model

2D_DXF.ZIP

English

3D PDF

PDF

English

Product Specifications

Application Specification

MICRO QUADLOK SYSTEM PIN- AND SOCKET HOUSING WITH INTEGRATED RETAINER

PDF

English

MICRO QUADLOK SYSTEM PIN- AND SOCKET HOUSING WITH INTEGRATED RETAINER

TIF

English

MICRO-QUADLOCK-SYSTEM STIFT-UND BUCHSENGEHAUSE MIT ANGESPRITZTER ZWEITER KONTAKTSICHERUNG

TIF

English

Product Specification

PRODUCT SPECIFICATION, MICRO QUADLOK SYSTEM PIN AND SOCKET HOUSING WITH INTEGRATED RETAINER

PDF

English

Product Environmental Compliance

TE Material Declaration

MD_1-1718333-1_05052015455_dmtec

PDF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Connector Style Housing for female terminals

Connector System Wire-to-Board, Wire-to-Device, Wire-to-Wire

Sealable No

Hybrid Connector No

Primary Locking Feature On the terminal

Strain Relief No

Configuration Features

Number of Positions 2

Number of Rows 1

Body Features

Color Black

Cable Exit Angle 180°

Body Material PBT GF

Contact Features

Mating Tab Width .63 mm [.025 in]

Mechanical Attachment

Mounting Feature No

Terminal Position Assurance Yes

Polarized Yes

Housing Features

Centerline (Pitch) 2.54 mm [.1 in]

Dimensions

Width 16.7 mm [.657 in]

Height 6.2 mm [.244 in]

Length 8 mm [.315 in]

Usage Conditions

Operating Temperature Range -40 – 80 °C [-40 – 176 °F]

Operation/Application

Circuit Application Signal

Industry Standards

UL Flammability Rating UL 94-HB

Packaging Features

Packaging Method Box

Other

Connector Position Assurance Capable No

Serviceable No

PRODUCT COMPLIANCE



Statement of Compliance

Statement of Compliance

PDF
