

R46\_310, Film, Metallized Polypropylene, Safety, 4.7 uF, 20%, 310 VAC (X2), 630 VDC, 110°C, Lead Spacing = 27.5mm



**Dimensions**

L	32mm +0.3mm
H	33mm +0.1mm
T	18mm +0.2mm
S	27.5mm +/-0.4mm
LL	4mm +2mm
F	0.8mm +/-0.05mm

**Packaging Specifications**

Packaging:	Tray
Packaging Quantity:	256

**General Information**

Supplier:	KEMET
Series:	R46_310
Dielectric:	Metallized Polypropylene
Style:	Radial
Features:	EMI Safety
RoHS:	Yes
Lead:	Cut
Qualifications:	ENEC, UL, cUL, CQC

**Specifications**

Capacitance:	4.7 uF
Capacitance Tolerance:	20%
Voltage AC:	310 VAC (X2)
Voltage DC:	630 VDC
Temperature Range:	-40/+110C
Rated Temperature:	110°C
Dissipation Factor:	0.10% 1kHz
Insulation Resistance:	6.383 GOhms
Max dV/dt:	150 V/us
Safety Class:	X2