

Coaxial Cable Connector 11_SMA-50-1-4/111_N

Description

Straight cable plug

Interface standards

IEC 60169-15_MIL-STD-348A/310_CECC 22110



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	18 GHz

Mechanical Data

Centre contact	soldered
Outer 2contact	crimped
Weight	0.0041 kg

Environmental Data

Operating temperature 2011/65/EU (RoHS)	-65 °C to 165 °C compliant
--	-------------------------------

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Body	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Insulator	PFA / PTFE	
Coupling nut	Bronze	Gold Plating (Nickel underplated)
Gasket	VMQ (Silicone rubber)	
Crimp ferrule	Copper	

Related Documents

Outline drawing	DOU-00007584
Catalogue drawing	DOU-00006102
Assembly instruction	DOC-0000179314

Ordering Information

Single package	11_SMA-50-1-4/111_NE
----------------	----------------------

Additional Information

Suitable cables	RG_178_B/U, RG_196_A/U
-----------------	------------------------