

URTK/S - Test disconnect terminal block



0311087

<https://www.phoenixcontact.com/us/products/0311087>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Test disconnect terminal block, with two test sockets for 4 mm test plugs, or for receiving bridge bars or screw bridges, nom. voltage: 400 V, nominal current: 41 A, connection method: Screw connection, 1 level, Rated cross section: 6 mm², cross section: 0.5 mm² - 10 mm², mounting type: NS 35/7,5, NS 35/15, NS 32, color: gray

Your advantages

- Easy and clear testing in current transformer secondary circuits can be performed using the test disconnect terminal blocks of the URTK/S range
- On both sides of the disconnect point, the terminal block has a test socket which can also be used to switch across to neighboring terminal blocks

Commercial data

| | |
|--------------------------------------|---------------------|
| Item number | 0311087 |
| Packing unit | 50 pc |
| Minimum order quantity | 50 pc |
| Sales key | BE12 |
| Product key | BE1233 |
| Catalog page | Page 519 (C-1-2019) |
| GTIN | 4017918001292 |
| Weight per piece (including packing) | 35.64 g |
| Weight per piece (excluding packing) | 33.94 g |
| Customs tariff number | 85369010 |
| Country of origin | DE |

Technical data

Product properties

| | |
|-----------------------|--------------------------------|
| Product type | Test disconnect terminal block |
| Number of connections | 2 |
| Number of rows | 1 |
| Potentials | 1 |

Insulation characteristics

| | |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution | 3 |

Electrical properties

| | |
|---|--------|
| Rated surge voltage | 6 kV |
| Maximum power dissipation for nominal condition | 1.31 W |

Connection data

| | |
|---------------------------------|-------------------|
| Number of connections per level | 2 |
| Nominal cross section | 6 mm ² |

1 level

| | |
|---|--|
| Screw thread | M4 |
| Tightening torque | 1.2 ... 1.5 Nm |
| Stripping length | 13 mm |
| Internal cylindrical gage | A5 |
| Connection in acc. with standard | IEC 60947-7-1 |
| Conductor cross section rigid | 0.5 mm ² ... 10 mm ² |
| Cross section AWG | 20 ... 8 (converted acc. to IEC) |
| Conductor cross section flexible | 0.5 mm ² ... 6 mm ² |
| Conductor cross section, flexible [AWG] | 20 ... 10 (converted acc. to IEC) |
| Conductor cross-section flexible (ferrule without plastic sleeve) | 0.5 mm ² ... 6 mm ² |
| Flexible conductor cross section (ferrule with plastic sleeve) | 0.5 mm ² ... 4 mm ² |
| 2 conductors with same cross section, solid | 0.5 mm ² ... 2.5 mm ² |
| 2 conductors with same cross section, flexible | 0.5 mm ² ... 6 mm ² |
| 2 conductors with same cross section, flexible, with ferrule without plastic sleeve | 0.5 mm ² ... 4 mm ² |
| 2 conductors with the same cross section, flexible, with TWIN ferrule with plastic sleeve | 0.5 mm ² ... 4 mm ² |
| Nominal current | 41 A |
| Maximum load current | 57 A (with 10 mm ² conductor cross section) |
| Nominal voltage | 400 V |
| Nominal cross section | 6 mm ² |

Dimensions

| | |
|-------|--------|
| Width | 8.2 mm |
|-------|--------|

URTK/S - Test disconnect terminal block



0311087

<https://www.phoenixcontact.com/us/products/0311087>

| | |
|--------------------|---------|
| End cover width | 2.2 mm |
| Height | 72 mm |
| Depth on NS 32 | 56.5 mm |
| Depth on NS 35/7,5 | 51.5 mm |
| Depth on NS 35/15 | 59 mm |

Material specifications

| | |
|---|-------------|
| Color | gray |
| Flammability rating according to UL 94 | V0 |
| Insulating material group | I |
| Insulating material | PA |
| Static insulating material application in cold | -60 °C |
| Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21)) | 125 °C |
| Relative insulation material temperature index (Elec., UL 746 B) | 130 °C |
| Fire protection for rail vehicles (DIN EN 45545-2) R22 | HL 1 - HL 3 |
| Fire protection for rail vehicles (DIN EN 45545-2) R23 | HL 1 - HL 3 |
| Fire protection for rail vehicles (DIN EN 45545-2) R24 | HL 1 - HL 3 |
| Fire protection for rail vehicles (DIN EN 45545-2) R26 | HL 1 - HL 3 |
| Calorimetric heat release NFPA 130 (ASTM E 1354) | 27,5 MJ/kg |
| Surface flammability NFPA 130 (ASTM E 162) | passed |
| Specific optical density of smoke NFPA 130 (ASTM E 662) | passed |
| Smoke gas toxicity NFPA 130 (SMP 800C) | passed |

Electrical tests

Surge voltage test

| | |
|-----------------------|-------------|
| Test voltage setpoint | 7.3 kV |
| Result | Test passed |

Temperature-rise test

| | |
|---|-------------------------------------|
| Requirement temperature-rise test | Increase in temperature \leq 45 K |
| Result | Test passed |
| Short-time withstand current 6 mm ² | 0.72 kA |
| Short-time withstand current 10 mm ² | 1.2 kA |
| Result | Test passed |

Power-frequency withstand voltage

| | |
|-----------------------|-------------|
| Test voltage setpoint | 1.89 kV |
| Result | Test passed |

Mechanical properties

Mechanical data

| | |
|-----------------|-----|
| Open side panel | Yes |
|-----------------|-----|

Mechanical tests

URTK/S - Test disconnect terminal block



0311087

<https://www.phoenixcontact.com/us/products/0311087>

Mechanical strength

| | |
|--------|-------------|
| Result | Test passed |
|--------|-------------|

Attachment on the carrier

| | |
|-------------------------|-------------|
| DIN rail/fixing support | NS 32/NS 35 |
| Test force setpoint | 5 N |
| Result | Test passed |

Test for conductor damage and slackening

| | |
|--------------------------------|------------------------------|
| Rotation speed | 10 rpm |
| Revolutions | 135 |
| Conductor cross section/weight | 0.5 mm ² / 0.3 kg |
| | 6 mm ² / 1.4 kg |
| | 10 mm ² / 2 kg |
| Result | Test passed |

Environmental and real-life conditions

Needle-flame test

| | |
|------------------|-------------|
| Time of exposure | 30 s |
| Result | Test passed |

Ambient conditions

| | |
|--|--|
| Ambient temperature (operation) | -60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.) |
| Ambient temperature (storage/transport) | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C) |
| Ambient temperature (assembly) | -5 °C ... 70 °C |
| Ambient temperature (actuation) | -5 °C ... 70 °C |
| Permissible humidity (operation) | 20 % ... 90 % |
| Permissible humidity (storage/transport) | 30 % ... 70 % |

Standards and regulations

| | |
|----------------------------------|---------------|
| Connection in acc. with standard | IEC 60947-7-1 |
|----------------------------------|---------------|

Mounting

| | |
|---------------|-----------|
| Mounting type | NS 35/7,5 |
| | NS 35/15 |
| | NS 32 |
| Screw thread | M3 |

URTK/S - Test disconnect terminal block



0311087

<https://www.phoenixcontact.com/us/products/0311087>

Drawings

Circuit diagram




URTK/S - Test disconnect terminal block

0311087

<https://www.phoenixcontact.com/us/products/0311087>

Schematic diagram



Three-phase transducer test set


URTK/S - Test disconnect terminal block



0311087

<https://www.phoenixcontact.com/us/products/0311087>

Circuit diagram




URTK/S - Test disconnect terminal block

0311087

<https://www.phoenixcontact.com/us/products/0311087>



Schematic diagram




Three-phase linked transducer test set

URTK/S - Test disconnect terminal block

0311087

<https://www.phoenixcontact.com/us/products/0311087>

Schematic diagram



Simple current transformer test circuit

a = normal operation

b = measured value testing

c = transformer short-circuit

d = relay testing

URTK/S - Test disconnect terminal block





0311087

<https://www.phoenixcontact.com/us/products/0311087>


Approvals


To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/0311087>

|  CSA Approval ID: 13631 | | | | |
|--|-----------------------|-----------------------|-------------------|-----------------------------|
| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
| | 300 V | 40 A | 26 - 10 | - |


|  IECEE CB Scheme Approval ID: NL-65058 | | | | |
|---|-----------------------|-----------------------|-------------------|-----------------------------|
| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
| | 400 V | - | - | - 6 |

|  EAC Approval ID: RU C-DE.BL08.B.00534 | | | | |
|--|--|--|--|--|
|--|--|--|--|--|

|  cULus Recognized Approval ID: E60425 | | | | |
|--|-----------------------|-----------------------|-------------------|-----------------------------|
| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
| Use group B | 300 V | 50 A | 26 - 8 | - |
| Use group C | 300 V | 50 A | 26 - 8 | - |

|  KEMA-KEUR Approval ID: 71-113436 REV.1 | | | | |
|--|-----------------------|-----------------------|-------------------|-----------------------------|
| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
| | 400 V | - | - | - 6 |

|  LR Approval ID: LR2041789TA-02 | | | | |
|--|--|--|--|--|
|--|--|--|--|--|

|  RS Approval ID: 22.44.01.00083.250 | | | | |
|--|--|--|--|--|
|--|--|--|--|--|

URTK/S - Test disconnect terminal block



0311087

<https://www.phoenixcontact.com/us/products/0311087>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-11.0 | 27141126 |
| ECLASS-12.0 | 27141126 |
| ECLASS-13.0 | 27250109 |

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC000902 |
|----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

URTK/S - Test disconnect terminal block



0311087

<https://www.phoenixcontact.com/us/products/0311087>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC


| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

URTK/S - Test disconnect terminal block

0311087

<https://www.phoenixcontact.com/us/products/0311087>

Accessories

 Note: Applying some accessories below might limit this product.


FB 10- RTK/S - Screw bridge

0311171

<https://www.phoenixcontact.com/us/products/0311171>



Screw bridge, pitch: 8.2 mm, number of positions: 10, color: silver

 Max. current carrying capacity: 41 A


EB 2- 8 - Insertion bridge

0202154

<https://www.phoenixcontact.com/us/products/0202154>



Insertion bridge, pitch: 8 mm, number of positions: 2, color: gray

 Max. current carrying capacity: 41 A

URTK/S - Test disconnect terminal block


0311087

<https://www.phoenixcontact.com/us/products/0311087>


EB 3- 8 - Insertion bridge

0202141

<https://www.phoenixcontact.com/us/products/0202141>




Insertion bridge, pitch: 8 mm, number of positions: 3, color: gray

 Max. current carrying capacity: 41 A

EB 10- 8 - Insertion bridge

0202138

<https://www.phoenixcontact.com/us/products/0202138>



Insertion bridge, pitch: 8 mm, number of positions: 10, color: gray

 Max. current carrying capacity: 41 A

URTK/S - Test disconnect terminal block

0311087

<https://www.phoenixcontact.com/us/products/0311087>

S - Switching lock

0308359

<https://www.phoenixcontact.com/us/products/0308359>



Switching lock, for disconnect slides, width: 8.2 mm, height: 12 mm, color: white


ASB 2-RTK/S - Switching jumper

0311281

<https://www.phoenixcontact.com/us/products/0311281>



Switching jumper, pitch: 8.2 mm, number of positions: 2, color: silver

 Max. current carrying capacity: 35 A

URTK/S - Test disconnect terminal block

0311087

<https://www.phoenixcontact.com/us/products/0311087>


USB 2-RTK/S - Switching jumper

0311278

<https://www.phoenixcontact.com/us/products/0311278>



Switching jumper, pitch: 8.2 mm, number of positions: 2, color: silver

 Max. current carrying capacity: 35 A


SB 4-RTK/S - Switching jumper

0311265

<https://www.phoenixcontact.com/us/products/0311265>



Switching jumper, pitch: 8.2 mm, number of positions: 4, color: silver

 Max. current carrying capacity: 35 A

URTK/S - Test disconnect terminal block

0311087

<https://www.phoenixcontact.com/us/products/0311087>


SB 2-RTK/S - Switching jumper

0311236

<https://www.phoenixcontact.com/us/products/0311236>



Switching jumper, pitch: 8.2 mm, number of positions: 2, color: silver

 Max. current carrying capacity: 35 A


EB 4- 8 - Insertion bridge

0202142

<https://www.phoenixcontact.com/us/products/0202142>



Insertion bridge, pitch: 8 mm, number of positions: 4, color: gray

 Max. current carrying capacity: 41 A

URTK/S - Test disconnect terminal block


0311087

<https://www.phoenixcontact.com/us/products/0311087>


EB 1/3/5/7-8 - Insertion bridge

3072340

<https://www.phoenixcontact.com/us/products/3072340>




Insertion bridge, pitch: 16.4 mm, number of positions: 4, pin assignment: 1, 3, 5, 7, length: 24 mm, color: gray

 Max. current carrying capacity: 41 A


EB 1/3/5-8 - Insertion bridge

3072341

<https://www.phoenixcontact.com/us/products/3072341>



Insertion bridge, pitch: 16.4 mm, number of positions: 3, pin assignment: 1,3,5, length: 24 mm, color: gray

 Max. current carrying capacity: 41 A

URTK/S - Test disconnect terminal block

0311087

<https://www.phoenixcontact.com/us/products/0311087>

D-URTK - Cover

0310020

<https://www.phoenixcontact.com/us/products/0310020>

Cover, depth: 41.5 mm, width: 2.2 mm, height: 72 mm, color: gray



TS-RTK - Partition plate

0310211

<https://www.phoenixcontact.com/us/products/0310211>

Partition plate, width: 0.8 mm, height: 72 mm, color: gray



URTK/S - Test disconnect terminal block



0311087

<https://www.phoenixcontact.com/us/products/0311087>

ATS-RTK - Partition plate

0310224

<https://www.phoenixcontact.com/us/products/0310224>

Partition plate, depth: 45.8 mm, width: 0.8 mm, height: 97.5 mm, color: gray



SBS 8:UNBEDRUCKT - Marker card

1007235

<https://www.phoenixcontact.com/us/products/1007235>

Marker card, Card, white, unlabeled, can be labeled with: Marker pen, mounting type: snap into tall marker groove, snap into flat marker groove, for terminal block width: 8 mm, lettering field size: 6 x 8.1 mm



URTK/S - Test disconnect terminal block

0311087

<https://www.phoenixcontact.com/us/products/0311087>

AP-ME METER - Cover profile

3034361

<https://www.phoenixcontact.com/us/products/3034361>




Cover profile, for covering terminal strips, snapped onto APT-ME cover profile carrier or APH-ME end bracket. A cover profile carrier should be positioned at the ends and at intervals of around 40 cm. Length supplied: 1 m

APH-ME - Cover profile carrier

3034374

<https://www.phoenixcontact.com/us/products/3034374>



Cover profile carrier, for mounting on NS 35/7,5 DIN rail, for fixing the AP-ME cover profile, can be sealed as an option

URTK/S - Test disconnect terminal block

0311087

<https://www.phoenixcontact.com/us/products/0311087>

APT-ME - Cover profile carrier

3034358

<https://www.phoenixcontact.com/us/products/3034358>

Cover profile carrier for mounting on NS 35/7.5 DIN rail for attaching the cover profile AP-ME




TS-UK 6-T - Separating plate

3072820

<https://www.phoenixcontact.com/us/products/3072820>

Separating plate, depth: 62.5 mm, width: 1 mm, height: 66.5 mm, color: gray



URTK/S - Test disconnect terminal block

0311087

<https://www.phoenixcontact.com/us/products/0311087>

SCP 2-8 - Short-circuit connector

3070402

<https://www.phoenixcontact.com/us/products/3070402>



Short-circuit connector, pitch: 8.15 mm, number of positions: 2, color: orange

SCP 3-8 - Short-circuit connector

3070403

<https://www.phoenixcontact.com/us/products/3070403>



Short-circuit connector, pitch: 8.15 mm, number of positions: 3, color: orange

URTK/S - Test disconnect terminal block



0311087

<https://www.phoenixcontact.com/us/products/0311087>

SCP 4-8 - Short-circuit connector

3070404

<https://www.phoenixcontact.com/us/products/3070404>



Short-circuit connector, pitch: 8.15 mm, number of positions: 4, color: orange

SCPI 2-8 - Short-circuit connector

3070423

<https://www.phoenixcontact.com/us/products/3070423>



Short-circuit connector, pitch: 8.15 mm, number of positions: 2, color: orange

URTK/S - Test disconnect terminal block

0311087

<https://www.phoenixcontact.com/us/products/0311087>



SCPI 4-8 - Short-circuit connector

3070424

<https://www.phoenixcontact.com/us/products/3070424>



Short-circuit connector, pitch: 8.15 mm, number of positions: 4, color: orange

NS 32 PERF 2000MM-VPE 10 - DIN rail perforated

1201002

<https://www.phoenixcontact.com/us/products/1201002>



DIN rail perforated, Pack of 10 (20 m), acc. to EN 60715, material: Steel, galvanized, passivated with a thick layer, G profile, color: silver

URTK/S - Test disconnect terminal block

0311087

<https://www.phoenixcontact.com/us/products/0311087>



NS 32 UNPERF 2000MM-VPE 10 - DIN rail, unperforated

1201015

<https://www.phoenixcontact.com/us/products/1201015>



DIN rail, unperforated, Pack of 10 (20 m), acc. to EN 60715, material: Steel, galvanized, passivated with a thick layer, G profile, color: silver

NS 35/ 7,5 PERF 2000MM - DIN rail perforated

0801733

<https://www.phoenixcontact.com/us/products/0801733>



DIN rail perforated, Pack of 25 (50 m), acc. to EN 60715, material: Steel, galvanized, passivated with a thick layer, Standard profile, color: silver

URTK/S - Test disconnect terminal block

0311087

<https://www.phoenixcontact.com/us/products/0311087>

NS 35/ 7,5 UNPERF 2000MM - DIN rail, unperforated

0801681

<https://www.phoenixcontact.com/us/products/0801681>



DIN rail, unperforated, Pack of 25 (50 m), acc. to EN 60715, material: Steel, galvanized, passivated with a thick layer, Standard profile, color: silver

NS 35/ 7,5 WH PERF 2000MM - DIN rail perforated

1204119

<https://www.phoenixcontact.com/us/products/1204119>



DIN rail perforated, Pack of 25 (50 m), acc. to EN 60715, material: Steel, Galvanized, white passivated, Standard profile, color: silver

URTK/S - Test disconnect terminal block

0311087

<https://www.phoenixcontact.com/us/products/0311087>



NS 35/ 7,5 WH UNPERF 2000MM-VPE 10 - DIN rail, unperforated

1204122

<https://www.phoenixcontact.com/us/products/1204122>



DIN rail, unperforated, Pack of 10 (20 m), acc. to EN 60715, material: Steel, Galvanized, white passivated, Standard profile, color: silver

NS 35/ 7,5 AL UNPERF 2000MM - DIN rail, unperforated

0801704

<https://www.phoenixcontact.com/us/products/0801704>



DIN rail, unperforated, Pack of 25 (50 m), acc. to EN 60715, material: Aluminum, uncoated, Standard profile, color: silver

URTK/S - Test disconnect terminal block

0311087

<https://www.phoenixcontact.com/us/products/0311087>

NS 35/ 7,5 ZN PERF 2000MM - DIN rail perforated

1206421

<https://www.phoenixcontact.com/us/products/1206421>



DIN rail perforated, Pack of 25 (50 m), acc. to EN 60715, material: Steel, galvanized, Standard profile, color: silver

NS 35/ 7,5 ZN UNPERF 2000MM - DIN rail, unperforated

1206434

<https://www.phoenixcontact.com/us/products/1206434>



DIN rail, unperforated, Pack of 25 (50 m), acc. to EN 60715, material: Steel, galvanized, Standard profile, color: silver

URTK/S - Test disconnect terminal block

0311087

<https://www.phoenixcontact.com/us/products/0311087>



NS 35/ 7,5 CU UNPERF 2000MM-VPE 10 - DIN rail, unperforated

0801762

<https://www.phoenixcontact.com/us/products/0801762>



DIN rail, unperforated, Pack of 10 (20 m), acc. to EN 60715, material: Copper, uncoated, Standard profile, color: copper-colored

NS 35/ 7,5 CAP - End cap

1206560

<https://www.phoenixcontact.com/us/products/1206560>

DIN rail end piece, for DIN rail NS 35/7.5



URTK/S - Test disconnect terminal block

0311087

<https://www.phoenixcontact.com/us/products/0311087>

NS 35/15 PERF 2000MM - DIN rail perforated

1201730

<https://www.phoenixcontact.com/us/products/1201730>



DIN rail perforated, Pack of 25 (50 m), similar to EN 60715, material: Steel, galvanized, passivated with a thick layer, Standard profile, color: silver

NS 35/15 UNPERF 2000MM - DIN rail, unperforated

1201714

<https://www.phoenixcontact.com/us/products/1201714>



DIN rail, unperforated, Pack of 25 (50 m), similar to EN 60715, material: Steel, galvanized, passivated with a thick layer, Standard profile, color: silver

URTK/S - Test disconnect terminal block

0311087

<https://www.phoenixcontact.com/us/products/0311087>



NS 35/15 WH PERF 2000MM - DIN rail perforated

0806602

<https://www.phoenixcontact.com/us/products/0806602>



DIN rail perforated, Pack of 25 (50 m), similar to EN 60715, material: Steel, Galvanized, white passivated, Standard profile, color: white

NS 35/15 WH UNPERF 2000MM-VPE 10 - DIN rail, unperforated

1204135

<https://www.phoenixcontact.com/us/products/1204135>



DIN rail, unperforated, Pack of 10 (20 m), similar to EN 60715, material: Steel, Galvanized, white passivated, Standard profile, color: silver

URTK/S - Test disconnect terminal block



0311087

<https://www.phoenixcontact.com/us/products/0311087>

NS 35/15 AL UNPERF 2000MM - DIN rail, unperforated

1201756

<https://www.phoenixcontact.com/us/products/1201756>



DIN rail, unperforated, similar to EN 60715, material: Aluminum, uncoated, Standard profile, color: silver

NS 35/15 ZN PERF 2000MM - DIN rail perforated

1206599

<https://www.phoenixcontact.com/us/products/1206599>



DIN rail perforated, Pack of 25 (50 m), similar to EN 60715, material: Steel, galvanized, Standard profile, color: silver

URTK/S - Test disconnect terminal block

0311087

<https://www.phoenixcontact.com/us/products/0311087>



NS 35/15 ZN UNPERF 2000MM - DIN rail, unperforated

1206586

<https://www.phoenixcontact.com/us/products/1206586>



DIN rail, unperforated, Pack of 25 (50 m), similar to EN 60715, material: Steel, galvanized, Standard profile, color: silver

NS 35/15 CU UNPERF 2000MM-VPE 10 - DIN rail, unperforated

1201895

<https://www.phoenixcontact.com/us/products/1201895>



DIN rail, unperforated, Pack of 10 (20 m), similar to EN 60715, material: Copper, uncoated, Standard profile, color: copper-colored

URTK/S - Test disconnect terminal block

0311087

<https://www.phoenixcontact.com/us/products/0311087>



NS 35/15 CAP - End cap

1206573

<https://www.phoenixcontact.com/us/products/1206573>

DIN rail end piece, for DIN rail NS 35/15



NS 35/15-2,3 UNPERF 2000MM-VPE 10 - DIN rail, unperforated

1201798

<https://www.phoenixcontact.com/us/products/1201798>



DIN rail, unperforated, Pack of 10 (20 m), acc. to EN 60715, material: Steel, galvanized, passivated with a thick layer, Standard profile 2.3 mm, color: silver

URTK/S - Test disconnect terminal block

0311087

<https://www.phoenixcontact.com/us/products/0311087>

ZB 8:UNBEDRUCKT - Zack marker strip

1052002

<https://www.phoenixcontact.com/us/products/1052002>




Zack marker strip, Strip, white, unlabeled, can be labeled with: PLOTMARK, CMS-P1-PLOTTER, mounting type: snapped, for terminal block width: 8.2 mm, lettering field size: 10.5 x 8.15 mm, Number of individual labels: 10

ZB 8 CUS - Zack marker strip

0825011

<https://www.phoenixcontact.com/us/products/0825011>



Zack marker strip, can be ordered: Strip, white, labeled according to customer specifications, mounting type: snap into tall marker groove, for terminal block width: 8.2 mm, lettering field size: 10.5 x 8.15 mm, Number of individual labels: 10

URTK/S - Test disconnect terminal block



0311087

<https://www.phoenixcontact.com/us/products/0311087>

UC-TM 8 - Marker for terminal blocks

0818072

<https://www.phoenixcontact.com/us/products/0818072>



Marker for terminal blocks, Sheet, white, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: snapped, for terminal block width: 8.2 mm, lettering field size: 7.6 x 10.5 mm, Number of individual labels: 56

UC-TM 8 CUS - Marker for terminal blocks

0824597

<https://www.phoenixcontact.com/us/products/0824597>



Marker for terminal blocks, can be ordered: by sheet, white, labeled according to customer specifications, mounting type: snap into tall marker groove, for terminal block width: 8.2 mm, lettering field size: 7.6 x 10.5 mm, Number of individual labels: 56

URTK/S - Test disconnect terminal block



0311087

<https://www.phoenixcontact.com/us/products/0311087>

UCT-TM 8 - Marker for terminal blocks

0828740

<https://www.phoenixcontact.com/us/products/0828740>



Marker for terminal blocks, Sheet, white, unlabeled, can be labeled with: TOPMARK NEO, TOPMARK LASER, BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: snapped, for terminal block width: 8.2 mm, lettering field size: 7.6 x 10.5 mm, Number of individual labels: 42

UCT-TM 8 CUS - Marker for terminal blocks

0829616

<https://www.phoenixcontact.com/us/products/0829616>



Marker for terminal blocks, can be ordered: by sheet, white, labeled according to customer specifications, mounting type: snap into tall marker groove, for terminal block width: 8.2 mm, lettering field size: 7.6 x 10.5 mm, Number of individual labels: 42

URTK/S - Test disconnect terminal block


0311087

<https://www.phoenixcontact.com/us/products/0311087>

ZB 8,LGS:FORTL.ZAHLEN - Zack marker strip

1052015

<https://www.phoenixcontact.com/us/products/1052015>



Zack marker strip, Strip, white, labeled, can be labeled with: CMS-P1-PLOTTER, printed horizontally: consecutive numbers 1 ... 10, 11 ... 20, etc. up to 91 ... 100, mounting type: snapped, for terminal block width: 8.2 mm, lettering field size: 10. 5 x 8.15 mm, Number of individual labels: 10

ZB 8,QR:FORTL.ZAHLEN - Zack marker strip

1052028

<https://www.phoenixcontact.com/us/products/1052028>



Zack marker strip, Strip, white, labeled, can be labeled with: CMS-P1-PLOTTER, Printed vertically: consecutive numbers 1 ... 10, 11 ... 20, etc. up to 91 ... 100, mounting type: snapped, for terminal block width: 8.2 mm, lettering field size: 10. 5 x 8.15 mm, Number of individual labels: 10

URTK/S - Test disconnect terminal block


0311087

<https://www.phoenixcontact.com/us/products/0311087>

ZB 8,LGS:L1-N,PE - Marker for terminal blocks

1052413

<https://www.phoenixcontact.com/us/products/1052413>



Marker for terminal blocks, Strip, white, labeled, can be labeled with: CMS-P1-PLOTTER, horizontal: L1, L2, L3, N, PE, L1, L2, L3, N, PE, mounting type: snapped, for terminal block width: 8.2 mm, lettering field size: 10.5 x 8.15 mm, Number of individual labels: 10

CLIPFIX 35 - End bracket

3022218

<https://www.phoenixcontact.com/us/products/3022218>



Quick mounting end clamp for NS 35/7,5 DIN rail or NS 35/15 DIN rail, with marking option, width: 9.5 mm, color: gray

URTK/S - Test disconnect terminal block

0311087

<https://www.phoenixcontact.com/us/products/0311087>



CLIPFIX 35-5 - End bracket

3022276

<https://www.phoenixcontact.com/us/products/3022276>




Quick mounting end clamp for NS 35/7,5 DIN rail or NS 35/15 DIN rail, with marking option, with parking option for FBS...5, FBS...6, KSS 5, KSS 6, width: 5.15 mm, color: gray

E/NS 35 N - End bracket

0800886

<https://www.phoenixcontact.com/us/products/0800886>



End clamp, width: 9.5 mm, color: gray

URTK/S - Test disconnect terminal block

0311087

<https://www.phoenixcontact.com/us/products/0311087>

E/UK - End bracket

1201442

<https://www.phoenixcontact.com/us/products/1201442>

End bracket, Mounting on a DIN rail NS 32 or NS 35, material: PA, color: gray



E/UK 1 - End bracket

1201413

<https://www.phoenixcontact.com/us/products/1201413>

End clamps, for supporting the ends of double-level and three-level terminal blocks, width: 10 mm, color: gray



URTK/S - Test disconnect terminal block

0311087

<https://www.phoenixcontact.com/us/products/0311087>



PSBJ 3,5/18/6 FARBLOS - Test plug strip

0311391

<https://www.phoenixcontact.com/us/products/0311391>

Test plug strip, number of positions: 1, color: transparent



PSBJ 3,5/18/6 BK - Test plug strip

0311388

<https://www.phoenixcontact.com/us/products/0311388>

Test plug strip, number of positions: 1, color: black



URTK/S - Test disconnect terminal block

0311087

<https://www.phoenixcontact.com/us/products/0311087>



PSBJ 3,5/18/6 GY - Test plug strip

0311375

<https://www.phoenixcontact.com/us/products/0311375>



Test plug strip, number of positions: 1, color: gray

PSBJ 3,5/18/6 VT - Test plug strip

0311362

<https://www.phoenixcontact.com/us/products/0311362>



Test plug strip, number of positions: 1, color: violet

URTK/S - Test disconnect terminal block

0311087

<https://www.phoenixcontact.com/us/products/0311087>



PSBJ 3,5/18/6 GN - Test plug strip

0311359

<https://www.phoenixcontact.com/us/products/0311359>



Test plug strip, number of positions: 1, color: green

PSBJ 3,5/18/6 YE - Test plug strip

0311346

<https://www.phoenixcontact.com/us/products/0311346>



Test plug strip, number of positions: 1, color: yellow

URTK/S - Test disconnect terminal block

0311087

<https://www.phoenixcontact.com/us/products/0311087>



PSBJ 3,5/18/6 BU - Test plug strip

0311333

<https://www.phoenixcontact.com/us/products/0311333>



Test plug strip, number of positions: 1, color: blue

PSBJ 3,5/18/6 RD - Test plug strip

0311320

<https://www.phoenixcontact.com/us/products/0311320>



Test plug strip, number of positions: 1, color: red

URTK/S - Test disconnect terminal block

0311087

<https://www.phoenixcontact.com/us/products/0311087>

PSBJ 3,5/18/6 WH - Test plug strip

0311317

<https://www.phoenixcontact.com/us/products/0311317>



Test plug strip, number of positions: 1, color: white

PSBJ-URTK/S RD - Test plug strip

0311744

<https://www.phoenixcontact.com/us/products/0311744>



Test plug strip, number of positions: 1, color: red

URTK/S - Test disconnect terminal block

0311087

<https://www.phoenixcontact.com/us/products/0311087>

PSBJ-URTK/S BU - Test plug strip

0311757

<https://www.phoenixcontact.com/us/products/0311757>



Test plug strip, number of positions: 1, color: blue

PSBJ-URTK/S YE - Test plug strip

0311731

<https://www.phoenixcontact.com/us/products/0311731>



Test plug strip, number of positions: 1, color: yellow

URTK/S - Test disconnect terminal block

0311087

<https://www.phoenixcontact.com/us/products/0311087>



PSBJ-URTK/S GN - Test plug strip

0311760

<https://www.phoenixcontact.com/us/products/0311760>



Test plug strip, number of positions: 1, color: green

PSBJ-URTK/S VT - Test plug strip

0311773

<https://www.phoenixcontact.com/us/products/0311773>



Test plug strip, number of positions: 1, color: violet

URTK/S - Test disconnect terminal block

0311087

<https://www.phoenixcontact.com/us/products/0311087>



PSBJ-URTK/S BK - Test plug strip

0311728

<https://www.phoenixcontact.com/us/products/0311728>

Test plug strip, number of positions: 1, color: black



SZS 1,0X4,0 VDE - Screwdriver

1205066

<https://www.phoenixcontact.com/us/products/1205066>

Screwdriver, slot-headed, VDE insulated, size: 1.0 x 4.0 x 100 mm, 2-component grip, with non-slip grip



Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com