

Fuse plug - ST-SILA250-UK 4 - 0921053

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Fuse plug, nominal current: 6.3 A, length: 33.1 mm, width: 6.1 mm, height: 45.7 mm, color: black

The figure shows the version without LED/light indicator



Key Commercial Data

Packing unit	1 pc
GTIN	 4 017918 010317
GTIN	4017918010317
Weight per Piece (excluding packing)	5.960 g
Custom tariff number	85369095
Country of origin	Poland

Technical data

General

Note	If the fuse is defective, the downstream circuit is not off load
Color	black
Insulating material	PA
Flammability rating according to UL 94	V2
Maximum power dissipation for nominal condition	1.5 W

Dimensions

Width	6.1 mm
Length	33.1 mm

General

Fuse plug - ST-SILA250-UK 4 - 0921053

Technical data

General

Fuse	G / 5 x 20
Insulating material group	CTI 600
LED voltage range	110 V AC/DC ... 250 V AC/DC
LED current range	1 mA
Nominal current I _N	6.3 A
Nominal voltage U _N	250 V
Relative insulation material temperature index (Elec., UL 746 B)	130 °C
Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21))	125 °C
Static insulating material application in cold	-60 °C
Surface flammability NFPA 130 (ASTM E 162)	passed
Specific optical density of smoke NFPA 130 (ASTM E 662)	passed
Smoke gas toxicity NFPA 130 (SMP 800C)	passed
Calorimetric heat release NFPA 130 (ASTM E 1354)	27,5 MJ/kg
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R26	HL 1 - HL 3

Connection data

Connection method	Plug connection
-------------------	-----------------

Standards and Regulations

Connection in acc. with standard	CSA
Flammability rating according to UL 94	V2

Classifications

eCl@ss

eCl@ss 10.0.1	27142001
eCl@ss 11.0	27142001
eCl@ss 4.0	27142000
eCl@ss 4.1	27142000
eCl@ss 5.0	27142000
eCl@ss 5.1	27141100
eCl@ss 6.0	27142000
eCl@ss 7.0	27142001
eCl@ss 8.0	27142001
eCl@ss 9.0	27142001

Fuse plug - ST-SILA250-UK 4 - 0921053

Classifications

ETIM

ETIM 2.0	EC000897
ETIM 3.0	EC000897
ETIM 4.0	EC002018
ETIM 5.0	EC000036
ETIM 6.0	EC000035
ETIM 7.0	EC000035

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121409
UNSPSC 11	39121409
UNSPSC 12.01	39121409
UNSPSC 13.2	39121629
UNSPSC 18.0	39121629
UNSPSC 19.0	39121629
UNSPSC 20.0	39121629
UNSPSC 21.0	39121629

Approvals


Approvals

Approvals

CSA / UL Recognized / cUL Recognized / EAC / cULus Recognized


Ex Approvals


Approval details


CSA		http://www.csagroup.org/services-industries/product-listing/	13631
Nominal voltage UN	300 V		
Nominal current IN	10 A		


Fuse plug - ST-SILA250-UK 4 - 0921053

Approvals

UL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 60425
Nominal voltage UN	300 V		
Nominal current IN	6.3 A		

cUL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 60425
Nominal voltage UN	300 V		
Nominal current IN	6.3 A		

EAC		RU C- DE.BL08.B.00714
-----	--	--------------------------

cULus Recognized	
------------------	---