


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT 19 BY AMP INCORPORATED. ALL RIGHTS RESERVED.

Loc		DIST		REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD		
N		REDRAWN W/O CHANGE PER EC 0020-1300-95	11 DEC 95	DB	GS		
P		OBS -2 PER EC 0020-602-96	17 DEC 96	MB	GS		
R		REV PER EC 0320-82-97	13 AUG 97	BC	GS		



RECOMMENDED PANEL CUTOUT
SCALE 1:1

- 1 PHENOLIC PER MIL-M-14, TYPE CFG, BLACK.
- 2 DIALLYL PHTHALATE PER MIL-M-14, TYPE SDG-F, BLUE.
- 3. MATES WITH BLOCK 201037 AND ACCOMODATES TYPE II, TYPE III+ OR TYPE VI #16 PIN OR SOCKET CONTACTS.

OBsolete	2	201345-2
	1	201345-1
MATERIAL		PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN D. BROCKWAY 11 DEC 95	AMP Incorporated Harrisburg, PA 17105-3608	
DIMENSIONS: mm (INCHES)		CHK R. STONE 07 MAR 96	NAME BLOCK, MALE, 104 PLACE, MINIATURE RECTANGULAR, M SERIES	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD G. A. STEINHAUER 21 MAR 96	DRAWING NO A2 00779 ©=201345	
0 PLC ±-		PRODUCT SPEC	SIZE	
1 PLC ±-		APPLICATION SPEC	CAGE CODE	
2 PLC ±0.13 [.005]			DRAWING NO	
3 PLC ±-			SCALE	
4 PLC ±-			SHEET 1 OF 1	
ANGLES ±-			REV R	
FINISH -		WEIGHT -		
MATERIAL SEE TABLE		CUSTOMER DRAWING		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[201345-1](#)