



Vishay Semiconductors

# Small Signal Schottky Diodes, Single and Dual



#### **FEATURES**





 These devices are protected by a PN junction guard ring against excessive voltage, such as electrostatic discharges



• AEC-Q101 qualified available

RoHS

- Base P/N-E3 RoHS-compliant, commercial grade
- Base P/N-HE3 RoHS-compliant, AEC-Q101 qualified
- Material categorization: for definitions of compliance please see <a href="https://www.vishay.com/doc?99912"><u>www.vishay.com/doc?99912</u></a>

#### **MECHANICAL DATA**

Case: SOT-23

Weight: approx. 8.8 mg
Packaging codes/options:

18/10K per 13" reel (8 mm tape), 10K/box 08/3K per 7" reel (8 mm tape), 15K/box

<b>DESIGN SUPPORT TOOLS</b> click logo to get started
---



PARTS TABLE					
PART	ORDERING CODE	CIRCUIT CONFIGURATION	TYPE MARKING	REMARKS	
BAS70-00	BAS70-00-E3-08 or BAS70-00-E3-18	Cinalo	70		
	BAS70-00-HE3-08 or BAS70-00-HE3-18	Single	73	Tape and reel	
BAS70-04	BAS70-04-E3-08 or BAS70-04-E3-18	Dual serial	74		
	BAS70-04-HE3-08 or BAS70-04-HE3-18	Duai Seriai	74		
BAS70-05	BAS70-05-E3-08 or BAS70-05-E3-18	Common cathode	75		
	BAS70-05-HE3-08 or BAS70-05-HE3-18	Common camode	75		
BAS70-06	BAS70-06-E3-08 or BAS70-06-E3-18	Common anode	76		
	BAS70-06-HE3-08 or BAS70-06-HE3-18	Common anode	70		

<b>ABSOLUTE MAXIMUM RATINGS</b> (T <sub>amb</sub> = 25 °C, unless otherwise specified)					
PARAMETER	TEST CONDITION	SYMBOL	VALUE	UNIT	
Repetitive peak reverse voltage		$V_{RRM} = V_{RRM} = V_{R}$	70	V	
Forward continuous current (1)		I <sub>F</sub>	200	mA	
Surge forward current (1)	t <sub>p</sub> < 1 s	I <sub>FSM</sub>	600	mA	
Power dissipation (1)		P <sub>tot</sub>	200	mW	

#### Note

(1) Device on fiberglass substrate, see layout on next page

THERMAL CHARACTERISTICS (T <sub>amb</sub> = 25 °C, unless otherwise specified)						
PARAMETER	TEST CONDITION	SYMBOL	VALUE	UNIT		
Thermal resistance junction to ambient air (1)		R <sub>thJA</sub>	500	K/W		
Junction temperature		Tj	125	°C		
Storage temperature range		T <sub>stg</sub>	-65 to +150	°C		
Operating temperature range		T <sub>op</sub>	-55 to +125	°C		

#### Note

(1) Device on fiberglass substrate, see layout on next page



#### www.vishay.com

## Vishay Semiconductors


<b>ELECTRICAL CHARACTERISTICS</b> (T <sub>amb</sub> = 25 °C, unless otherwise specified)						
PARAMETER	TEST CONDITION	SYMBOL	MIN.	TYP.	MAX.	UNIT
Reserve beakdown voltage	I <sub>R</sub> = 10 μA (pulsed)	V <sub>(BR)</sub>	70			V
Leakage current	V <sub>R</sub> = 50 V	I <sub>R</sub>		20	100	nA
Forward voltage	I <sub>F</sub> = 1.0 mA	V <sub>F</sub>			410	mV
Forward voltage (1)	I <sub>F</sub> = 15 mA	V <sub>F</sub>			1000	mV
Diode capacitance	$V_R = 0 V, f = 1 MHz$	C <sub>D</sub>		1.5	2	pF
Reserve recovery time	$I_F = I_R = 10 \text{ mA}, i_R = 1 \text{ mA},$ $R_L = 100 \Omega$	t <sub>rr</sub>			5	ns

#### Note


### LAYOUT FOR $R_{thJA}$ TEST


Thickness:


Fiberglass 1.5 mm (0.059") Copper leads 0.3 mm (0.012")




### PACKAGE DIMENSIONS in millimeters (inches): SOT-23









Document no.: 6.541-5014.01-4 Rev. 8 - Date: 23.Sept.2009 17418

<sup>&</sup>lt;sup>(1)</sup> Pulse test;  $t_p \le 300 \mu s$ 



## **Legal Disclaimer Notice**

Vishay

### **Disclaimer**

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

# **Mouser Electronics**

**Authorized Distributor** 

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Vishay:

BAS70-05-V-GS08 BAS70-00-GS08 BAS70-06-GS08 BAS70-05-GS08 BAS70-04-GS08 BAS70-06-V-GS08
BAS70-02V-GS08 BAS70-00-V-GS18 BAS70-05-V-GS18 BAS70-06-V-GS18 BAS70-00-V-GS08 BAS70-04-V-GS08
BAS70-04-V-GS18 BAS70-00-E3-08 BAS70-05-E3-08 BAS70-05-E3-18 BAS70-06-E3-08 BAS70-00-E3-18
BAS70-04-HE3-18 BAS70-04-E3-08 BAS70-00-HE3-18 BAS70-05-HE3-08 BAS70-05-HE3-18
BAS70-04-E3-18 BAS70-04-HE3-08 BAS70-06-E3-18 BAS70-06-HE3-18 BAS70-06-HE3-08 BAS581-02V-GS18
BAS16-GS08 BAS40-02V-GS08 BAS581-02V-GS08