

www.vishay.com

Vishay Dale

Power Metal Strip[®] Resistors, Very High Power (to 15 W), Low Value (down to 0.0001 Ω), Surface Mount




DESIGN SUPPORT TOOLS AVAILABLE





FEATURES





 Proprietary processing technique produces extremely low resistance values, down to 0.0001 Ω ROHS
COMPLIANT
HALOGEN
FREE
GREEN
(5-2008)

- Sulfur resistance by construction that is unaffected by high sulfur environments
- Specially selected and stabilized materials allow for high power rating (to 15 W)
- Very low inductance 0.5 nH to 5 nH
- Low thermal EMF (< 3 μV/°C)
- AEC-Q200 qualified (1)
- Material categorization: for definitions of compliance please see <u>www.vishay.com/doc?99912</u>


Notes

- Follow link to Overview of Automotive Grade Products for more details: www.vishay.com/doc?49924
- (1) Flame retardance test may not be applicable to some resistor technologies

STANDARD ELECTRICAL SPECIFICATIONS						
GLOBAL MODEL	SIZE	POWER RATING P _{70 °C} W	TOLERANCE %	$\begin{array}{c} \textbf{RESISTANCE VALUE} \\ \textbf{RANGE} \\ \Omega \end{array}$	RESISTANCE VALUES CURRENTLY AVAILABLE (1) Ω	WEIGHT (typical) g/1000 pieces
WSLP3921	3921	5.0	1.0, 5.0	2m to 4m	2m, 2.5m, 3m, 4m	281
WSLP3921	3921	9.0	1.0, 5.0	0.2m to 1m	0.2m, 0.3m, 0.5m, 0.7m, 1m	281
WSLP5931	5931	7.0	1.0, 5.0	3m	3m	398
WSLP5931	5931	8.0	1.0, 5.0	2m	2m	398
WSLP5931	5931	10.0	1.0, 5.0	0.2m to 1m	0.2m, 0.3m, 0.5m, 1m	398
WSLP5931	5931	15.0	1.0, 5.0	0.1m	0.1m	398

Note

(1) Other values may be available, contact factory



Note

Revision: 14-Mar-2019

- (1) WSL marking (<u>www.vishay.com/doc?30327</u>)
- (2) Packaging code: EB (lead (Pb)-free) is non-standard packaging codes designating 1000 piece reels. These non-standard packaging codes are identical to our standard EA (lead (Pb)-free), except that they have a package quantity of 1000 pieces
- (3) Follow link for customization capabilities: www.vishay.com/doc?48163

1 Document Number: 30176


www.vishay.com

Vishay Dale

TECHNICAL SPECIFICATIONS						
PARAMETER	UNIT	RESISTOR CHARACTERISTICS				
PANAMETEN		WSLP3921	WSLP5931			
	ppm/°C	+125 for 0.2 mΩ	\pm 300 for 0.1 m Ω			
Component temperature coefficient (including terminal) (1)		\pm 175 for 0.3 m Ω , 0.5 m Ω and 0.7 m Ω	\pm 225 for 0.2 m Ω			
TCR measured from -55 °C to 150 °C		\pm 75 for 1 m Ω to 4 m Ω and 2.5 m Ω	\pm 175 for 0.3 m Ω and 0.5 m Ω			
			\pm 75 for 1 m Ω to 4 m Ω			
Element TCR (2)	ppm/°C	< 20				
Operating temperature range	°C	-65 to +170				
Maximum working voltage (3)	V	$(P \times R)^{1/2}$				

- Component TCR total TCR that includes the TCR effects of the resistor element and the copper terminal Element TCR only applies to the alloy used for the resistor element Maximum working voltage the WSL is not voltage sensitive, but is limited by power / energy dissipation and is also not ESD sensitive

DIMENSIONS in inches (millimeters)



Notes

- 3D models available: 3921 model www.vishay.com/doc?30315; 5931 model www.vishay.com/doc?30315; 5931 model
- Surface mount solder profile recommendations: www.vishay.com/doc?31052

MODEL	DIMENSIONS in inches (millimeters)				SOLDER PAD DIMENSIONS in inches (millimeters)		
WIODEL	L	W	Н	Т	d	b	I
WSLP3921	0.394 ± 0.010	0.205 ± 0.010	0.020	0.080 ± 0.010	0.106 ± 0.010	0.244 ± 0.010	0.220 ± 0.005
	(10.0 ± 0.254)	(5.20 ± 0.254)	(0.5)	(2.00 ± 0.254)	(2.70 ± 0.254)	(6.20 ± 0.254)	(5.60 ± 0.13)
WSLP5931	0.591 ± 0.010	0.305 ± 0.010	0.020	0.157 ± 0.010	0.205 ± 0.010	0.344 ± 0.010	0.220 ± 0.005
	(15.0 ± 0.254)	(7.75 ± 0.254)	(0.5)	(4.00 ± 0.254)	(5.20 ± 0.254)	(8.75 ± 0.254)	(5.60 ± 0.13)


GLOBAL MODEL	RESISTANCE VALUE $(m\Omega)$	THERMAL RESISTANCE (1) (°C/W)	"D" THICKNESS (Inches)	ELEMENT MATERIAL
WSLP3921	0.2	2.7	0.0560	Mn-Cu-Sn
WSLP3921	0.3	3.8	0.0510	Mn-Cu
WSLP3921	0.5	5.8	0.0300	Mn-Cu
WSLP3921	0.7	6.3	0.0205	Mn-Cu
WSLP3921	1.0	10.9	0.0150	Mn-Cu
WSLP3921	2.0	12.0	0.0270	Fe-Cr
WSLP3921	3.0	20.7	0.0170	Fe-Cr
WSLP3921	4.0	22.8	0.0130	Fe-Cr
WSLP5931	0.1	2.4	0.0490	Mn-Cu-Sn
WSLP5931	0.2	2.4	0.0490	Mn-Cu
WSLP5931	0.3	3.5	0.0300	Mn-Cu
WSLP5931	0.5	5.7	0.0180	Mn-Cu
WSLP5931	1.0	7.2	0.0330	Fe-Cr
WSLP5931	2.0	13.2	0.0155	Fe-Cr
WSLP5931	3.0	19.3	0.0105	Fe-Cr

⁽¹⁾ The full power rating of Power Metal Strip resistors are dependent upon the ability of the circuit board to dissipate the heat energy created in the resistance element. It is recommended to follow common design practices for power semiconductors that ensure the junction temperature is maintained with in thermal limits by using large pad surfaces, thermal vias, heavier copper weights, internal layers as well as other thermal spreading features. The Thermal resistance values provided function in the same manner as junction to terminal temperature


www.vishay.com

Vishay Dale


DERATING - AMBIENT TEMPERATURE



DERATING - TERMINAL TEMPERATURE



PULSE CAPABILITY



www.vishay.com/resistors/power-metal-strip-calculator

PERFORMANCE				
TEST	CONDITIONS OF TEST	TEST LIMITS		
Thermal shock	-55 °C to +150 °C, 1000 cycles, 15 min at each extreme	± 1.0 %		
Short time overload	5 x rated power for 5 s	± 0.5 %		
Low temperature operation	-65 °C for 24 h	± 0.5 %		
High temperature storage	1000 h at +170 °C	± 1.0 %		
Bias humidity	+85 °C, 85 % RH, 10 % bias, 1000 h	± 0.5 %		
Mechanical shock	100 g's for 6 ms, 5 pulses	± 0.5 %		
Vibration	Frequency varied 10 Hz to 2000 Hz in 1 min, 3 directions, 12 h	± 0.5 %		
Load life at 70 °C	1000 h, 1.5 h "ON", 0.5 h "OFF"	± 1.0 %		
Resistance to solder heat	3 x at 250 °C ± 5 °C for 30 s ± 5 s	± 0.5 %		
Moisture resistance	MIL-STD-202, method 106, 0 % power, 7b not required	± 1.0 %		

PACKAGING								
MODEL		REEL						
WIODEL	TAPE WIDTH	DIAMETER	PIECES/REEL	CODE				
WSLP3921	16 mm/embossed plastic	330 mm/13"	3000	EA				
WSLP5931	24 mm/embossed plastic	330 mm/13"	1500	EA				

Notes

- Embossed carrier tape per EIA-481
- (1) Additional packaging details at www.vishay.com/doc?20051



Legal Disclaimer Notice

Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Vishay:

```
        WSLP39211L000FEB
        WSLP39212L000FEB
        WSLP39213L000FEB
        WSLP39214L000FEB
        WSLP39211L5000FEB

        WSLP59311L000FEB
        WSLP59312L000FEB
        WSLP59313L000FEB
        WSLP5931L3000FEB
        WSLP5931L5000FEB

        WSLP59312L000FEA
        WSLP59311L000FEA
        WSLP39212L000FEA
        WSLP39211L000FEA
        WSLP5931L2000FEA

        WSLP39214L000FEA
        WSLP3921L5000FEA
        WSLP39213L000FEA
        WSLP39213L000FEA
        WSLP39213L000FEA

        WSLP39214L000JEK
        WSLP3921L3000JEA
        WSLP39213L000JEA
        WSLP39213L000JEA
        WSLP39213L000JEA
        WSLP39213L000JEA

        WSLP39211L000FEK
        WSLP39211L000FEK
        WSLP39211L3000JEA
        WSLP39211L3000JEA
        WSLP39211L000JEA
        WSLP39213L000JEA
        WSLP39213L000JEA

        WSLP39213L000FEK
        WSLP39214L000JEA
        WSLP39211L000JEA
        WSLP39211L2000FEK
        WSLP39211L2000FEK

        WSLP39211L4000FEK
        WSLP39211L500FEB
        WSLP39211L2000FEA
        WSLP39211L2000FEK
        WSLP39211L2000JEA

        WSLP39211L500FEB
        WSLP39211L2000JEA
        WSLP39211L2000JEA
        WSLP39211L2000JEA
        WSLP39211L000JEA

        WSLP59311L000JEA
        WSLP39211L2000JEA
        WSLP59311L000FEK
        WSLP39211L5000JEA
```