

Automotive 1500 W Transil™


Datasheet - production data

Features

- Peak pulse power:
 - 1500 W (10/1000 μs)
 - 10 kW (8/20 μs)
- Stand-off voltage range: from 5.8 V to 70 V
- Unidirectional and bidirectional types
- Low leakage current:
 - 0.2 µA at 25 °C
 - 1 μA at 85 °C
- Operating T_{i max}: 150 °C
- High power capability at T_{imax}:
 - 1250 W (10/1000 μs)
- JEDEC registered package outline
- Resin meets UL 94, V0
- AEC-Q101 qualified

Complies with the following standards

- ISO 10605, $C = 150 \text{ pF} R = 330 \Omega$:
 - 30 kV (air discharge)
 - 30 kV (contact discharge)
- ISO 10605 C = 330 pF, R = 330 Ω :
 - 30 kV (air discharge)
 - 30 kV (contact discharge)
- ISO 7637-2^(a)
 - Pulse 1: $V_S = -100 \text{ V}$
 - Pulse 2a: $V_S = +50 \text{ V}$
 - Pulse 3a: V_S = -150 V
 - Pulse 3b: $V_S = +100 \text{ V}$



Description

The SM15TY Transil series has been designed to protect sensitive automotive circuits against surges defined in ISO 7637-2 and against electrostatic discharges according to ISO 10605.

The Planar technology makes it compatible with high-end circuits where low leakage current and high junction temperature are required to provide reliability and stability over time. SM15TY are packaged in SMC (SMC footprint in accordance with IPC 7531 standard).

TM: Transil is a trademark of STMicroelectronics

a. Not applicable to parts with stand-off voltage lower than the average battery voltage (13.5 V)

Characteristics SM15TY

1 Characteristics

Table 1. Absolute maximum ratings ($T_{amb} = 25 \,^{\circ}\text{C}$)

Symbol	Parai	Value	Unit		
V _{PP}	Peak pulse voltage	ISO 10605 (C = 330 Contact discharge Air discharge ISO 10605 (C = 150 Contact discharge Air discharge	30 30 30 30	kV	
P _{PP}	Peak pulse power dissipation ⁽¹⁾	$T_{j initial} = T_{amb}$	1500	W	
T _{stg}	Storage temperature range	-65 to + 150	°C		
T _j	Operating junction temperature range	g junction temperature range		-40 to + 150	°C
T _L	Maximum lead temperature for soldering	260	°C		

^{1.} For a surge greater than the maximum values, the diode will fail in short-circuit.

Figure 1. Electrical characteristics - definitions





Figure 2. Pulse definition for electrical characteristics



SM15TY Characteristics

Table 2. Electrical characteristics, typical values unless otherwise stated ($T_{amb} = 25$ °C)

	I _{RM} max@V _{RM}			V _{BR} @I _R ⁽¹⁾			V _{CL} @I _{PP} 10/1000 μs		R _D 10/1000 μs	V _{CL} @I _{PP} 8/20 μs		R _D 8/20 μs	α T ⁽²⁾	
Order code	25 °C	85 °C		min	typ	max		max			max			max
	μ	A	٧	V			mA	V ⁽³⁾	A ⁽⁴⁾	Ω	V ⁽³⁾	A ⁽⁴⁾	Ω	10-4/ °C
SM15T6V8AY/CAY	500	2000	5.8	6.45	6.8	7.14	10	10.5	143	0.023	13.4	746	0.008	5.7
SM15T7V5AY/CAY	250	1000	6.4	7.13	7.5	7.88	10	11.3	132	0.026	14.5	690	0.01	6.1
SM15T10AY/CAY	10	50	8.55	9.5	10	10.5	1	14.5	103	0.039	18.6	538	0.015	7.3
SM15T12AY/CAY	0.2	1	10.2	11.4	12	12.6	1	16.7	90	0.046	21.7	461	0.02	7.8
SM15T15AY/CAY	0.2	1	12.8	14.3	15	15.8	1	21.2	71	0.076	27.2	368	0.031	8.4
SM15T18AY/CAY	0.2	1	15.3	17.1	18	18.9	1	25.2	59.5	0.106	32.5	308	0.044	8.8
SM15T22AY/CAY	0.2	1	18.8	20.9	22	23.1	1	30.6	49	0.153	39.3	254	0.064	9.2
SM15T24AY/CAY	0.2	1	20.5	22.8	24	25.2	1	33.2	45	0.178	42.8	234	0.075	9.4
SM15T27AY/CAY	0.2	1	23.1	25.7	27	28.4	1	37.5	40	0.228	48.3	207	0.096	9.6
SM15T30AY/CAY	0.2	1	25.6	28.5	30	31.5	1	41.5	36	0.278	53.5	187	0.12	9.7
SM15T33AY/CAY	0.2	1	28.2	31.4	33	34.7	1	45.7	33	0.333	59	169	0.14	9.8
SM15T36AY/CAY	0.2	1	30.8	34.2	36	37.8	1	49.9	30	0.403	64.3	156	0.17	9.9
SM15T39AY/CAY	0.2	1	33.3	37.1	39	41.0	1	53.9	28	0.461	69.7	143	0.2	10
SM15T47AY/CAY	0.2	1	40.2	44.7	47	49.4	1	64.5	23.2	0.653	84	119	0.291	10.1
SM15T56AY/CAY	0.2	1	48	53.3	56	58.9	1	77.4	20	0.925	100	100	0.411	10.3
SM15T68AY/CAY	0.2	1	58.1	64.6	68	71.4	1	92	16.3	1.26	121	83	0.6	10.4
SM15T75AY/CAY	0.2	1	64.1	71.3	75	78.8	1	103	14.6	1.66	134	75	0.74	10.5
SM15T82AY/CAY	0.2	1	70	77.8	82	86.0	1	113	13.9	1.94	146	69	0.87	10.5

^{1.} Pulse test: $t_p < 50 \text{ ms}$

To calculate maximum clamping voltage at other surge level, use the following formula: V_{CL}max = V_{CL} - R_D x (I_{PP} - I_{PPappli}) where IPP_{appli} is the surge current in the application


^{3.} To calculate V_{BR} or V_{CL} versus junction temperature, use the following formulas: V_{BR} @ T_J = V_{BR} @ 25 $^{\circ}$ C x (1 + $^{\alpha}$ T x (T_J - 25)) V_{CL} @ T_J = V_{CL} @ 25 $^{\circ}$ C x (1 + $^{\alpha}$ T x (T_J - 25))

^{4.} Surge capability given for both directions for unidirectional and bidirectional types.

Characteristics SM15TY

Figure 3. Peak pulse power dissipation versus initial junction temperature (typical values)

Figure 4. Peak pulse power versus exponential pulse duration $(T_j \text{ initial } = 25 \text{ °C})$







Figure 5. Clamping voltage versus peak pulse current (exponential waveform, maximum values)

Figure 6. Junction capacitance versus reverse applied voltage for unidirectional types (typical values)








Figure 7. Junction capacitance versus reverse applied voltage for bidirectional types (typical values)

Figure 8. Thermal resistance junction to ambient versus copper surface under each lead





SM15TY Characteristics

Figure 9. Leakage current versus junction temperature (typical values)

Figure 10. Peak forward voltage drop versus peak forward current (typical values)





Figure 11. Relative variation of thermal impedance junction to ambient versus pulse duration



Characteristics SM15TY

Figure 12. ISO7637-2 pulse 1 response ($V_S = -100 \text{ V}$)





Figure 13. ISO7637-2 pulse 2 response ($V_S = 50 \text{ V}$)



SM15TY Characteristics

Figure 14. ISO7637-2 pulse 3a response ($V_S = -150 \text{ V}$)





Figure 15. ISO7637-2 pulse 3b response ($V_S = 100 \text{ V}$)




Note: ISO7637-2 pulses responses are not applicable for product with a stand off voltage lower than the average battery voltage (13.5 V).

2 Application and design guidelines

More information is available in the Application note AN2689 "Protection of automotive electronics from electrical hazards, guidelines for design and component selection".

3 Ordering information scheme

Figure 16. Ordering information scheme



SM15TY Package information

4 Package information

- Case: JEDEC DO-214AB molded plastic over planar junction
- Terminals: solder plated, solderable as per MIL-STD-750, Method 2026
- Polarity: for unidirectional types the band indicates cathode
- Flammability: epoxy is rated UL 94, V0
- RoHS package

In order to meet environmental requirements, ST offers these devices in different grades of ECOPACK[®] packages, depending on their level of environmental compliance. ECOPACK[®] specifications, grade definitions and product status are available at: www.st.com. ECOPACK[®] is an ST trademark.

Table 3. SMC dimensions





Figure 17. SMC footprint dimensions in Figure 18. Marking layout⁽¹⁾ mm (inches)



1. Marking layout can vary according to assembly location.

Package information SM15TY

Table 4. Marking

Order code	Marking	Order code	Marking	
SM15T6V8AY	MDEY	SM15T6V8CAY	BDEY	
SM15T7V5AY	MDGY	SM15T7V5CAY	BDGY	
SM15T10AY	MDPY	SM15T10CAY	BDPY	
SM15T12AY	MDTY	SM15T12CAY	BDTY	
SM15T15AY	MDXY	SM15T15CAY	BDXY	
SM15T18AY	MEEY	SM15T18CAY	BEEY	
SM15T22AY	MEKY	SM15T22CAY	BEKY	
SM15T24AY	MEMY	SM15T24CAY	BEMY	
SM15T27AY	MEPY	SM15T27CAY	BEPY	
SM15T30AY	MERY	SM15T30CAY	BERY	
SM15T33AY	METY	SM15T33CAY	BETY	
SM15T36AY	MEVY	SM15T36CAY	BEVY	
SM15T39AY	MEXY	SM15T39CAY	BEXY	
SM15T47AY	MFAY	SM15T47CAY	BFAY	
SM15T56AY	MFBY	SM15T56CAY	BFBY	
SM15T68AY	MFPY	SM15T68CAY	BFPY	
SM15T75AY	MFOY	SM15T75CAY	BFOY	
SM15T82AY	MFRY	SM15T82CAY	BFRY	

5 Ordering information

Table 5. Ordering information

Order code	Marking	Package	Weight	Base qty	Delivery mode
SM15TxxxAY/CAY ⁽¹⁾	See Table 4 on page 10	SMC	0.25 g	2500	Tape and reel

Where xxx is nominal value of V_{BR} and A or CA indicates unidirectional or bidirectional version. See Table 2 for list of available devices and their order codes

6 Revision history

Table 6. Document revision history

Date	Revision	Changes	
15-Sep-2010	1	Initial release.	
09-Nov-2011	2	Added order codes in <i>Table 2</i> and <i>Table 4</i> . Updated <i>Figure 5</i> , <i>6</i> , <i>7</i> , and <i>Table 1</i> . Added <i>Figure 11</i> . Deleted old Table 2. Thermal parameter. Updated <i>ISO</i> 10605, $C = 150 \text{ pF} - R = 330 \Omega$: on page 1	
27-Mar-2012	3	Added footnote on page 1.	

Please Read Carefully:

Information in this document is provided solely in connection with ST products. STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, modifications or improvements, to this document, and the products and services described herein at any time, without notice.

All ST products are sold pursuant to ST's terms and conditions of sale.

Purchasers are solely responsible for the choice, selection and use of the ST products and services described herein, and ST assumes no liability whatsoever relating to the choice, selection or use of the ST products and services described herein.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted under this document. If any part of this document refers to any third party products or services it shall not be deemed a license grant by ST for the use of such third party products or services, or any intellectual property contained therein or considered as a warranty covering the use in any manner whatsoever of such third party products or services or any intellectual property contained therein.

UNLESS OTHERWISE SET FORTH IN ST'S TERMS AND CONDITIONS OF SALE ST DISCLAIMS ANY EXPRESS OR IMPLIED WARRANTY WITH RESPECT TO THE USE AND/OR SALE OF ST PRODUCTS INCLUDING WITHOUT LIMITATION IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION), OR INFRINGEMENT OF ANY PATENT, COPYRIGHT OR OTHER INTELLECTUAL PROPERTY RIGHT.

UNLESS EXPRESSLY APPROVED IN WRITING BY TWO AUTHORIZED ST REPRESENTATIVES. ST PRODUCTS ARE NOT RECOMMENDED, AUTHORIZED OR WARRANTED FOR USE IN MILITARY, AIR CRAFT, SPACE, LIFE SAVING, OR LIFE SUSTAINING APPLICATIONS, NOR IN PRODUCTS OR SYSTEMS WHERE FAILURE OR MALFUNCTION MAY RESULT IN PERSONAL INJURY, DEATH, OR SEVERE PROPERTY OR ENVIRONMENTAL DAMAGE. ST PRODUCTS WHICH ARE NOT SPECIFIED AS "AUTOMOTIVE GRADE" MAY ONLY BE USED IN AUTOMOTIVE APPLICATIONS AT USER'S OWN RISK.

Resale of ST products with provisions different from the statements and/or technical features set forth in this document shall immediately void any warranty granted by ST for the ST product or service described herein and shall not create or extend in any manner whatsoever, any liability of ST.

ST and the ST logo are trademarks or registered trademarks of ST in various countries.

Information in this document supersedes and replaces all information previously supplied.

The ST logo is a registered trademark of STMicroelectronics. All other names are the property of their respective owners.

© 2012 STMicroelectronics - All rights reserved

STMicroelectronics group of companies

Australia - Belgium - Brazil - Canada - China - Czech Republic - Finland - France - Germany - Hong Kong - India - Israel - Italy - Japan -Malaysia - Malta - Morocco - Philippines - Singapore - Spain - Sweden - Switzerland - United Kingdom - United States of America

www.st.com

12/12 Doc ID 17865 Rev 3



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

STMicroelectronics:

```
SM15T22AY
SM15T22CAY
SM15T24CAY
SM15T27CAY
SM15T33AY
SM15T36AY
SM15T36CAY
SM15T39AY

SM15T47AY
SM15T47CAY
SM15T68CAY
SM15T10AY
SM15T10CAY
SM15T12AY
SM15T12CAY
SM15T15AY

SM15T15CAY
SM15T56CAY
SM15T6V8AY
SM15T6V8CAY
SM15T75CAY
SM15T7V5AY

SM15T7V5CAY
SM15T82CAY
SM15T18AY
SM15T18CAY
SM15T24AY
SM15T27AY
SM15T30AY

SM15T30CAY
SM15T39CAY
SM15T68AY
SM15T75AY
```