

## PCFN-124D2M,000 Product Details



### PCFN-124D2M,000 (1461193-9)

TE Internal Number: 1461193-9

 **Active**

 [Add to Part List](#)

### Industrial Relays (General Purpose)

 [Converted to EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

#### Product Highlights:

- PCF Series
- Contact Arrangement = 1 Form A, SPST-NO, 1 N/O
- Contact Current Rating = 25 Amps.
- Monostable Coil Magnetic System
- Without Coil Suppression Diode

[View all Features](#) | [Find Similar Products](#)

### Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)
- ▶ [Request Samples](#)

**NEW!**

### Documentation & Additional Information

#### Product Drawings:

- [PCFN-D2M SPEC 000 CUSTOMER DRAWING](#) (PDF, English)

#### Catalog Pages/Data Sheets:

- None Available

#### Product Specifications:

- None Available

#### Application Specifications:

- None Available

#### Instruction Sheets:

- None Available

#### CAD Files:

- None Available

#### Additional Information:

- [Product Line Information](#)

#### Related Products:

- [Tooling](#)

[List all Documents](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- [Termination Type](#) = Through Hole

#### Electrical Characteristics:

- [Contact Current Rating \(Amps.\)](#) = 25
- [Coil Resistance \(Ω\)](#) = 640
- [Coil Power, Nominal \(mW\)](#) = 900
- [Actuating System](#) = DC
- [Input Voltage \(VDC\)](#) = 24

#### Body Related Features:

- [Series](#) = PCF

#### Contact Related Features:

- [Mounting Options](#) = PC Board
- [Enclosure](#) = Flux-Tight
- FCC Part 68 Isolation = No
- Relay Type = PCB
- [Contact Material](#) = Silver Tin Oxide
- Approx. Dimensions (L x W x H) (mm [in]) = 30.40 x 16.00 x 26.50 [1.197 x .630 x 1.044]
- Approved Standards = UL Recognized, CSA Certified, TUV Approved

#### Configuration Related Features:

- [Contact Arrangement](#) = 1 Form A, SPST-NO, 1 N/O
- [Coil Magnetic System](#) = Monostable
- [Coil Suppression Diode](#) = Without
- [Coil Selection Criteria](#) = Nominal Voltage
- Coil Latching = Without
- [LED Indicator](#) = Without

#### Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Converted to comply with RoHS directive

#### Other:

- Brand = OEG