



Laird Technologies continues to develop and improve all land mobile radio antenna products. Years of refinement in the mechanical and electrical design of load coil products have resulted in the most technically advanced antennas on the market. These mobile antennas are designed and built for demanding applications and typically outlast the cars they are mounted on. The antennas are manufactured in over 100 variations and each model is permanently marked for model and frequency. No ground plane antennas provide flexibility in any mounting application, while dual and wide band models attain full value out of today's advanced radios. Please contact Laird Technologies for availability on additional products and mobile applications.

FEATURES

- Gold plated contact provides the most corrosion resistance and best power transfer over time
- ABS material is injection molded directly around the solid brass inserts for a virtually indestructible load coil housing that will not leak or disassemble
- Stainless steel shock spring or elastomer spring options dampens vibration and will not rust
- O-ring built into the base provides a weather-tight seal with gold push pin contact for best power transfer over time

APPLICATIONS

- Police Cruisers
- Municipal Vehicles
- Emergency Vehicles
- Industrial Vehicles

global solutions: local support™

Americas: +1.847.839.6907
IAS-AmericasEastSales@lairdtech.com
Europe: +44.(0).1628.858941
IAS-EUSales@lairdtech.com
Asia: +86.21.5855.0827.127
IAS-AsiaSales@lairdtech.com

www.lairdtech.com

| Model | Description | Frequency Range | Center | Gain Freq | Overall Length | Whip Style |
|--------------------------------------|-----------------------------------|-----------------|---------|-----------|----------------|------------------|
| Lowband DC Ground Base Models | | | | | | |
| C27 | 1/4 Wave | 26.75-31 MHz | Tunable | Unity | 52.5" | 49" Tapered |
| C30 | 1/4 Wave | 30 - 35 MHz | Tunable | Unity | 52.5" | 49" Tapered |
| C34 | 1/4 Wave | 34 - 37 MHz | Tunable | Unity | 52.5" | 49" Tapered |
| C37 | 1/4 Wave | 37 - 40 MHz | Tunable | Unity | 52.5" | 49" Tapered |
| C40S | 1/4 Wave w/Spring | 40 - 47 MHz | Tunable | Unity | 52.5" | 49" Tapered |
| C40 | 1/4 Wave | 40 - 47 MHz | Tunable | Unity | 52.5" | 49" Tapered |
| C47 | 1/4 Wave | 47 - 50 MHz | Tunable | Unity | 52.5" | 49" Tapered |
| VHF Models | | | | | | |
| B66 | 1/4 Wave Broadband | 66 - 174 MHz | Tunable | Unity | 51" | 49" Tapered |
| B132 | 1/4 Wave Broadband | 132 - 928 MHz | Tunable | Unity | 23" | 21" Straight |
| B132S | 1/4 Wave Broadband | 132 - 525 MHz | Tunable | Unity | 23" | 21" Straight |
| B1322N | NGP Base Loaded 1/2 Wave | 132 - 174 MHz | Tunable | 2.4 dBi | 57" | 55" Tapered |
| B1322W | 1/4 Wave Wideband | Variable* | Tunable | Unity | 23" | 21" Straight |
| B1322WS | 1/4 Wave Wideband w/spring | Variable* | Tunable | Unity | 23" | 21" Straight |
| B1323S | 5/8 Wave w/Spring | 132 - 174 MHz | Tunable | 3 dBi | 59" | 55" Tapered |
| B1323 | 5/8 Wave | 132 - 174 MHz | Tunable | 3 dBi | 57" | 55" Tapered |
| B1442NS | NGP Base Loaded 1/2 Wave w/Spring | 144 - 174 MHz | Tunable | 2.4 dBi | 53" | 49" Tapered |
| B1442N | NGP Base Loaded 1/2 Wave | 144 - 174 MHz | Tunable | 2.4 dBi | 51" | 49" Tapered |
| B1443 | 5/8 Wave | 144 - 174 MHz | Tunable | 3 dBi | 51-3/8" | 49" Tapered |
| B1443S | 5/8 Wave w/Spring | 144 - 174 MHz | Tunable | 3 dBi | 53-3/8" | 49" Tapered |
| B2003 | 5/8 Wave | 200 - 225 MHz | Tunable | 3 dBi | 35" | 33" Straight |
| B2503 | 5/8 Wave | 250 - 280 MHz | Tunable | 3 dBi | 26.5" | 24-1/2" Straight |
| B2002N | NGP Base Loaded 1/2 Wave | 200 - 225 MHz | Tunable | 2.4 dBi | 31.5" | 29-1/2" Straight |

| Model | Description | Frequency Range | Center | Gain Freq | Overall Length | Whip Style |
|-------------------|--------------------------------|-----------------|---------|-----------|----------------|--------------------|
| UHF Models | | | | | | |
| B4063 | 5/8 Wave | 406 - 430 MHz | Tunable | 3 dBi | 15" | 13" Straight |
| B4303 | 5/8 Wave | 430 - 450 MHz | Tunable | 3 dBi | 14" | 11-13/16" Straight |
| B4503 | 5/8 Wave | 450 - 470 MHz | Tunable | 3 dBi | 13" | 11" Straight |
| B4703 | 5/8 Wave | 470 - 490 MHz | Tunable | 3 dBi | 12.5" | 10-11/16" Straight |
| B4903 | 5/8 Wave | 490 - 512 MHz | Tunable | 3 dBi | 12.5" | 10-1/2" Straight |
| B4065C | Closed Coil Collinear | 406 - 430 MHz | Tunable | 5 dBi | 39.5" | 37-3/8" Collinear |
| B4305C | Closed Coil Collinear | 430 - 450 MHz | Tunable | 5 dBi | 36" | 34-1/8" Collinear |
| B4505CS | Closed Coil Collinear w/Spring | 450 - 470 MHz | Tunable | 5 dBi | 37" | 32-3/4" Collinear |
| B4505C | Closed Coil Collinear | 450 - 470 MHz | Tunable | 5 dBi | 35" | 32-3/4" Collinear |
| B4705C | Closed Coil Collinear | 470 - 490 MHz | Tunable | 5 dBi | 33" | 31-1/4" Collinear |
| B4905C | Closed Coil Collinear | 490 - 512 MHz | Tunable | 5 dBi | 31" | 29-1/8" Collinear |
| B4062N | NGP 1/2 Wave | 406 - 430 MHz | Tunable | 2.4 dBi | 14.31" | 11-9/16" Straight |
| B4302N | NGP 1/2 Wave | 430 - 450 MHz | Tunable | 2.4 dBi | 12.5" | 10-5/8" Straight |
| B4502N | NGP 1/2 Wave | 450 - 470 MHz | Tunable | 2.4 dBi | 12.5" | 10-5/16" Straight |
| B4065CN | NGP Closed Coil Collinear | 406 - 430 MHz | Tunable | 5 dBi | 36" | 34-1/8" Collinear |
| B4305CN | NGP Closed Coil Collinear | 430 - 450 MHz | Tunable | 5 dBi | 35" | 32-7/8" Collinear |
| B4505CN | NGP Closed Coil Collinear | 450 - 470 MHz | Tunable | 5 dBi | 32.5" | 30-1/2" Collinear |
| B4705CN | NGP Closed Coil Collinear | 470 - 490 MHz | Tunable | 5 dBi | 30.5" | 28-7/16" Collinear |
| B4905CN | NGP Closed Coil Collinear | 490 - 512 MHz | Tunable | 5 dBi | 29" | 27-1/8" Collinear |



Innovative **Technology**
for a **Connected** World

Mobile Load Coil Antennas

| Model | Description | Frequency Range | Center Freq | Gain | Overall Length |
|------------------------------|----------------------------|-----------------|-------------|-------|----------------|
| Wideband - Lowband | | | | | |
| WPC3950B-001 | Omnidirectional Heavy Duty | 39 - 46 MHz | 42.5 MHz | 2 dBi | 63-7/8" |
| Wideband - VHF Models | | | | | |
| CW1320 | End Fed 1/4 Wave | 132 - 174 MHz | Tunable | Unity | 18-3/4" |
| CW1443 | Base Loaded 5/8 Wave | 144 - 156 MHz | 150 MHz | 3 dBi | 50-1/2" |
| CW1503 | Base Loaded 5/8 Wave | 150 - 162 MHz | 156 MHz | 3 dBi | 48-1/2" |
| CW1533 | Base Loaded 5/8 Wave | 153 - 169 MHz | 161 MHz | 3 dBi | 49-1/2" |
| CW1623 | Base Loaded 5/8 Wave | 162 - 174 MHz | 168 MHz | 3 dBi | 43-1/2" |
| Wideband - UHF Models | | | | | |
| CW4065C | Closed Coil Collinear | 406 - 430 MHz | 418 MHz | 5 dBi | 37-1/2" |
| CW4405C | Closed Coil Collinear | 440 - 470 MHz | 455 MHz | 5 dBi | 35-1/2" |

ANT-DS-Mobile-Load-Coil 1212

Any information furnished by Laird Technologies, Inc. and its agents is believed to be accurate and reliable. All specifications are subject to change without notice. Responsibility for the use and application of Laird Technologies materials rests with the end user. Laird Technologies makes no warranties as to the fitness, merchantability, suitability or non-infringement of any Laird Technologies materials or products for any specific or general uses. Laird Technologies shall not be liable for incidental or consequential damages of any kind. All Laird Technologies products are sold pursuant to the Laird Technologies Terms and Conditions of sale in effect from time to time, a copy of which will be furnished upon request. © Copyright 2012 Laird Technologies, Inc. All Rights Reserved. Laird, Laird Technologies, the Laird Technologies Logo, and other marks are trade marks or registered trade marks of Laird Technologies, Inc. or an affiliate company thereof. Other product or service names may be the property of third parties. Nothing herein provides a license under any Laird Technologies or any third party intellectual property rights.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

TE Connectivity:

[B1322NR](#) [B1323](#) [B1443](#) [B4703](#) [B4502N](#) [B1443R](#) [B4502NR](#) [B1322N](#) [B132R](#) [B4505CNS](#) [B1442NS](#) [B1443S](#)
[B4505CN](#) [B132S](#) [B4302N](#) [B4305CN](#) [B4065C](#) [B4063](#) [B4505C](#) [B4505CS](#) [B2503](#) [B2003](#) [B66](#) [BB2003S](#) [BB4305C](#)
[BB4305CNS](#) [BB4703S](#) [C27](#) [C37](#) [C47](#) [B4065CNS](#) [B4305CNS](#) [B4905C](#) [B4905CN](#) [B4905CS](#) [BB2003](#) [BB2503S](#)
[BB4062N](#) [BB4063](#) [BB4065C](#) [BB4065CS](#) [BB4302N](#) [BB4303](#) [BB4305CN](#) [BB4703](#) [BB4705C](#) [BB4905C](#) [C27S](#)
[C30](#) [C30S](#) [C34](#) [C34S](#) [C37S](#) [C40](#) [C40S](#) [C47S](#) [CW1503S](#) [CW1533](#) [CW1533S](#) [CW1623](#) [CW1623CO](#) [CW1623S](#)
[CW4405C](#) [B1322NS](#) [B1442NSG](#) [B2003S](#) [B2003SG](#) [B4062NS](#) [B4063S](#) [B4065CS](#) [B4302NS](#) [B4502NS](#) [B4503S](#)
[B4505CSG](#) [B4703S](#) [B4705CNS](#)