



Advanced air-flow design enhances air circulation around battery

 Unique notched slots assure quick and easy battery insertion and replacement

Thru Hole Mount

.074 (1.9) | .503 (12.8)

MATERIAL:

Base: PBT, UL Rated 94V-0


Contacts: .020 (.50) Spring Steel, Tin-Nickel Plate
Operating Temperature: -60°F to +293°F (-51°C to +145°C)

CAT. NO.	C	Н	L	NO. OF CELLS	BATTERY Reference
105	.074 (1.9)	.335 (8.5)	.805 (20.5)	(1) 2430	
1025	.074 (1.9)	.452 (11.5)	.805 (20.5)	(1) 2450 (2) 2430	CR2430, CL2430, BR2450, CR2477

.805 (20.5)

(1) 2477

(2) 2430







Thru Hole Mount

MATERIAL:

Base: PBT, UL Rated 94V-0


Contacts: .020 (.50) Spring Steel, Tin-Nickel Plate


Operating Temperature: -60°F to +293°F (-51°C to +145°C)

CAT. NO.	BATTERY REFERENCE
1068	(1) CR2450, (1) CL2450



- Polarized holder
- Mounts securely for wave soldering
- Reliable spring tension assures low contact resistance





1

Surface Mount

MATERIAL:

Base: LCP, UL Rated 94V-0


Contacts: .006 (.15) Phosphor Bronze, Gold Plate (Flash) Operating Temperature: -60°F to +293°F (-51°C to +145°C)

CAT. NO. BULK		BATTERY REFERENCE
1052	1052TR	(1) CR2450

Tape & Reel Spec's: 56mm wide; 20mm pitch; 13 inch reel, (400 pieces per reel)

24mm TOP Loading AVAILABLE ON TAPE AND REEL


- Polarized holder
- Low profile for densely packed PCB'sCompatible with vacuum and mechanical
- Compatible with vacuum and mechanical pick & place systems
- Conductive carrier tape meets ANSA/EIA- 481 standard





24mm AUTO-IN/EZ-OUT

- Battery "Pop-in" from Top for automated assembly
- No tools required
 Finger pressure ba
- Finger pressure battery release





Mounting Detail

OSS [1.4] DIA
(2) PLS.

Thru Hole Mount

MATERIAL:

Contacts: .008 (.20) Phosphor Bronze, Nickel Plate

Base: High Temp Nylon 46, UL Rated 94V-0

Operating Temperature: -60°F to +293°F (-51°C to +145°C)

CAT. NO.	L	C	BATTERY REFERENCE
1053	.788 (20.0)	.048 (1.2)	(1) CR2450



Thru Hole Mount


MATERIAL:

Contacts: .020 (.50) Spring Steel, Tin-Nickel Plate


Base: PBT, UL Rated 94V-0

Operating Temperature: -60°F to +293°F (-51°C to +145°C)

CAT. NO.	BATTERY REFERENCE	
301	BR3032	



30mm





(800) 221-5510 • kec@keyelco.com